


DRAWING NO: NCA1000-1065-C  
THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: NCA1000-1065  
SUITS CONDUCTOR

ARMOUR RODS

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
19/2.00	COPPER	10.00	RIGHT HAND
7/0.136	COPPER	10.36	RIGHT HAND
19/0.083	COPPER	10.54	RIGHT HAND



BOX LABEL



P/N: NCA1000-1065

ID:

DESCRIPTION:

NON-TENSION HARD DRAWN COPPER ARMOUR RODS

19/2.00 COPPER

7/0.136 COPPER



19/0.083 COPPER

RANGE: 10.00 - 10.65

COLOUR-CODE: YELLOW

QTY: 10    WEIGHT:    BATCH:

PRODUCT LABEL



NCA1000-1065

19/2.00 COPPER

7/0.136 COPPER

19/0.083 COPPER


WEIGHT: 132kg

BATCH NO:   

MONTH/YEAR:

TECHNICAL SPECIFICATIONS;

CATALOGUE NUMBER: NCA1000-1065  
DESCRIPTION: NON-TENSION HARD DRAWN COPPER ARMOUR RODS  
MATERIAL: HARD DRAWN COPPER WIRE  
NUMBER OF RODS: 10  
ROD DIAMETER: 3.65mm  
OVERAL LENGTH: 1320mm  
END FINISH: CHAMFERED  
FITTING LAY DIRECTION: RIGHT HAND  
COLOUR CODED: YELLOW  
RODS ARE LABELED, BUNDLED IN A SET AND TAPED AT BOTH ENDS.

							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE		IMPLIED TOLERANCES HOLE DIA AND LOCATIONS:±0.5mm. DIMENSIONS UP TO 30mm:±1.5mm. DIMENSIONS OVER 30mm:±5% UP TO A MAX OF:±5mm. ANGULAR DIMENSIONS:±5°.		TCPN - PART Alias UTX/DUL NCA1000-1065 Cat No NCA1000-1065		TITLE NON-TENSION HARD DRAWN COPPER ARMOUR RODS (NCA) FITTING COND.RANGE: Ø10.00-Ø10.65 19/2.00 COPPER 7/0.136 COPPER 19/0.083 COPPER								
LOC												DRAWN RN		DATE 06-05-2013		 TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia					
												CHECKED MN		APPROVED AT							
DIST	—	I	NEW RELEASE		06-05-2013	RN	AT	MATERIAL DESC HARD DRAWN COPPER WIRE						SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO NCA1000-1065-C		SHEET 1	OF 1	REV 1
	POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO											

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.