

© 2020 TE Connectivity. All Rights Reserved.


PRINT:
5:1






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	Inner Hsg: chamfer removed	03SEP2010	CLA	ASC
	E1	ECR-12017745	17OCT2012	SZN	SZG
	E2	LASER PRINT UPDATED	10DEC2019	SZN	LSZ

CODINGS
M 2:1



A-A



NOTES:

1 AREA FOR PRINT

2 USABLE CONTACTS MCON 1.2
SEE TE-NO. 1452674, SINGLE WIRE SYSTEM

3 MAX. WIRE SIZE RANGE 1.0 mm² FLR PERMITTED
FOR CAVITY-Ø 3.55MM
QUANTITY SEE WIRE HARNESS DRAWING
FOR PERMISSIBLE CURRENT CARRYING CAPACITY OF THE SINGLE CONTACT
SEE PRODUCT SPECIFICATION NO.108-18782

4 SUPPLIER-MARK

5 SPACE OF ACTIVITY

6 SUPPLY CONDITION: RETAINER IN PRELOCKED POSITION

7 WARPAGE PERMITTED TO MAX. -0.5mm

8 TE ORDER-NO.

9 ACCORDING TO INTERFACE DRAWING
SEE TE-NO. 114-18679-3

10 ASSEMBLY LINE SEGMENT IDENTIFICATION


11 DATE CODE (DDDYY)

12 DIVERGENT MARKING FOR PARTS FROM DIFFERENT LOCATIONS (BR, CN, U.S...)

CODING A AS SHOWN


TE-ORDER-NO. 8	COD	DESCRIPTION	REV	QTY	DESCRIPTION	MATERIAL	SURFACE/COLOUR	ITEM
3-1670915-1	C	2pos. MCON 1.2 - LL Connector, Sealed	A	1	2pos. MCON 1.2 - Seal	MVQ-30	NATURE	4
				1	2pos. MCON 1.2 - Retainer	PA66-GF15	VIOLETT	3
				1	2pos. MCON 1.2 - Protec. Cover	PA6-GF15	BLACK	2
				1	2pos. MCON 1.2 - Recepticle Hsg.	PA66-GF30	BLUE	1
2-1670915-1	B	2pos. MCON 1.2 - LL Connector, Sealed	A	1	2pos. MCON 1.2 - Seal	MVQ-30	NATURE	4
				1	2pos. MCON 1.2 - Retainer	PA66-GF15	VIOLETT	3
				1	2pos. MCON 1.2 - Protec. Cover	PA6-GF15	BLACK	2
				1	2pos. MCON 1.2 - Recepticle Hsg.	PA66-GF30	NATURE	1
1-1670915-1	A	2pos.MCON 1.2 - LL Connector, Sealed	E	1	2pos. MCON 1.2 - Seal	MVQ-30	NATURE	4
				1	2pos. MCON 1.2 - Retainer	PA66-GF15	VIOLETT	3
				1	2pos. MCON 1.2 - Protec. Cover	PA6-GF15	BLACK	2
				1	2pos. MCON 1.2 - Recepticle Hsg.	PA66-GF30	BLACK	1

RETAINER IN END POSITION



3D VIEW
1:1





THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ALL TO DIN 9001/ISO TUNING TO NOM. DIN AND ISO 8015
ANGLES ±2°

MATERIAL -
FINISH -

DWN	R. Bachmann	19DEC2006
CHK	A. Schroebel	26SEP2008
APVD	J. Waller	26SEP2008
PRODUCT SPEC	108-18969	
APPLICATION SPEC	114-18861	
WEIGHT	2.4 g	

TE Connectivity

NAME 2pos. MCON 1.2 - LL Connector , Sealed
Version with turned rec. hsg.

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-1670915	

CUSTOMER DRAWING | SCALE 15:1 | SHEET 1 OF 1 | REV E2

4805 (3/13)