

# 6000 Series Photocontrol Electronic | Heavy-Duty Grade Control

# **KEY FEATURES**

- High reliability, versatile, and long-life
- Multi-volt operation
- High-temp housing and components
- 360 Joule MOV Standard
- Meets or exceeds ANSI C136.10

### **COMMON USES**

- Designated for all traditional roadway and area lighting applications and equipment
- Compatible with all solid state ballast | Drivers applications and equipment

TE Connectivity's (TE) advanced technology 6000 Series Photocontrol provides a unique mix of low-cost, long-life, and multi-volt operation for demanding Roadway Lighting applications.

## Innovative Long Life Design

TE's unique design considerably improves the relay life. Rated by 2000W operation, the 6000 Series exceeds the 1000W requirements of ANSI C136.10 by surpassing 11,000 ON/OFF operations, its expected life is far greater than 10 years.

#### **Rugged Housing**


Like all of our electronic controls, the 6000 Series utilizes our interlocking base/cap design for superior environmental protection.

#### **Programmable Option**

The newest member of the 6000 Series family, the 6190, utilizes a microprocessor in its design ensuring precise calibration for inverse ratio operation and allowing for user-defined factory programmable attributes including ON/OFF ratios, ON light levels and time delays. That's Advanced Technology!



# **6000 Series Photocontrols**



The 6000 Series is the result of over fifty years of experience designing and delivering superior photocontrols and other lighting accessories in the US and around the world.

#### Features

Rated Volts Frequency Operating Light Levels Time Delay ON/OFF OFF/ON Ratio Fail Mode Surge Protection Rated Life 105 - 305 VAC 50/60 Hz Standard 1.5 Fc ON (optional 1 - 3 Fc) Instant ON, 2 - 5 second delay OFF 1.5 : 1 & 0.6 : 1 ON 360 Joules 10 years


## Specifications

#### Dimensions: approx. 3.26" [83mm] dia. x 2.08" [53mm] high (not including contacts) Physical Enclosure: designed to meet ANSI C136.10 Power consumption: less than 0.5 watts at 120 VAC Minus 40°C to plus 65°C Temperature @ 96% RH DC Electromagnetic switch type exceeds 11,000 Control **ON/OFF** operations per ANSI C136.10 Relay Rating 30 Amp Rated at 120 VAC Load Rating 2000 Watt Tungsten 1800 VA Non-drifting Phototransistor Light Sensor

ANSI Standard Cap Colors	
120V	Gray
208 / 240 / 277V	Maroon
120 / 208 / 240 / 277V	Blue

## How to Specify

The 6000 series offers almost unlimited options ensuring your lighting network needs will be met.



#### **TE Technical Support Center**

USA:	+1 (800) 327-6996
Canada:	+1 (905) 475-6222
Mexico	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

#### energy.te.com

© 2005-2008, 2012 Tyco Electronics Corporation

a TE Connectivity Ltd. Company. All Rights Reserved.

4-1773447-1 E268 04/2012

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.



P = Phototransistor

F = IR Filtered Phototransistor

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.