

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	See ECO-19-002621	2/19/19	J.B	T.L

ES2000
Flame - Retardant, Adhesive - Lined
Heat - Shrinkable Tubing




Table 1: Dimensions mm (inches)

Size	As Supplied		As Recovered							
	Minimum Expanded I.D. Including Core (D)		Maximum Recovered I.D. Including Core (d)		Minimum Recovered Total Wall (W)		Minimum Recovered Adhesive Wall (W1)		Minimum Recovered Jacket Wall (W2)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
No.0	4.57	0.180	1.02	0.040	0.86	0.034	0.38	0.015	0.48	0.019
No.1	5.72	0.225	1.27	0.050	1.20	0.047	0.56	0.022	0.64	0.025
No.2	7.44	0.293	1.65	0.065	1.52	0.060	0.76	0.030	0.76	0.030
No.3	10.85	0.427	2.41	0.095	1.91	0.075	1.02	0.040	0.89	0.035
No.4	17.78	0.700	4.45	0.175	2.41	0.095	1.37	0.054	1.04	0.041
No.11	9.02	0.355	2.29	0.090	1.78	0.070	0.94	0.037	0.84	0.033

Color: Jacket shall be black; adhesive liner shall be amber.

Reference Specification 108-120024

THIS DRAWING IS UNPUBLISHED.
 ALL RIGHTS RESERVED.
 COPYRIGHT 2019 TE Connectivity

DIMENSIONS: INCHES	DWN	J. Bitter	09AUG2017	MATERIAL	-	FINISH	-			
	CHK	T. Licko	-							
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	T. Licko	-							
0 PLC ± -	PRODUCT SPEC	-	NAME	ES2000 Flame - Retardant, Adhesive - Lined Heat - Shrinkable Tubing						
1 PLC ± -	APPLICATION SPEC	-	SIZE	A4	CAGE CODE	00779	DRAWING NO	ES2000	RESTRICTED TO	-
2 PLC ± -	WEIGHT	0	SCALE	None	SHEET	1	OF	1	REV	A
3 PLC ± -	CUSTOMER DRAWING									
4 PLC ± -										
ANGLES ± -										