


REV: EC0 # DATE: A1 09-012043 18 MAY 09




STRAIGHT ADAPTOR

- 00









| Tyco Electronics | | Raychem Adapters 305 Constitution Drive Menlo Park, CA 94025, USA | | TITLE: HEXASHIELD ADAPTOR FOR CODE 40 CONNECTORS TINEL CLAMPING NUT | | | | |
|-------------------------|--|---|--|--|---------|-------------|--|--|
| DIMENSIONS AR | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN | | Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application. | | -KC-YY- | YY-AYY-2-YY | | |
| BRACKETS. | | | | | | | | |
| DRAWN: | DATE: | APPROVED: | DATE: | CODE IDENT. NO: | SCALE: | SHEET: | | |
| A. BUI | 13 MAY 09 | M. PIOZET | 13 MAY 09 | 06090 | NONE | 1 OF 4 | | |

| REV: | EC0 # | DATE: |
|------|-----------|-----------|
| A1 | 09-012043 | 18 MAY 09 |

KIT DESCRIPTION

| ITEM | DESCRIPTION | MATERIAL | | |
|------|---------------------------------|-----------------|--|--|
| 1 | BODY ASSEMBLY | STAINLESS STEEL | | |
| 2 | TINEL CLAMPING ADAPTOR ASSEMBLY | STAINLESS STEEL | | |
| | TINEL-LOCK™ RING | TINEL-X™ | | |
| 3 | CONIC RING | STAINLESS STEEL | | |
| 4 | STAR | STAINLESS STEEL | | |

TABLE OF DIMENSIONS

| Order Number | Shell | Size | Tinel Entry | ØA Thread Class 6H | ØB Max | ØC Max | D Max | E Max | F Max | G Max | | rule ntity |
|-----------------|-------|------|----------------|-----------------------|------------------|------------------|-----------------|-----------------|-----------------|-----------------|------|---------------|
| | Mil. | Com. | Size | | | | | | | | Std. | Opt. |
| 09 | Α | 09 | 05 | M12 x 1 | 19.0 [0.75"] | 38.5 [1.52"] | 12.5 [0.49"] | 38.5 [1.52"] | 16.0 [0.63"] | 42.0 [1.65"] | 1 | - |
| 11 | В | 11 | 08 | M15 x 1 | 22.0 [0.87"] | 38.5 [1.52"] | 13.0 [0.51"] | 39.0 [1.54"] | 17.5 [0.69"] | 43.5 [1.71"] | 2 | - |
| 13 | С | 13 | 10 | M18 x 1 | 25.5 [1.00"] | 38.5 [1.52"] | 14.0 [0.55"] | 39.5 [1.56"] | 19.0 [0.75"] | 45.0 [1.77"] | 3 | - |
| 15 | D | 15 | 12 | M22 x 1 | 30.5 [1.20"] | 38.5 [1.52"] | 14.5 [0.57"] | 40.5 [1.60"] | 20.5 [0.81"] | 46.5 [1.83"] | 5 | - |
| 17 | Е | 17 | 14 | M25 x 1 | 33.5 [1.32"] | 38.5 [1.52"] | 15.0 [0.59"] | 41.0 [1.61"] | 22.0 [0.87"] | 48.0 [1.89"] | 6 | 7 |
| 19 | F | 19 | 16 | M28 x 1 | 37.0 [1.46"] | 38.5 [1.52"] | 15.5 [0.61"] | 41.5 [1.63"] | 23.5 [0.93"] | 49.5 [1.95"] | 7 | 8 |
| 21 | G | 21 | 18 | M31 x 1 | 38.5 [1.52"] | 38.5 [1.52"] | 16.5 [0.65"] | 42.5 [1.67"] | 25.5 [1.00"] | 51.5 [2.03"] | 9 | 11 |
| 23 | Н | 23 | 20 | M34 x 1 | 42.0 [1.65"] | 38.5 [1.52"] | 17.0 [0.67"] | 43.0 [1.69"] | 27.0 [1.06"] | 53.0 [2.09"] | 10 | 13 |
| 25 | J | 25 | 20 | M37 x 1 | 46.5 [1.83"] | 46.0 [1.81"] | 18.0 [0.71"] | 51.5 [2.03"] | 28.5 [1.12"] | 62.0 [2.44"] | 12 | 18 |


| Tinel Entry Size | ØS |
|------------------------|-----------------|
| | |
| 05 | 10.97/11.13 |
| | [0.432/0.438"] |
| 08 | 15.72/15.91 |
| | [0.619"/0.626"] |
| 10 | 18.84/19.11 |
| | [0.742"/0.752"] |
| 12 | 22.02/22.28 |
| | [0.867"/0.877"] |

| Tinel Entry Size | øs |
|------------------------|--------------------------------|
| 14 | 25.17/25.46 [0.991"/1.002"] |
| 16 | 28.34/28.63 [1.116"/1.127"] |
| 18 | 31.52/31.81 [1.241"/1.252"] |
| 20 | 34.69/34.98 [1.366"/1.377"] |

| ≆ Tycc | Electronics | 305 Constitution Drive | Raychem Adapters 305 Constitution Drive Menlo Park, CA 94025, USA | | TITLE: HEXASHIELD ADAPTOR FOR CODE 40 CONNECTORS TINEL CLAMPING NUT | | | | |
|--|--------------------|--|---|--------------------------|--|---------------|--|--|--|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS. | | Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application. | | DOCUMENT NO. HEX40 | -KC-YY- | YY-AYY-2-YY | | | |
| DRAWN: A BUI | DATE: 13 MAY 09 | APPROVED: M. PIOZET | DATE: 13 MAY 09 | CODE IDENT. NO: 06090 | SCALE: NONE | SHEET: 2 OF 4 | | | |

| REV: | EC0 # | DATE: |
|------|-----------|-----------|
| A1 | 09-012043 | 18 MAY 09 |

PART NUMBERING




APPLICATION

- These adaptors are designed to be mounted on the following connectors:

MIL-DTL-38999 Series III and IV

- They are qualified to the Tyco Electronics specification RB-114, when installed on metallic Mil-Specification circular connectors only.
- They are designed for wire bundle installations having an single overall braid terminated by means of a Tinel-Lock™ ring.
- They are also designed to accept Raychem heat shrink moulded parts where strain relief and sealing is required see illustrations.



- Use in conjunction with the ferrules HET-A-0XX, which are purchased separately. Refer to HET-A-0XX Customer Drawing for relevant
- selection details.
- * Refer to TR Customer Drawing for further information on Tinel-Lock™ rings.

INSTALLATION

- See Installation Procedure RPIP-696-04.

PACKAGING


- All components are supplied in a plastic bag.

| Tyco Electronics | | Raychem Adapters 305 Constitution Drive Menlo Park, CA 94025, USA | | HEXASHIELD ADAPTOR FOR CODE 40 CONNECTORS TINEL CLAMPING NUT | | | | |
|--|--------------------|--|--------------------|--|----------------|------------------|--|--|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS. | | Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application. | | HEX40-KC-YY-YY-AYY-2-YY | | | | |
| DRAWN: A. BUI | DATE: 13 MAY 09 | APPROVED: M. PIOZET | DATE: 13 MAY 09 | CODE IDENT. NO: 06090 | SCALE: NONE | SHEET: 3 OF 4 | | |

| REV: | EC0 # | DATE: |
|------|-----------|-----------|
| A1 | 09-012043 | 18 MAY 09 |

NOTES

- 1. Item 4 Star is not supplied with Hexashield Order Number 09.
- 2. The DS option, illustrated below, is for a Drilled Star that is available on sizes 15 to 25 only. This option is to allow unshielded wires to pass through the assembly.




| STAR SIZE | 15 | 17 | 19 | 21 | 23 | 25 |
|-----------|---------|---------|---------|---------|---------|---------|
| ØH MAX | 3.0 | 6.0 | 9.0 | 12.0 | 15.0 | 18.0 |
| | [0.12"] | [0.24"] | [0.35"] | [0.47"] | [0.59"] | [0.71"] |

3. Where the ferrule quantities required are standard, the item 4 - Star - is also standard.

If the optional quantity is selected then 2 items 4 will be supplied - one "split" and the other one standard*, See below for illustration.

EXAMPLE: FERRULE QUANTITY CODE -A13

-A13 = -A10 SPLIT STAR + -A3 STANDARD STAR



- * On Order Number 19 only, the Optional Ferrule quantity of 8 uses a "standard" star also.
- 4. Assembly is to be permanently marked with Code Identity Number and Part Number. (e.g. 06090 HEX40-KC-00-21-A9-2)

| Tyco Electronics | | Raychem Adapters 305 Constitution Drive Menlo Park, CA 94025, USA | | HEXASHIELD ADAPTOR FOR CODE 40 CONNECTORS TINEL CLAMPING NUT | | | | |
|--|-------|--|-----------|--|---------|--------|--------|--|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS. | | Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application. | | DOCUMENT NO. HEX40- | -KC-YY- | YY-AYY | -2-YY | |
| DRAWN: | DATE: | APPROVED: | DATE: | CODE IDENT. NO: | SCALE: | SHEET: | | |
| A. BUI 13 MAY 09 | | M. PIOZET | 13 MAY 09 | 06090 | NONE | | 4 OF 4 | |