Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A

Supplier Information							
Company Name	TE Connectivity	**Request Document ID**		**Contact Name**	TE PRODUCT COMPLIANCE	**Contact Title**	
Company Unique ID	TE Connectivity	**Response Date**	2018-08-19	**Contact Email**	productcompliance@te.com		
Contact Phone Number	+001-800-522-6752						

Legal Statement	
Supplier Acceptance	true

Legal Statement

The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.

Product							
Manufacturer Item number	2-103635-4	**Amount**	5.25779338	**Version**	-	**Identity**	
Manufacturer Item Name	25 MTE HDR SRRA LATCH .100CL	**Weight Uom**	g	**Mfr Site**		**Authority**	
Date		**UOM**	Each				
EURoHS-0508	Product(s) does not meet EU RoHS requirements and is not under exemptions						
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products						
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed						
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed						

Product Disclosure

Sub-Item/Material/ Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	25 MTE HDR HSG SR LATCH .100				1.0	3.906	g	
Material	2	LCP-GF35				1.0	3.906	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	2.0	1.0	0.07812	g	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	34.3	1.0	1.339758	g	
Substance	3	1,3-Benzenedicarboxylic acid, polymer with 1,4-benzenedicarboxylic acid, [1,1-biphenyl]-4,4-diol and 4-hydroxybenzoic acid	Supplier	60088-52-0	62.7	1.0	2.449062	g	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	0.03906	g	
Sub-Item	1	MTE POST PLTD 15 DPLX				25.0	0.05407174	g	
Material	2	Brass				25.0	0.053216	g	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	25.0	5.3216E-7	g	
Substance	3	Zinc	Supplier	7440-66-6	28.0225	25.0	0.01491245	g	
Substance	3	Manganese	Supplier	7439-96-5	0.05	25.0	2.6608E-5	g	
Substance	3	Antimony	Supplier	7440-36-0	0.01	25.0	5.3216E-6	g	
Substance	3	Iron	Supplier	7439-89-6	0.05	25.0	2.6608E-5	g	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	25.0	5.3216E-5	g	
Substance	3	Copper	Supplier	7440-50-8	71.5	25.0	0.03804944	g	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	25.0	5.3216E-7	g	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	25.0	5.3216E-6	g	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	25.0	2.6608E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	0.2	25.0	1.0643E-4	g	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	25.0	2.6608E-6	g	

Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	25.0	2.6608E-5	g	
Material	2	Nickel Plate				25.0	5.9489E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	25.0	1.189788E-6	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	25.0	5.94894E-7	g	
Substance	3	Nickel	Nickel	7440-02-0	99.7	25.0	5.9311E-4	g	
Material	2	Gold Plate				25.0	8.3873E-5	g	
Substance	3	Gold	Supplier	7440-57-5	99.7	25.0	8.362138E-5	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	25.0	2.51619E-7	g	
Material	2	Tin-Lead Plate				25.0	1.7697E-4	g	
Substance	3	Tin	Supplier	7440-31-5	86.5	25.0	1.5308E-4	g	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.5	25.0	8.8484E-7	g	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	13.0	25.0	2.300584E-5	g	