

POSITION SENSORS

We are a leading manufacturer of industrial linear and angular position, tilt and fluid level sensors. Both off-the-shelf and custom position sensing solutions are available featuring our core technologies, including inductive, potentiometric, magnetoresistive, hall effect, reed switch, electrolytic and capacitive sensing. Sophisticated designs and manufacturing techniques provide reliable and cost effective solutions for a broad range of harsh applications such as automotive, power generation, subsea, hydraulics, medical, HVACR, process controls, factory automation, security systems, military/aerospace and nuclear. TE position sensors are available with analog and digital outputs. Our comprehensive range of signal conditioning instrumentation enables us to meet the specific needs of OEMs and end users.



ANISOTROPIC MAGNETORESISTIVE (AMR) SENSOR COMPONENTS

Magnetoresistive (MR)



MEAS KMY, KMZ

Package	SOT-223, E-line 4 pin
Type	Linear low field sensor
Range	-2 to 2 kA/m magnetic field
Unique Features	<ul style="list-style-type: none"> • High sensitivity • Low hysteresis • Linear to uniaxial field strength
Output	Ratiometric with output voltage range 20 mV/V
Resolution	Typ. 0.1% of range
Accuracy	Typ. 1.0% of range
Operating Temp.	-40°C to 150°C
Dimensions (mm)	SOT: 6.6 x 7.0 x 1.6 E-line: 16 x 4.2 x 2.4
Typical Applications	Non-destructive material testing, spray arm detection in dish washers, magnetic imaging, brake pedal position




MEAS MS32

Package	TDFN
Type	Low field switch sensor
Range	1 to 3 kA/m magnetic switching field
Unique Features	<ul style="list-style-type: none"> • Linearized ratiometric output • Temperature compensated switching point
Output	Ratiometric with output voltage range 10 mV/V
Resolution	Typ. 0.1 kA/m
Accuracy	Typ. 0.1 kA/m
Operating Temp.	-25°C to 85°C
Dimensions (mm)	TDFN: 2.5 x 2.5 x 0.8
Typical Applications	Piston position switch, reed switch replacement



MEAS KMT32B, KMT37

Package	TDFN, SO-8
Type	Angle sensor
Range	180° angle
Unique Features	<ul style="list-style-type: none"> • High accuracy • High resolution
Output	Sine and cosine signals with output voltage range 20 mV/V
Resolution	Typ. 0.01° to 0.1°
Accuracy	Typ. 0.1° to 1.0°
Operating Temp.	-40°C to 150°C (175°C on request)
Dimensions (mm)	TDFN: 2.5 x 2.5 x 0.8 SO-8: 5 x 4 x 1.75
Typical Applications	Steering position, flow meters, rpm meters, rotary encoders



MEAS KMT36H

Package	TDFN 2.5 x 2.5
Type	Angle sensor
Range	360° angle
Unique Features	<ul style="list-style-type: none"> • High accuracy • High resolution • 360° full turn
Output	Three 120° phase shifted output signals with output voltage range 20 mV/V
Resolution	Typ. 0.01° to 0.1°
Accuracy	Typ. 0.1° to 1°
Operating Temp.	-40°C to 150°C
Dimensions (mm)	TDFN: 2.5 x 2.5 x 0.8
Typical Applications	Steering position, gage readings, rotary encoders



MEAS KMX Series

Package	DFN 2 x 6
Type	Linear displacement sensor
Range	Absolute within pole pitch, else incremental
Unique Features	<ul style="list-style-type: none"> • For pole pitch • KMX 1000: p= 1 mm • KMX 2000: p= 2 mm • KMX 5000: p= 5 mm
Output	Sine and cosine signals with output voltage range 20 mV/V
Resolution	0.01% to 0.1% of pole pitch
Accuracy	0.1% to 1.0% of pole pitch
Operating Temp.	-40°C to 125°C
Dimensions (mm)	DFN: 2 x 6 x 0.8
Typical Applications	Roller conveyors, circular saws, bending machines etc.



MEAS KMA36

Package	TSSOP
Type	Angle sensor
Range	360° angle
Unique Features	<ul style="list-style-type: none"> • Low cost MR encoder for rotational and incremental measurements
Output	Voltage 0 - 5 V, I ² C, customer specific
Resolution	Typ. 0.1°
Accuracy	Typ. 0.3°
Operating Temp.	-25°C to 85°C
Dimensions (mm)	TSSOP20: 6.5 x 6.4 x 1.2
Typical Applications	Knobs, small robotics, angular / linear position

ANGULAR POSITION TRANSDUCERS—INDUCTIVE

Absolute



MEAS RVIT-Z

Package	PCB for OEM volumes
Resolution	Infinite
Excitation	DC voltage
Output	DC voltage, DC current, digital
Range	Up to ±75°
Unique Features	<ul style="list-style-type: none"> • Absolute position
Operating Temp.	-25°C to 85°C
Dimensions (mm)	Custom
Typical Applications	Viscometers, valve position, robotics, HVACR vane position, ATM's, joysticks



MEAS R60D

Package	Servo mount with ball bearing
Resolution	Infinite
Excitation	DC symmetrical ±15 VDC
Output	±7.5 VDC
Range	±60°
Unique Features	<ul style="list-style-type: none"> • Absolute position • Low momentum of inertia
Operating Temp.	-25°C to 85°C
Dimensions (mm)	Aluminum case size 11 (Ø27 mm)
Typical Applications	Dancer arm position, rotary actuator position feedback, throttle lever position feedback, ball valve position, textile manufacturing equipment, printing presses



MEAS R30A

Package	Servo mount with ball bearing
Resolution	Infinite
Excitation	AC operated
Output	AC voltage
Range	±30° to ±60°
Unique Features	<ul style="list-style-type: none"> • Absolute position
Operating Temp.	-55°C to 150°C
Dimensions (mm)	Aluminum case size 11 (Ø27 mm)
Typical Applications	Machine tool equipment, rotary actuator feedback, valve positioning, power generation valve position

ANGULAR POSITION—ENCODERS

Absolute



MEAS ED-18

Package	Medium duty with sleeve or ball bearing
Resolution	Analog 1.4°
Max. Speed	300 RPM (Sleeve bearing) 3000 RPM (Ball bearing)
Excitation	5 VDC
Unique Features	<ul style="list-style-type: none"> • Low profile • Excellent stability • No optical degradation
Output	Voltage or current
Range	360°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	25.4 x 25.4 x 33.78
Typical Applications	Feedback sensor or human machine interface device, servomotor position and speed control



MEAS ED-22

Package	Medium duty with sleeve bearing
Resolution	Analog 1.4°
Max. Speed	300 RPM
Excitation	5 VDC
Unique Features	<ul style="list-style-type: none"> • Encapsulated electronics, sealed unit • Highly resistant to vibration • No optical degradation
Output	Voltage
Range	270°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	Ø19.1 x 37.1
Typical Applications	Low-cost, non-contact human machine interface potentiometer replacement



MEAS R36

Package	Heavy duty shaftless
Resolution	Analog 1.4°
Max. Speed	—
Excitation	5 VDC
Unique Features	<ul style="list-style-type: none"> • Rugged housing • Shaftless • No optical degradation
Output	Voltage
Range	180°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	37.36 x 25.4 x 7.62
Typical Applications	Feedback sensor or human machine interface device, rudder control, servomotor position and speed control

ANGULAR POSITION—ENCODERS

Absolute



MEAS H005, H009 Series

Package	<ul style="list-style-type: none"> • 12.7 mm - 22.19 mm / .500 in - .875 in housing diameter • 3.170 mm / .1248 in shaft diameter • 16.9 mm - 17.4 mm / .670 in - .680 in housing length
Range	Up to 359 degrees
Output Options	Analog / PWM / Serial
Resolution	12-bit analog / PWM 14-bit serial (SPI)
Absolute Linearity	±0.2%
Nominal Supply	5 volts
Operating Temp.	-40°C to 150°C
Rotational Life	> 100 million cycles (Bearing life)
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets



MEAS H009, 1200 Series Dual Output

<ul style="list-style-type: none"> • 22.23 mm / .875 in housing diameter • 3.170 mm / .1248 in shaft diameter • 26.1 mm / 1.03 in housing length 	<ul style="list-style-type: none"> • 22.23 mm / .875 in housing diameter • 3.170 mm / .1248 in shaft diameter • 26.1 mm / 1.03 in housing length
Range	Up to 359 degrees (Dual output)
Output Options	Analog / PWM / Serial
Resolution	12-bit analog / PWM 14-bit serial (SPI)
Absolute Linearity	± 0.2% (Dual output)
Nominal Supply	5 volts (Dual output)
Operating Temp.	-40°C to 150°C
Rotational Life	> 100 million cycles (Bearing life)
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets

Incremental



MEAS ED-19

Package	Medium duty with sleeve or ball bearing
Resolution/ Accuracy	1024, 400, 256 CPR (Others on request)
Max. Speed	300 RPM (Sleeve bearing) 3000 RPM (Ball bearing)
Excitation	5 VDC
Unique Features	<ul style="list-style-type: none"> • Sleeve or ball bearing • No optical degradation
Output	Quadrature (TTL level, open collector)
Range	360°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	25.4 x 25.4 x 33.78
Typical Applications	Feedback sensor or human machine interface device, servo / stepper motor position and speed control



MEAS ED-20

Medium duty with ball bearing	Medium duty with ball bearing
1024, 400, 256 CPR (Others on request)	1024, 400, 256 CPR (Others on request)
3000 RPM	3000 RPM
5 VDC (NPN and LVD), 12 - 32 VDC (HVD)	5 VDC (NPN and LVD), 12 - 32 VDC (HVD)
<ul style="list-style-type: none"> • Resistant to contamination • Metallic threaded bushing mounting • No optical degradation 	<ul style="list-style-type: none"> • Resistant to contamination • Metallic threaded bushing mounting • No optical degradation
Quadrature (NPN, LVD and HVD)	Quadrature (NPN, LVD and HVD)
360°	360°
-40°C to 85°C	-40°C to 85°C
Ø31.75 x 33.24	Ø31.75 x 33.24
Feedback sensor or human machine interface device, servo / stepper motor position and speed control	Feedback sensor or human machine interface device, servo / stepper motor position and speed control

TILT SENSORS

Single Axis



MEAS E-Series

Package	Ceramic housing
Type	Inclination sensor module
Range	±5°, ±15°
Output	Voltage
Unique Features	<ul style="list-style-type: none"> • Easy to handle • Minimal temperature drift • Good long term stability
Accuracy	±0.2° to ±0.5°
Operating Temp.	-25°C to 85°C
Dimensions (mm)	29 x 17 x 16.5
Typical Applications	Road construction, building monitoring, weighing systems, mobile and stationary cranes, platform leveling



MEAS AccuStar EA

Package	LCP housing
Type	Inclinometer sensor module
Range	±45° to ±60°
Output	Voltage
Unique Features	<ul style="list-style-type: none"> • Compact • Low power • Vertical and horizontal mount
Accuracy	0° to 10° ±0.1% accuracy 10° to 60° ±0.75% reading
Operating Temp.	-30°C to 65°C
Dimensions (mm)	65.91 x 51.56 x 30.5
Typical Applications	Wheel alignment, construction, equipment, antenna positioning, robotics, crane / boom angle



MEAS APS System

Package	Plastic housing
Type	Inclination system
Range	±45°, ±90°
Output	Analog / digital
Unique Features	<ul style="list-style-type: none"> • Stand alone system • Separate system and sensor
Accuracy	0° to 10° ±0.1% accuracy 10° to 45° ±0.75% of reading
Operating Temp.	-25°C to 65°C
Dimensions (mm)	127.5 x 88 x 32.2
Typical Applications	Tower crane safety, RV and mobile trailer leveling, water and oil well drilling rigs, mining equipment



MEAS G-Series

Package	Aluminum housing IP67
Type	Inclinometer
Range	±10°
Output	Switch
Unique Features	<ul style="list-style-type: none"> • Programmable • EMC standard • High switch accuracy
Accuracy	±0.25°
Operating Temp.	-25°C to 85°C
Dimensions (mm)	80 x 75 x 57.5
Typical Applications	Lift platforms, building device control, train inclination monitoring, position switch



MEAS IT9000

Package	Aluminum or stainless
Type	Inclinometer
Range	±45° to ±240°
Output	Voltage divider, 4 - 20 mA
Unique Features	<ul style="list-style-type: none"> • Rugged industrial design, IP67 / 68 • Submersible • Designed for brutal environments • CSA, CENELEC certification for hazardous area applications
Accuracy	±1%
Operating Temp.	-34°C to 90°C
Dimensions (mm)	Ø130 x 100
Typical Applications	Waste water control, tainter gates, draw bridges, heavy industrial applications



MEAS AccuStar IP66

Package	Aluminum housing IP66
Type	Inclinometer
Range	±3° to ±45°
Output	Current
Unique Features	<ul style="list-style-type: none"> • EMI and RFI rated • CE pending • Water tight enclosure
Accuracy	0° to 10° ±0.1% linearity 10° to 45° ±1% linearity
Operating Temp.	-25°C to 60°C
Dimensions (mm)	98.04 x 63 x 35.05
Typical Applications	Tower crane safety, RV and mobile trailer leveling, water and oil well drilling rigs, mining equipment

TILT SENSORS

Dual Axis



MEAS DPL, DPN Series

Package	PCB board
Type	Inclination board module
Range	±2° to ±30°
Output	Voltage / RS 232 / SPI
Unique Features	<ul style="list-style-type: none"> • High resolution • Minimal temperature drift • User configurable
Accuracy	±0.05° to ±0.8°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	45 x 45 x 20
Typical Applications	Laser leveling, weighing systems, mobile and stationary cranes, hydraulic leveling, building monitoring, wind power



MEAS DOG2 Series

Package	Plastic PA 6.6 housing, IP67
Type	Inclinometer
Range	±25°, ±45°, ±90°
Output	Voltage / Current / J1939 / CANopen®
Unique Features	<ul style="list-style-type: none"> • Plug and play • Wide measurement range • Cost-efficient • Cable with connector • Fast MEMS sensor
Accuracy	< ± 0.5° (Full temp. range)
Operating Temp.	-40°C to 85°C
Dimensions (mm)	70.5 x 45 x 15
Typical Applications	Off road vehicle, fork lift, truck leveling, man lift, harvester, farm machine, tip over protection, solar panel control



MEAS DPG Series

Package	Aluminum housing IP67
Type	Inclinometer
Range	±5° to ±30°
Output	RS232 / Voltage
Unique Features	<ul style="list-style-type: none"> • CE approved • Rugged housing • Easy to use • User configurable
Accuracy	±0.05° to ±0.3°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	84 x 70 x 34.2
Typical Applications	Platform leveling, road construction machines, tunnel drilling, mobile leveling



MEAS D Series

Package	Aluminum housing IP67
Type	Inclinometer
Range	±5° to ±30°
Output	RS232 / Voltage / Current / Switch / PWM / CANopen®
Unique Features	<ul style="list-style-type: none"> • High accuracy • Rugged housing • Programmable • CE approved
Accuracy	±0.04° to ±0.8°
Operating Temp.	-40°C to 85°C
Dimensions (mm)	84 x 70 x 46
Typical Applications	Drilling machines, mobile and stationary cranes, wind power, antenna / radar leveling

PROXIMITY SENSORS



MEAS PS801

Package	Stainless steel
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPST reed switch, normally open
Operating Temp.	-30°C to 120°C
Dimensions (mm)	Ø12 x 65
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PS811

Package	Nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPST reed switch, normally open
Operating Temp.	-30°C to 110°C
Dimensions (mm)	Ø10 x 38
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PS831

Package	Stainless steel
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPST reed switch, normally open
Operating Temp.	-30°C to 130°C
Dimensions (mm)	Ø12 x 32
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PS2011AB

Package	Glass filled nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPST reed switch, normally open
Operating Temp.	-30°C to 105°C
Dimensions (mm)	29 x 7 x 20
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PS2021AB

Package	Glass filled nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPST reed switch, normally closed
Operating Temp.	-30°C to 105°C
Dimensions (mm)	29 x 7 x 20
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PS2031AB

Package	Glass filled nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPDT reed switch
Operating Temp.	-30°C to 105°C
Dimensions (mm)	29 x 7 x 20
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PS501

Package	Glass filled nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity sensor • Used with proximity magnet
Unique Features	SPST reed switch, normally open
Operating Temp.	-30°C to 130°C
Dimensions (mm)	Ø6 x 32
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication

PROXIMITY MAGNET



MEAS PM101

Package	Glass filled nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity magnet • Used with proximity sensor
Unique Features	Housed magnet
Operating Temp.	-30°C to 105°C
Dimensions (mm)	29 x 7 x 20
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PM50

Package	Glass filled nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity magnet • Used with proximity sensor
Unique Features	Housed magnet
Operating Temp.	-30°C to 70°C
Dimensions (mm)	Ø6 x 32
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PM81

Package	Nylon 6.6
Type	<ul style="list-style-type: none"> • Proximity magnet • Used with proximity sensor
Unique Features	Housed magnet
Operating Temp.	-30°C to 120°C
Dimensions (mm)	Ø10 x 38
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication



MEAS PM83

Package	Stainless steel
Type	<ul style="list-style-type: none"> • Proximity magnet • Used with proximity sensor
Unique Features	Housed magnet
Operating Temp.	-30°C to 120°C
Dimensions (mm)	Ø12 x 32
Typical Applications	Door interlocks, hook switches, security systems, safety interlocks, position indication

LINEAR POSITION TRANSDUCERS

Cable Extension Transducers



MEAS PT1, PT5

Range	0 - 2 to 0 - 250 inches
Output	Voltage divider, 0 - 5 VDC, 0 - 10 VDC, 4 - 20 mA, incremental encoder, CANbus, DeviceNet™, RS-232
IP Rating	IP65, IP67 (PT5)
Enclosure	Aluminum and abs plastic (PT1)
Accuracy	±0.04% to ±0.25%
Unique Features	<ul style="list-style-type: none"> • Designed for most factory environments • Industry standard output signals • User serviceable • Compact design (PT1)
Operating Temp.	-40°C to 90°C
Dimensions (mm)	85 x 100 x 70 (PT1) 100 x 175 x 80 (PT5)
Typical Applications	Factory automation, industrial, die casting, injection molding



MEAS PT8000

Range	0 - 2 to 0 - 60 inches
Output	Voltage divider, 0 - 5 VDC, 0 - 10 VDC, 4 - 20 mA, incremental / absolute encoder, CANbus, DeviceNet™, RS-232
IP Rating	IP67, IP68
Enclosure	Aluminum or stainless
Accuracy	±0.04% to ±0.25%
Unique Features	<ul style="list-style-type: none"> • Heavy duty, submersible • Designed for extreme industrial and marine environments • CSA, CENELEC certification for hazardous area applications • High accuracy, high acceleration • Free-release proof with VLS option • M12 and DEUTSCH connector options
Operating Temp.	-40°C to 90°C
Dimensions (mm)	90 x 140 x 135
Typical Applications	Steel mills, lumber and paper mills, factory automation, die-casting, injection molding, mobile construction and mining



MEAS PT9000

Range	0 - 75 to 0 - 1700 inches
Output	Voltage divider, 0 - 5 VDC, 0 - 10 VDC, 4 - 20 mA, incremental / absolute encoder, CANbus, DeviceNet™, RS-232
IP Rating	IP67, IP68
Enclosure	Aluminum or stainless
Accuracy	±0.04% to ±0.25%
Unique Features	<ul style="list-style-type: none"> • Heavy duty, submersible • Proven workhorse for long stroke applications • Designed for extreme industrial and marine environments • CSA, CENELEC certification for hazardous area applications • Free-release proof with VLS option • M12 and DEUTSCH connector options
Operating Temp.	-40°C to 90°C
Dimensions (mm)	200 x 135 x 125
Typical Applications	Mobile hydraulic boom position, water resource management, mining and tunnel boring equipment, telescoping mechanism position, theatre stage control

LINEAR POSITION TRANSDUCERS

Cable Extension Transducers



MEAS M150, MTA

Range	0 - 1.5 to 0 - 5 inches
Output	Voltage divider
Environment / IP Rating	IP50
Enclosure	Aluminum
Accuracy	±0.4% to ±1%
Unique Features	<ul style="list-style-type: none"> • M150: one of the world's smallest stringpots • Designed for space-critical and testing applications
Operating Temp.	-40°C to 85°C (M150) -55°C to 100°C (MTA)
Dimensions (mm)	19 x 19 x 10 (M150)
Typical Applications	Aerospace, automotive instrumentation, automotive crash testing, automotive and motorcycle racing



MEAS MT2, MT3

Range	0 - 3 to 0 - 30 inches
Output	Voltage divider, incremental encoder
Environment / IP Rating	IP50, IP67 (MT3A)
Enclosure	Aluminum and polycarbonate
Accuracy	±0.25% to ±1.1%
Unique Features	<ul style="list-style-type: none"> • Designed for test applications • Dual-axis measuring cable alignment • Tracks high-acceleration linear position up to 136g's • High-frequency response • GAM EG 13 certification
Operating Temp.	-55°C to 125°C
Dimensions (mm)	55 x 45 x 55
Typical Applications	Automotive crash testing, aerospace and flight testing



MEAS SM, SP

Range	0 - 2.5 to 0 - 50 inches
Output	Voltage divider, 0 - 10 VDC, 4 - 20 mA
Environment / IP Rating	IP50, IP67 (SP)
Enclosure	Polycarbonate with stainless steel bracket
Accuracy	±0.25% to ±1%
Unique Features	<ul style="list-style-type: none"> • In-stock • Compact design • M12 connection • Adjustable mounting bracket • Free-release tolerant • Custom configurations for OEMS
Operating Temp.	-18 to 70°C (SM) -40°C to 85°C (SP)
Dimensions (mm)	120 x 140 x 140
Typical Applications	Factory automation, light industrial, seismic testing, racing instrumentation, medical imaging systems, fume hood position



MEAS SG, SR

Range	0 - 80 to 0 - 175 inches
Output	Voltage divider, 0 - 5 VDC, 0 - 10 VDC, 4 - 20 mA, incremental encoder, CANbus
Environment / IP Rating	IP67
Enclosure	Polycarbonate with stainless steel bracket
Accuracy	±0.35% to ±0.5%
Unique Features	<ul style="list-style-type: none"> • In stock • Low cost, high value stringpot • Versatile stainless steel mounting bracket • Simple one-button user scalable stroke range (SR) • Custom configurations available for OEM customers
Operating Temp.	-40°C to 85°C
Dimensions (mm)	100 x 120 x 200
Typical Applications	Outdoor mobile construction equipment, outrigger positioning, hydraulic lifts, water and power controls



MEAS SK1, SK6

Range	0 - 250 and 0 - 400 inches
Output	4 - 20 mA, 0 - 10 V, voltage divider, CAN J1939, CANopen®, Encoder drive
Environment / IP Rating	IP67
Enclosure	Polycarbonate with stainless steel bracket
Accuracy	±.25% FS
Unique Features	<ul style="list-style-type: none"> • In stock • Compact design • M12 connectivity • Adjustable mounting bracket
Operating Temp.	-40°C to 85°C
Dimensions (mm)	120 x 140 x 140
Typical Applications	Mobile construction equipment, factory automation



MEAS PTX, PT101

Range	0 - 2 to 0 - 100 inches
Output	Voltage divider, 0 - 5 VDC, 0 - 10 VDC, 4 - 20 mA, incremental encoder, velocity output (DV301)
Environment / IP Rating	IP50
Enclosure	Aluminum
Accuracy	±0.04% to ±0.25%
Unique Features	<ul style="list-style-type: none"> • Original classic design • High precision • Proven track record
Operating Temp.	-40°C to 90°C
Dimensions (mm)	Model and range specific
Typical Applications	Aerospace testing, architectural and structural testing, factory automation

LINEAR POSITION TRANSDUCERS—INDUCTIVE

Absolute



MEAS HR

Package	AISI-400 series stainless steel
Linearity	±0.25% of range
Excitation	AC operated
Output	AC voltage
Range	±0.05 to ±10 inches
Unique Features	<ul style="list-style-type: none"> • Large bore to core clearance • Broad range of excitation frequencies • Variety of options • Mild radiation resistance option
Operating Temp.	-55°C to 150°C (220°C optional)
Diameter (mm)	20.6
Typical Applications	General industrial



MEAS M12

Package	AISI-304 series stainless steel
Linearity	±0.25% of range
Excitation	AC operated
Output	AC voltage
Range	±10 to ±100 mm
Unique Features	<ul style="list-style-type: none"> • Metric series • High stroke to length ratio • Constant sum of secondaries • Excellent temperature coefficient
Operating Temp.	-55°C to 150°C (220°C optional)
Diameter (mm)	12
Typical Applications	Hydraulic spool valve position feedback, flight simulators, aircraft flight control feedback



MEAS HC

Package	AISI-400 series stainless steel
Linearity	±0.25% of range
Excitation	AC and DC operated versions
Output	AC or DC voltage, 4 - 20 mA loop or RS-485
Range	±0.05 to ±10 inches
Unique Features	<ul style="list-style-type: none"> • Hermetically sealed • Welded connector • Double shielding • Intrinsically safe version • CE mark for DC versions
Operating Temp.	-55°C to 150°C (AC); 0°C to 70°C (DC)
Diameter (mm)	19
Typical Applications	Harsh environments, submersible applications, process controls, valve position feedback



MEAS XS-C

Package	AISI-304 series stainless steel
Linearity	±0.25% of range
Excitation	AC operated
Output	AC voltage
Range	±0.25, ±0.5 and ±1 inches
Unique Features	<ul style="list-style-type: none"> • High pressure • Bulkhead mounting • Hermetically sealed welded assembly
Operating Temp.	-55°C to 150°C
Diameter (mm)	19
Typical Applications	Hydraulic actuators, other pressurized vessels



MEAS DC-SE

Package	AISI-400 series stainless steel
Linearity	±0.25% of range
Excitation	8.5 to 28 VDC
Output	0 - 5 VDC (4 wire), 1 - 6 VDC (3 wire)
Range	0 - 0.1 to 0 - 6 inches
Unique Features	<ul style="list-style-type: none"> • CE mark • Low current consumption (6 mA typical) • Synchronous demodulation • Shielded cable
Operating Temp.	-25°C to 85°C
Diameter (mm)	19
Typical Applications	Positioning sensing feedback, battery operated systems, test labs, ram guide, platen position



MEAS XS-D

Package	AISI-400 series stainless steel
Linearity	±2% of range
Excitation	AC operated
Output	AC voltage
Range	±1 to ±10 inches
Unique Features	<ul style="list-style-type: none"> • Very high stroke to body length ratio
Operating Temp.	-55°C to 150°C
Diameter (mm)	20.6
Typical Applications	Where sensor installation length is restricted, ideal replacement for linear potentiometers

Other models available, please consult MEAS website library.

LINEAR POSITION TRANSDUCERS—INDUCTIVE

Absolute



MACRO HSTA/R

Package	AISI-410 stainless steel
Linearity	±0.25% of range
Excitation	AC operated
Output	AC voltage
Range	±0.050 to ±10.0 inches
Unique Features	<ul style="list-style-type: none"> • IP68 rating, hermetically sealed • Mild radiation resistant (30 Mrad) optional • Axial or radial connector with thru-bore construction
Operating Temp.	-55°C to 200°C standard (Contact factory for higher temperature)
Diameter (mm)	19
Typical Applications	High temperature steam and gas valves, nuclear power plants, harsh and corrosive environments, environments with heavy dust, dirt, and humidity



MACRO HLR/HLIR

Package	AISI-410 stainless steel
Linearity	±0.25% of range
Excitation	AC (HLR) or DC (HLIR)
Output	AC voltage or 4-20 mA
Range	±1 to ±10 inches
Unique Features	<ul style="list-style-type: none"> • UL/ULC or CSA intrinsically safe rating • Intrinsically safe: <ul style="list-style-type: none"> • Class I Division I, Class I Division II • ATEX certified • 1/2" NPT conduit thread
Operating Temp.	-50°C to 100°C (Per Macro Sensors instructions)
Diameter (mm)	19
Typical Applications	Gas turbine servo controls, fuel valve position feedback, petrochemical process plants



MACRO SSI/R

Package	Alloy 625
Linearity	±0.10% of range
Excitation	AC or DC operated
Output	AC or 4-20 mA loop digital CANbus available
Range	±1.0 to ±10.0 inches
Unique Features	<ul style="list-style-type: none"> • Operating pressure to 5,000 psi (7,500 psi proof) • Seawater submersible IP68 • Standard Seacon connector • Axial or radial connection
Operating Temp.	-40°C to 80°C
Diameter (mm)	23.9
Typical Applications	Off-shore drilling platforms, pipeline monitoring, choke valves, mooring cables, extensometers, pulp and paper mills



MACRO HPGS 750

Package	AISI-410 stainless steel
Linearity	±0.25% of range
Excitation	AC operated
Output	AC voltage
Range	±0.050 to ±10.0 inches
Unique Features	<ul style="list-style-type: none"> • Radial screw-on 38999 connector • IP68 rating, hermetically sealed • Designed for high vibration applications
Operating Temp.	-55°C to 200°C
Diameter (mm)	19
Typical Applications	Nuclear power generation equipment, hydraulic cylinder position, steam valve positioning, power generation equipment, corrosive environments, high-vibration environments



MACRO CD375

Package	AISI-410 stainless steel
Linearity	±0.25% of range
Excitation	AC operated
Output	AC voltage
Range	± 0.025 to ±1 inches
Unique Features	<ul style="list-style-type: none"> • Compact design • Operating pressure to 20,000 psi+
Operating Temp.	-55°C to 200°C
Diameter (mm)	9.5
Typical Applications	Machine tools, robotic grippers, medical equipment, valve position sensing, hydraulic cylinder, down-hole equipment



MACRO GHSE/R

Package	AISI-410 stainless steel
Linearity	±0.1% of range
Excitation	DC operated
Output	0 - 10 VDC
Range	0.100 to 4 inches
Unique Features	<ul style="list-style-type: none"> • Spring loaded design • IP68 rating, hermetically sealed • Axial and radial connection • Low pressure air-extend / spring-retract version available (GHSER 750-A)
Operating Temp.	-20°C to 70°C
Diameter (mm)	19
Typical Applications	Industrial gaging systems, replaces dial indicators, fabricated metal products gaging

LINEAR POSITION TRANSDUCERS—INDUCTIVE

Dimensional Gaging Products



MEAS LBB Spring-Extend



MEAS LBB Air-Extend



MEAS PCA 375



MEAS GC



MEAS Ultimate-Precision Digital LBB

Linearity	±0.2% of range	±0.2% of range	±0.5% of range	±0.25% (Voltage) to ±0.5% (4 - 20 mA) of range	Accuracy ±0.2%
Excitation	AC operated	AC operated	AC operated	AC or DC voltage	5 VDC USB (Bus or external)
Output	AC voltage	AC voltage	AC voltage	AC or DC voltage, RS-485, or 4 - 20 mA loop	RS485; USB
Range	±0.02 to ±0.20 inches	±0.04 and ±0.1 inches	±0.02 to ±1 inches	±0.05 to ±2 inches	1, 2, 5 and 10 mm
Unique Features	<ul style="list-style-type: none"> • 0.000004 inch (0.1 µm) repeatability • Removable tungsten carbide contact tip • Double shielded LVDT • Repairable 	<ul style="list-style-type: none"> • 0.000004 inch (0.1 µm) repeatability • Removable tungsten carbide contact tip • Double shielded LVDT • Repairable 	<ul style="list-style-type: none"> • Longer strokes • IP65 cable exit • Accepts industry standard contact tips • Heavy duty return spring 	<ul style="list-style-type: none"> • Hermetically sealed • Welded MS connector (MIL-C-5015) • CE mark for DC versions • Special tips available • Air extend spring retract available 	<ul style="list-style-type: none"> • Plug-and-play • 14-bit resolution • COM libraries provided • CE mark • USB adapter and power supply available
Operating Temp.	-40°C to 70°C	-40°C to 70°C	-20°C to 70°C	-55°C to 150°C (AC) 0°C to 70°C (DC)	0°C to 60°C
Diameter (mm)	8 or 9.5	8 or 9.5	9.5	19 mm body, 1/2 - 20 threads	Stackable gage system
Typical Applications	Process standards, manufacturing on-line inspection, robotics, replaces dial indicators in manual measurement systems	Process standards, manufacturing on-line inspection, robotics, replaces dial indicators in manual measurement systems	High density gaging fixtures, resistance weld verification, pressing applications, X-Y stage position feedback, rough casting inspection	Harsh environments, environments requiring hermetic seal, high temperatures (150°C for AC units)	Multi-channel electronic dimensional gaging, precision dimensional measurement, optics inspection systems, SPC data collection, hand tools

LINEAR POSITION ENCODERS

Incremental



MEAS ED32i

Package	IP67 aluminum
Range	Magnetic scale, 5 mm pole pitch, typically up to 100 m absolute version up to 100 mm range on request
Excitation	5 VDC
Output	5 V TTL ABZ differential quadrature; RS-485
Resolution	≥10 µm; field programmable
Max. Speed	4 m/s
Unique Features	<ul style="list-style-type: none"> • Contactless incremental measurement • Very high accuracy, programmable resolution • High speed up to 4 m/s • Error detection, missing scale function • Adapter plate for easy mounting
Operating Temp.	-25°C to 85°C
Dimensions (mm)	60 x 20 x 10
Typical Applications	Linear displacement measurement in industrial and medical applications

ANGULAR POSITION—POTENTIOMETERS



MEAS 6000 Series

Servo Mount

Package	<ul style="list-style-type: none"> • 12.7 mm - 50.8 mm / 0.500" - 2.00" housing diameter • 3.170 mm - 6.34 mm / 0.1248" - 0.2498" shaft diameter • 12.7 mm - 1.74 mm / 0.500" - 0.680" housing length • 11.11 mm - 47.62 mm / 0.438" - 1.875" mounting pilot diameter
Resistance	1K - 20K Ω
Range	Up to 355°
Linearity	\pm 0.5%
Output Smoothness	<0.1%
Resolution	Infinite
Operating Temp.	-65°C to 125°C
Rotational Life	50 million cycles / minute
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets



MEAS 6200 Series

Bushing Mount

<ul style="list-style-type: none"> • 12.7 mm - 50.8 mm / 0.500" - 2.00" housing diameter • 3.170 mm - 6.34 mm / 0.1248" - .2498" shaft diameter • 12.7 mm - 1.74 mm / 0.500" - 0.680" housing length • 3/8 32 NEF thread / 10.31 mm / 0.4062" pilot diameter 	
Resistance	1K - 20K Ω
Range	Up to 355°
Linearity	\pm 0.5%
Output Smoothness	<0.1%
Resolution	Infinite
Operating Temp.	-65°C to 125°C
Rotational Life	50 million cycles / minute
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets



MEAS 6900 Series

Element/Wiper/Insulator

Package	<ul style="list-style-type: none"> • 17.81 mm - 45.85 mm / 0.702" - 1.805" in element outside diameter • 4.724 mm - 11.05 mm / 0.186" - 0.435" element inside diameter • 3.175 mm - 6.35 mm / 0.125" - 0.250" shaft insulator inside diameter • 4.064 mm - 7.80 mm / 0.160" - 0.307" mating wiper inside diameter • 5.08 mm / 0.200" assembled package height
Resistance	1K / 5K / 10K Ω
Range	Up to 350°
Linearity	\pm 0.5%
Output Smoothness	< 0.1%
Resolution	Infinite
Operating Temp.	-65°C to 125°C
Rotational Life	50 million cycles / minute
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets



MEAS 6100 Series

Hollow Shaft

<ul style="list-style-type: none"> • 27.94 mm - 66.5 mm / 1.100" - 2.62" housing diameter • 3.175 mm - 19 mm / 0.125" - 0.752" hollow shaft diameter 	
Resistance	1K - 20K Ω
Range	Up to 355°
Linearity	\pm 0.5%
Output Smoothness	< 0.1%
Resolution	Infinite
Operating Temp.	-65°C to 125°C
Rotational Life	50 million cycles / minute.
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets

ANGULAR POSITION—POTENTIOMETERS



MEAS RT8, RT9

Package	Aluminum or stainless IP67, IP68
Resolution	±0.15% to ±1.25%
Unique Features	<ul style="list-style-type: none"> • Absolute rotary • Designed for heavy industrial applications • CSA, CENELEC certification for hazardous area applications
Output	Voltage divider, 0 - 5 V, 0 - 10 V, 4 - 20 mA, incremental encoder, CANbus, DeviceNet™
Range	0 - 0.125 to 0 - 200 turns
Operating Temp.	-40°C to 90°C
Dimensions (mm)	Ø65 x 100 (RT8) Ø115 x 60 (RT9)
Typical Applications	Valve control, airport passenger loading bridge, water management, factory automation

LINEAR POSITION—POTENTIOMETERS



MEAS MLP, CLP

Package	Aluminum body, steel rod, IP65, IP67
Range	0 - 0.5 to 0 - 6" (MLP) 0 - 1 to 0 - 10" (CLP)
Linearity	±0.5 to ±1% (MLP) ±0.1 to ±0.2% (CLP)
Excitation	Up to 40 VDC max.
Output	Voltage divider
Resolution	Essentially infinite
Max. Speed	10 m/s
Unique Features	<ul style="list-style-type: none"> • Extended temperature range, miniature design • First choice for auto racing applications • Perfect for high cycle applications
Operating Temp.	-40°C to 90°C
Dimensions (mm)	Diameter / cross section: Ø9.5 mm (MLP) 15 mm x 15 mm (CLP)
Typical Applications	Vehicle testing, autosport instrumentation, structural and architectural testing and robotics.



MEAS 5903, 5905 Series

Linear Motion

Package	<ul style="list-style-type: none"> • 7.94 mm - 12.7 mm / 0.312" - 0.500" housing diameter • 1.98 mm - 3.18 mm / 0.078" - 0.125" shaft diameter
Resistance	1K / 5K / 10K
Range	5903 series - up to 50.8 mm / 2" stroke 5905 series - up to 101.6 mm / 4" stroke
Linearity	±1%
Output Smoothness	<0.1%
Resolution	Infinite
Operating Temp.	-65°C to 125°C
Stroke Life	50 million cycles min
Typical Applications	Critical position feedback applications in commercial, industrial, medical, aircraft and military markets

LVDT / RVDT INSTRUMENTATION



MEAS LVM-110, LiM-420

Package Open circuit board

Supply DC voltage

Output DC voltage or current

Operating Temp. 0°C to 55°C

Unique Features

- Master / slave for multi-up applications
- Dip switch selectable excitation frequencies
- Plug-in PCB or wire termination
- Small form factor

Dimensions (mm) 63 x 56 x 21

Typical Applications OEM applications



MEAS LDM-1000

Package DIN rail mount

Supply 10 to 30 VDC

Output DC voltage and current

Operating Temp. -25°C to 85°C

Unique Features

- Operates with 4, 5 & 6 wire LVDT / RVDTs
- Adjustable zero, span and phase
- Status LEDs
- CE mark

Dimensions (mm) 115 x 99 x 23

Typical Applications Automotive test track instrumentation, gas and steam turbine controls, factory automation



MEAS ATA-2001

Package 1/8 DIN panel mount

Supply 115 and 220 VAC, 50 - 400 Hz

Output DC voltage and current

Operating Temp. -40°C to 85°C

Unique Features

- Push button programmable
- Splash proof front panel
- LED status lights
- Mounting hardware included
- CE mark

Dimensions (mm) 267 x 99 x 49

Typical Applications Precision metrology labs, power generation valve position monitoring



MEAS PML 1000

Package 1/8 DIN panel mount

Supply 90 to 265 VAC, 50 - 60 Hz or 24 VDC

Output DC voltage and current (RS-485 optional)

Operating Temp. 10°C to 55°C

Unique Features

- 5 digit LED display
- Auto-calibration
- Programmable
- Splash proof front panel
- Mounting hardware included
- CE mark

Dimensions (mm) 173 x 97 x 49

Typical Applications Remote monitoring stations, measurement test stands, process monitoring



MEAS MP 2000

Package 1/4 DIN panel mount

Supply 100 to 240 VAC, 47 - 63 Hz

Output DC voltage and RS-232

Operating Temp. 0°C to 55°C

Unique Features

- Programmable set point controller
- Dual channel with math functions
- Digital I/O
- Large LCD display
- Splash proof front panel

Dimensions (mm) 178 x 92 x 92

Typical Applications LVDT based weighing systems, pass / fail parts sorting, quality inspection



MACRO LVC-4000

Package DIN rail mount

Supply 9 to 30 VDC

Output RS-485, DC voltage, and 4-20 mA

Operating Temp. -20°C to 75°C

Unique Features

- Push-button calibration
- Digital RS-485 interface
- Master / slave excitation synchronization (Up to 16 channels)
- Supports all standard AC LVDTs, RVDTs, and VR half-bridge sensors

Dimensions (mm) 114.5 x 99 x 22

Typical Applications Gas and steam turbine controls, automotive test instrumentation, factory automation



MACRO LVC-4500

Package DIN rail mount

Supply 9 to 30 VDC

Output RS-485, DC voltage, and 4-20 mA

Operating Temp. -20°C to 75°C

Unique Features

- Push-button calibration
- Diff / sum ratiometric conditioning
- Digital RS-485 interface
- Master / slave excitation synchronization (Up to 16 channels)
- Supports all standard AC LVDTs, RVDTs, and VR half-bridge sensors

Dimensions (mm) 114.5 x 99 x 22

Typical Applications Gas and steam turbine controls, automotive test instrumentation, factory automation



MACRO MMX Mini Module

Package DIN rail mount

Supply 15 to 30 VDC

Output DC voltage or 4-20 mA

Operating Temp. 0°C to 70 °C

Unique Features

- Push-button calibration
- Flame retardant mini-module housing
- Master / slave excitation synchronization (Up to 10 channels)
- LED status lights
- Supports all standard AC LVDTs, RVDTs, and VR half-bridge sensors

Dimensions (mm) 85.1 x 70.4 x 17.8

Typical Applications Automotive test instrumentation, factory automation