





REV. A
DCO 144146

COIL: @ 25°C
 RESISTANCE 100 OHMS $\pm 20\%$
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 3.5 VDC
 MUST RELEASE _____

ENVIRONMENT:
 VIBRATION 10 Hz TO 500 Hz @ 10 g's
 SHOCK 30 g's 6 MS. DURATION
 TEMPERATURE -55 $^\circ\text{C}$ TO +85 $^\circ\text{C}$
 NOTES: OPERATE TIME 6 MS MAX
RELEASE TIME 3 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 16JAN2006 CK. JERRY C. 1/17/06

CII Technologies™
 advanced control electronic solutions

CUST. C.I.I. STD.
 CUST. NO. _____ REV. _____

MW4S RELAY
 4 GHZ

MW4S-5AEG