

DIGITAL COMPONENT SENSOR DEVELOPMENT TOOLS



WIRELESS DEMO AND DEVELOPMENT KITS



Environmental Sensor Tag

Humidity, Temperature, Pressure

- 0 100% RH
- 300 to 1,200 mbar

Standard 2.4 GHz wireless communication

iOS 7.0+ Android™ 4.3+

Operating Temp. | 20°C to 85°C

Туре

Specifications

Communication

Interface Application



M5600

Pressure

- 50 15K psi
- Type G/S/C

Standard 2.4 GHz wireless communication

iOS 7.0+ Android™ 4.3+

-20°C to 85°C



U5600

Pressure

- 2 10K psi
- Type G/S/C/A

Standard 2.4 GHz wireless communication

iOS 7.0+ Android™ 4.3+

-20°C to 85°C

DIGITAL COMPONENT SENSOR DEVELOPMENT TOOLS



SHIELDS AND HATS



Arduino Weather Shield

Humidity, Temperature, Pressure Type

HTU21D, MS5637, MS8607, TSYS01*, TSD305

Specifications • 0 - 100% RH

- 20°C to 85°C
- 300 to 1,200 mbar

Arduino / Genuino

Communication Interface

Partner Board

Sensors



Raspberry Pi™ Sensors Weather Hat

Humidity, Temperature, Pressure

HTU21D, MS5637, TSYS01*, TSD305

- 0 100% RH
- 20°C to 85°C 300 to 1,200 mbar

Raspberry Pi^{TM}



PicTail Plus

Humidity, Temperature, Pressure

HTU21DF, MS5637, TSYS01*, MS8607

- 0 100% RH
- -20°C to 85°C
- 300 to 1,200 mbar

Microchip Explorer 16

WING BOARDS













	HTU21D	MS5637	MS8607	TSYS01*	TSYS02D*	KMA36(A)
Туре	Humidity	Pressure	Pressure, Temperature, Humidity	Temperature	Temperature	Angular Position
Specifications	• 0 to 100% RH • -40°C to 125°C • 3.3 to 5.5 V	• 10 to 2,000 mbar • -40°C to 85°C • 1.5 to 3.6 V	• 10 to 2,000 mbar • -40°C to 85°C • 0 to 100% RH • 1.5 to 3.6 V	• -40°C to 125°C • 2.2 to 3.6 V	• -40°C to 125°C • 1.5 to 3.6 V	• 0 to 360° • -25°C to 85°C • 2.9 to 6.0 V
Accuracy	±3% RH	±2 mbar	±3% RH, ±2 mbar, ±1.0°C	±0.1°C	±0.2°C	±0.1°
Communication Interface	I ² C	I ² C	I ² C	I ² C	I ² C	I ² C
Compatibility	Configured to operate with the Xplained Pro development platform	Configured to operate with the Xplained Pro development platform	Configured to operate with the Xplained Pro development platform	Configured to operate with the Xplained Pro development platform	Configured to operate with the Xplained Pro development platform	Configured to operate with the Xplained Pro development platform

DIGITAL COMPONENT SENSOR DEVELOPMENT TOOLS



PERIPHERAL MODULES

Digilent Pmod™













	A STATE OF THE STA					
	HTU21D	MS5637	MS8607	TSYS01*	TSYSO2D*	KMA36(A)
Туре	Humidity	Pressure	Pressure, Temperature, Humidity	Temperature	Temperature	Angular Position
Specifications	• 0 to 100% RH • -40°C to 125°C • 3.3 to 5.5 V	• 10 to 2,000 mbar • -40°C to 85°C • 1.5 to 3.6 V	• 10 to 2,000 mbar • -40°C to 85°C • 0 to 100% RH • 1.5 to 3.6 V	• -40°C to 125°C • 2.2 to 3.6 V	• -40°C to 125°C • 1.5 to 3.6 V	• 0° to 360° • -25°C to 85°C • 2.9 to 6.0 V
Accuracy	±3% RH	±2 mbar	±3% RH, ±2 mbar, ±1.0°C	±0.1°C	±0.2°C	±0.1°
Communication Interface	I ² C	I ² C	I ² C	I ² C	I ² C	I ² C
Compatibility	Development systems compatible with Digilent Pmod™ connections	Development systems compatible with Digilent Pmod™ connections	Development systems compatible with Digilent Pmod™ connections	Development systems compatible with Digilent Pmod™ connections	Development systems compatible with Digilent Pmod™ connections	Development systems compatible with Digilent Pmod™ connections







Туре Pressure

- 1.5 to 3.6 V

Accuracy

Communication Interface

Specifications

Compatibility

- 10 to 1,200 mbar
- -40°C to 85°C

±2 mbar

 I^2C

Development systems compatible with Digilent Pmod™ connections

MS5837

Pressure

- 10 to 2,000 mbar • -40°C to 85°C
- 1.5 to 3.6 V
- ±2 mbar

 I^2C

Development systems compatible with Digilent Pmod™ connections



MS5805

Pressure

- 10 to 2,000 mbar
- -40°C to 85°C • 1.8 to 3.6 V

±2 mbar

 I^2C

Development systems compatible with Digilent Pmod™ connections



TSD305

Temperature

- -10°C to +85°C
- 1.68 to 3.6 V

±1°C

 I^2C

Development systems compatible with Digilent Pmod™ connections

DIGITAL COMPONENT SENSOR DEVELOPMENT TOOLS



GROVE SYSTEM



KMA36

Angular Position Type

• 0 to 360° Specifications • -25°C to 85°C

• 5.0 V

±0.1° Accuracy Comm. Interface I²C

Compatibility

TSYSO1*

Temperature

• -40°C to 125°C

• 5.0 V

±0.1°C

 I^2C

Development platform compatible with grove systems



TSYSO2

Temperature

• -40°C to 125°C

• 5.0 V

±0.2°C

 I^2C

Development platform compatible with grove systems



MS5637

Pressure

• 10 to 2,000 mbar

• -40°C to 85°C

• 5.0 V

±2 mbar

I²C

Development platform compatible with grove systems



MS8607

Pressure, Temperature, Humidity

• 10 to 2,000 mbar

• -40°C to 85°C

• 0 to 100% RH

• 5.0 V

±3% RH, ±2 mbar, ±1.0°C

 I^2C

Development platform compatible with grove systems



Development platform

compatible with

grove systems

Humidity

• -40°C to 125°C

• 5.0 V

±3% RH

Compatibility

Communication

Specifications

Accuracy

Interface

Туре

HTU21D

• 0 to 100% RH

 I^2C

Development platform compatible with grove systems



MS5611

Pressure

• 10 to 1,200 mbar

• -40°C to 85°C

• 5.0 V

±2 mbar

 I^2C

Development platform compatible with grove systems



MS5837

Pressure

• 10 to 2,000 mbar

• -40°C to 85°C

• 5.0 V

±2 mbar

 I^2C

Development platform compatible with grove systems



MS5805

Pressure

• 10 to 2,000 mbar

• -40°C to 85°C

• 5.0 V

±2 mbar

 I^2C

Development platform compatible with grove systems

TSD305

Temperature

• -10°C to +85°C

• 5.0 V

±1°C

 I^2C

Development platform compatible with grove systems