



Automotive Parts > Automotive Connectors > Automotive Housings > GET .64 CONNECTOR SYSTEM, RECEPT AND TAB



Nominal Voltage Architecture: 12 V

Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: **6**

Sealable: **Yes**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

[All GET .64 Connector System, Recept and Tab \(62\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Board, Wire-to-Device, Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	6
Number of Positions	6
Number of Rows	1

Electrical Characteristics

--	--



Nominal Voltage Architecture	12 V
------------------------------	------

Body Features

Cable Exit Angle	180 °
Primary Product Color	Black
Connector & Keying Code	A

Contact Features

Contact Size	.64mm
Contact Type	Receptacle
Mating Tab Width	.64 mm[.025 in]

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	Yes
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 66 GF35
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	6.9 mm[.272 in]
Product Width	24.5 mm[.965 in]
Product Length	31.4 mm[1.236 in]
Connector Height	19.6 mm[.772 in]

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
Operating Temperature (Max)	125 °C[257 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

IP Rating	IP67
-----------	------

Packaging Features

--	--



Packaging Quantity	600
Packaging Method	Package

Other

Serviceable	Yes
Connector Position Assurance Capable	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in M-14370-1) Decamethylcyclopentasiloxane (D5) (.5% in 27519757557) Octamethylcyclotetrasiloxane (D4) (.5% in M-13361-1) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-G3353-T273
GET .64 CONNECTOR SYSTEM,
RECEPT AND TAB

Also in the Series | [Get .64 Connector System](#)

Automotive Headers(3)

Automotive Housings(86)

Automotive Signal & Power Connector
Housings(86)

Customers Also Bought

TE Part #144998-6
4P JPT CONNECTOR ASSY

TE Part #1612123-1
SQUIB FERRITE

TE Part #1612290-2
0.64 RCPT SEALED AU STRIP


TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING

TE Part #2035170-2
CONTACT,FEMALE, 0.64, 18AWG,CU

TE Part #316988-6
.040 II MLC PLUG ASSY 10P

TE Part #936397-5
2.8MM SLD 6P PLUG RETAINER YEL

TE Part #2465712-1
24POS,HYBRID,REC HSG ASSY,
UNSLD,TYPE-A



TE Part #2465714-1
30POS,0.5 SERIES,REC HSG ASSY,
UNSLD,A

Documents

Product Drawings

1X6 SEALED ASSY W/ CPA 6 CLSD

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1438153-3_H.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1438153-3_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1438153-3_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

GET 0.64 Interconnection System

English

Product Specifications

Application Specification

English