






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	14APR2017	DW	CW



NOTES / 注解:

- I. TECHNICAL CHARACTERISTICS / 技术参数:
- SHELL MATERIAL / 主体材料 : NICKEL PLATED BRASS / 铜镀镍
 - SEAL MATERIAL / 密封材料: RUBBER, BLACK
 - PINCH RING MATERIAL / 夹紧件材料: NYLON, GREY
 - OPERATION TEMPERATURE / 工作温度: -40°C - +100°C
 - PROTECTION DEGREE / 防护等级: IP68
 - WIRE RANGE / 夹线范围: 15-21 mm

T3707320113-000	DLX-32-MTC (15~21) 电磁屏蔽金属接头 M32 (15~21)
PART NUMBER 料 号	PART DESCRIPTION 描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14APR2017 DAVID WANG		 TE Connectivity											
		CHK 14APR2017 CHRIS WANG													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DLX-32-MTC (15~21)											
		APVD 14APR2017 XIANG XU		SIZE A3											
		PRODUCT SPEC -						CAGE CODE -							
		APPLICATION SPEC -										DRAWING NO C-T3707320113000			
		WEIGHT -													
0 PLC ±-		SCALE 1:1													
1 PLC ±-						SHEET 1 OF 1									
2 PLC ±-										REV A					
3 PLC ±-															
4 PLC ±-															
ANGLES ±-															
MATERIAL - -		FINISH - -													
CUSTOMER DRAWING															