

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	A87085-000	MV-064064-25-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084






Quantity per roll: 25.000 PCs

Labels across: 12

Winding: outside

length of roll: 19,85 m



LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity		
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,12]	DIMENSIONS mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED	CHK S. Iser / 01.04.2020 DATE	APVD S. Iser / 01.04.2020 DATE	Name		
	ADHESIVE	LABEL WIDTH:	±0,3 [0,12]			Name				
	LINER	WEB WIDTH:	±0,8 [0,31]			PRODUCT SPEC DATE	Tamper-proof Label Size „064064“			
		VERTICAL REPEAT:	±0,8 [0,31]*			APPLICATION SPEC DATE	WEIGHT MV: 0,004 g		SIZE A3	CAGE CODE C2290
		HORIZONTAL REPEAT:	±0,8 [0,31]*			MATERIAL SEE TABLE	FINISH	DRAWING NO C-TAMPERPROOF		RESTRICTED TO
		PRINT POSITIONING:	±0,8 [0,31]*					CUSTOMER DRAWING		SHEET 1 of 1
		LEFT MARGIN:	±0,4 [0,16]					REV A1		
		QUANTITY:	-0% +2%							
			*NON ACCUMULATING							

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

TAMPER-PROOF SERIES