

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
TN	D87328-000	TN-127111-10-9	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll: 10.000 PCs

Labels across: 5

Winding: outside

length of roll: 31,8 m








approx. Ø 114 [4.488]

Ø 76,2 [3,00]

TAMPER-PROOF SERIES

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity	
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,12]	 DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	CHK S. Iser / 01.04.2020 DATE	 Name Tamper-prrof Label Size „127111“			
	ADHESIVE	LABEL WIDTH:	±0,3 [0,12]		APVD S. Iser / 01.04.2020 DATE				
	LINER	WEB WIDTH:	±0,8 [0,31]		PRODUCT SPEC DATE				
		VERTICAL REPEAT:	±0,8 [0,31]*		APPLICATION SPEC DATE				
		HORIZONTAL REPEAT:	±0,8 [0,31]*	WEIGHT T1K: 0,014 g T2K: 0,021g	SIZE A3	CAGE CODE C2290	DRAWING NO C-TAMPER-PROOF	RESTRICTED TO	
		PRINT POSITIONING:	±0,8 [0,31]*		CUSTOMER DRAWING				
		LEFT MARGIN:	±0,4 [0,16]		SHEET 1 of 1				
		QUANTITY:	-0% +2%		REV A1				
		*NON ACCUMULATING							