



DESCRIPTION	TE Part No.	Conductor AWG/MCM	Dimensions in Inch (mm)			Color Code	Die Index No.	No. of Crimp per side
			ØA (Barrel ID)	ØC (Barrel OD)	J (Total Length)			
TCSS-8-U	EN3750-630	8	0.18 (4.58)	0.28 (7.12)	1.0 (25.4)	Red	49	1
TCSS-6-U	EN3750-631	6	0.20 (5.0)	0.3 (7.62)	1.75 (44.45)	Blue	7	1
TCSS-4-U	EN3750-632	4	0.25 (6.35)	0.34 (8.64)	1.75 (44.45)	Gray	8	1
TCSS-2-U	EN3750-633	2	0.31 (7.87)	0.42 (10.67)	2.0 (50.8)	Brown	9	1
TCSS-1-U	EN3750-634	1	0.36 (9.14)	0.47 (11.94)	2.06 (52.32)	Green	11	1
TCSS-1/0-U	EN3750-635	1/0	0.4 (10.16)	0.52 (13.21)	2.08 (52.83)	Pink	12	1
TCSS-2/0-U	EN3750-636	2/0	0.45 (11.43)	0.57 (14.48)	2.17 (55.12)	Black	13	1
TCSS-3/0-U	EN3750-637	3/0	0.49 (12.45)	0.62 (15.75)	2.3 (58.42)	Orange	14	1
TCSS-4/0-U	EN3750-638	4/0	0.56 (14.22)	0.7 (17.78)	2.32 (58.93)	Purple	15	1
TCSS-250-U	EN3750-639	250	0.6 (15.24)	0.76 (19.3)	2.46 (62.48)	Yellow	16	1
TCSS-300-U	EN3750-640	300	0.65 (16.51)	0.82 (20.83)	2.47 (62.74)	White	17	2
TCSS-350-U	EN3750-641	350	0.7 (17.78)	0.88 (22.35)	2.6 (66.04)	Red	18	2
TCSS-400-U	EN3750-642	400	0.76 (19.3)	0.96 (24.38)	2.74 (69.6)	Blue	19	2
TCSS-500-U	EN3750-643	500	0.83 (21.08)	1.07 (27.18)	3.15 (80.01)	Brown	20	2
TCSS-600-U	EN3750-644	600	0.92 (23.37)	1.19 (30.23)	3.22 (81.79)	Green	22	2
TCSS-750-U	EN3750-645	750	1.03 (26.16)	1.31 (33.27)	3.72 (94.49)	Black	24	2
TCSS-1000-U	EN3750-646	1000	1.17 (29.72)	1.51 (38.35)	4.28 (108.71)	White	27	3

NOTE :-

- 1) FINISH = ELECTRO TIN PLATED
- 2) FOR COPPER CONDUCTOR ONLY
- 3) INSERT ONE INSTALLATION INSTRUCTION IN EACH STANDARD PACKAGE

NO.	REV.	DESCRIPTION	DATE	DRAWN	CHECKED
SCALE :		MATERIAL :-	DATE	SIGN	NAME
		ETP-COPPER	03/12/18		V.B.
		Copper Compression Slices Standard Barrel	03/12/18		A.V.
			03/12/18		S.M.
TOLERANCE	WEIGHT:	PARTNO / PCN NO:		A4	
- DIMENSION	-		DRAWING. NO.		REV
- HOLES	ALL DIMENSION ARE IN INCH (MM)		TCSS-U		00
- ANGLES	-				