




EMI & EMC Solutions > IEC Inlets > Inlet Filters > FN9262 Power Entry Module with EMC Filter – High-Performance Fused Solution



Filtering Requirements: **Filtered**
Current Rating (Max): **4 A**
Output Termination Type: **Litz Wire**
Pollution Degree: **PD2**
IP Rating: **IP40**

[All FN9262 Power Entry Module with EMC Filter – High-Performance Fused Solution \(55\)](#)

Features

Product Type Features

Filter Type	Power Entry Module
Level Of Filtering	Inductor & Capacitor
Filtering Requirements	Filtered
Output Termination Type	Litz Wire

Electrical Characteristics

Capacitance Cy1	2.2
Inductance L1	7 μ H
Capacitance Cx1	.22
Overvoltage Category	II
Current Rating (Max)	4 A
Leakage Current (Max) (120VAC, 60Hz)	310 μ A
Leakage Current (Max) (250VAC, 50Hz)	180 μ A



Body Features

Product Weight	55 g[1.94 oz]
----------------	---------------

Dimensions

Product Width	35 mm[1.37 in]
Product Length	34 mm[1.33 in]
Product Height	46.5 mm[1.83 in]

Operation/Application

Cooling Method	Natural Convection
----------------	--------------------

Industry Standards

Certified To	CSA 22.2 No. 8-13, GB/T 15287, GB/T 15288, IEC/EN 60939-3, UL 60939-3
Pollution Degree	PD2
IP Rating	IP40
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the



product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # CAT-PF6-LO
IL 13, IL 13 P, IL 19

Also in the Series | Schaffner FN9262

Inlet Filters(55)

Medical Inlet Filters(55)

Customers Also Bought

TE Part #9543-005M-D-C-3-S
5MBAR ULTRA-LOW SENSOR

TE Part #1622395-1
LR1 1% 240K

TE Part #1744428-2
3.96 EP HDR ASSY 2P R/A, GW

TE Part #1744429-2
3.96 EP HDR ASSY 2P W/PEGS, GW

TE Part #2-2176230-6
3522 100R 5% 3W

TE Part #9-2176422-5
TLRP 2512 3.0W R120 1% 75PPM 4K RL

TE Part #9-2176422-6
TLRP 2512 3.0W R150 1% 75PPM 4K RL

TE Part #4-2176613-7
EP 4W (SS) 82R 5%



Documents

Product Drawings

FN9262S-4-07

English

Datasheets & Catalog Pages

Power Entry Module with EMC Filter FN9262

English

Agency Approvals

CB_SE-93906M2

English