



# ALUMINUM SHEAR BOLT SPLICE ASBS CONNECTORS

## #2 AWG COMPACT TO 1000 kcmil CONCENTRIC

### KEY FEATURES

- Heavy-duty design made of high strength, tin-plated aluminum alloy
- Range taking, compact and smooth body design
- Dual rated for aluminum and copper conductors
- Provides long service life under normal operating conditions with reserve capacity for emergency loading conditions
- Pre-engineered design for perfect fit in medium voltage cable accessories up to 35 kV
- TE's ASBS are UL listed and CSA certified
- No crimp tooling or dies required for installation

TE Connectivity's (TE) Aluminum Shear Bolt Splice ASBS connectors are range taking mechanical connectors which accommodate a wide range of aluminum and copper conductors from #2 AWG compact stranded to 1000 kcmil concentric stranded Class B to reduce inventory and prevent accidental use of wrong conductor. The primary application of aluminum shear bolt connectors is for underground splices up to 35 kV.

TE's ASBS connectors are ideally suited for aluminum to aluminum, aluminum to copper and copper to copper applications making them the universal connector solution. The only tool required to install the connector is a standard ratchet wrench with the appropriate sized hexagonal sockets.

The connectors design incorporates shear bolt heads, which ensures that the correct torque is applied to each bolt and consequently the optimal contact force is generated to minimize connection resistance. A holding tool is recommended to avoid core bending of conductors and can be ordered from TE (#IT-1000-019). The solid center stop (available on all sizes) inside the connectors ensure proper conductor positioning and eliminates oil leakage when connecting oil impregnated conductors.

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**

## Aluminum Shear Bolt Splice ASBS Connectors



### PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (MM)

Catalog Number	Part Number	Conductor Range		O.D. Range	Length	Connector O.D.	Number of Bolts	Socket Size
		Compact stranded	Standard stranded					
Aluminum Shear Bolt Splice ASBS Connectors								
ASBS-2-3/0	CL8618-000	2 AWG	3/0 AWG	.268-.470 (6.8-11.9)	2.5 (65)	.95 (24)	2	1/2 (13)
ASBS-2-350	694472-000	2 AWG	350 kcmil	.268-.681 (6.8-17.3)	3.9 (100)	1.22 (31)	4	11/16 (17)
ASBS-3/0-500	CL8619-000	3/0 AWG	500 kcmil	.423-.813 (10.7-20.6)	4.9 (125)	1.3 (34)	4	3/4 (19)
ASBS-3/0-500-S	CU2713-000	3/0 AWG	500 kcmil	.423-.813 (10.7-20.6)	4.9 (125)	1.3 (34)	4	3/4 (19)
ASBS-350-750	CL7947-000	350 kcmil	750 kcmil	.616-.998 (15.6-25.3)	6.7 (170)	1.67 (42.5)	6	7/8 (22)
ASBS-500-750	E89931-000	500 kcmil	750 kcmil	.736-.998 (18.7-25.3)	6.0 (152)	1.52 (39)	6	3/4 (19)
ASBS-600-1000	C68131-000	600 kcmil	1000 kcmil	.813-1.152 (20.6-29.2)	8.0 (203)	1.75 (44.4)	6	7/8 (22)

### PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (MM)

Catalog Number	Part Number	Conductor Range	O.D. Range	Length	Connector O.D.	Number of Bolts	Socket Size	Insert Used
<b>Aluminum Shear Bolt Splice ASBS Connectors UL/CSA Listed</b>								
ASBS-2-U	1974155-1	2 AWG compact to 2 AWG concentric	0.268-0.292 (6.81-7.42)	2.6 (65)	0.94 (24)	2	1/2 (13)	Yes**
ASBS-2-4/0-U	1974138-1	2 AWG compact to 4/0 AWG concentric	0.268-0.528 (6.81-13.41)	3.9 (100)	1.22 (31)	4	11/16 (17)	No
ASBS-2-4/0/250-350-U	2182352-1	Side #1: 2 AWG compact to 4/0 AWG concentric Side #2: 250 compact to 350 kcmil concentric	Side #1: 0.268-0.528 (6.81-13.41) Side #2: 0.520-0.681 (13.21-17.30)	3.9 (100)	1.22 (31)	4	11/16 (17)	No
ASBS-250-350-U	1974139-1	250 compact to 350 kcmil concentric	0.520-0.681 (13.21-17.30)	3.9 (100)	1.22 (31)	4	11/16 (17)	No
ASBR-250-350/350-500-U	2182769-1	Side #1: 250 compact to 350 kcmil concentric Side #2: 350 compact to 500 kcmil concentric	Side #1: 0.520-0.681 (13.21-17.30) Side #2: 0.616-0.813 (15.65-20.65)	5.4 (138)	1.3 (33) / 1.67 (42.5)	5	11/16 (17) / 7/8 (22)	No
ASBR-250-350/600-750-U	2182770-1	Side #1: 250 compact to 350 kcmil concentric Side #2: 600 kcmil compact to 750 kcmil concentric	Side #1: 0.520-0.681 (13.21-17.30) Side #2: 0.813-0.998 (20.65-25.35)	5.4 (138)	1.3 (33) / 1.67 (42.5)	5	11/16 (17) / 7/8 (22)	No
ASBS-350-500-U	1974144-1	350 compact to 500 kcmil concentric	0.616-0.813 (15.65-20.65)	6.7 (170)	1.67 (42.5)	6	7/8 (22)	Yes**
ASBR-350-500/600-750-U	1974146-1	Side #1: 350 kcmil compact to 500 kcmil concentric Side #2: 600 kcmil compact to 750 kcmil concentric	Side #1: 0.616-0.813 (15.65-20.65) Side #2: 0.813-0.998 (20.65-25.35)	6.7 (170)	1.67 (42.5)	6	7/8 (22)	Yes**
ASBR-350-500/1000-U	2182732-1	Side #1: 350 kcmil compact to 500 kcmil concentric Side #2: 1000 kcmil compact to 1000 kcmil concentric	Side #1: 0.616-0.813 (15.65-20.65) Side #2: 1.060-1.152 (26.92-29.26)	7.4 (189)	1.67 (42.5) / 1.75 (44.5)	6	7/8 (22)	Yes**
ASBS-600-750-U	1974145-1	600 kcmil compact to 750 kcmil concentric	0.813-0.998 (20.65-25.35)	6.7 (170)	1.67 (42.5)	6	7/8 (22)	No
ASBR-600-750/1000-U	2182734-1	Side #1: 600 kcmil compact to 750 kcmil concentric Side #2: 1000 kcmil compact to 1000 kcmil concentric	Side #1: 0.813-0.998 (20.65-25.35) Side #2: 1.060-1.152 (26.92-29.26)	7.4 (189)	1.67 (42.5) / 1.75 (44.5)	6	7/8 (22)	No
ASBS-1000-U	1974151-1	1000 kcmil compact to 1000 kcmil concentric	1.060-1.152 (26.92-29.26)	8.0 (203)	1.75 (44.5)	6	7/8 (22)	No

\*\* DO NOT remove insert. Please contact your TE representative for conductor sizes or types not listed.

#### FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+ 7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015

[te.com/energy](http://te.com/energy)

© 2018 TE Connectivity. All Rights Reserved. EPP-2624-10/18-EN

Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.