

## MECHANICAL CONNECTORS AND REPAIR SLEEVES BSM

FOR LOW AND MEDIUM VOLTAGE APPLICATION UP TO 42 kV

### KEY FEATURES

- Wide application range
- Compact design
- Can be used with almost every type of conductor and material
- Torque-controlled shear head bolts guarantee an excellent electrical contact
- Easy installation with standard socket spanner
- Pre-engineered design for perfect fit in medium voltage cable accessories up to 42 kV
- Tested according to IEC 61238-1 class A

TE Connectivity's (TE) mechanical connectors and repair sleeves BSM are designed for use in low and medium voltage applications. Three sizes of BSM connectors cover conductor sizes ranging from 25 mm<sup>2</sup> to 400 mm<sup>2</sup>. Our connectors consist of a tin-plated body, shear bolt heads and inserts for small conductor sizes.

Made of special aluminium alloy, these contact bolts are double shear bolt heads with hexagon heads. The bolts are treated with a highly lubricating agent. Contact bolts are irremovable once their heads have been sheared off. The lug body is made of a high-tensile, tin-plated aluminium alloy. The internal surface of the conductor holes are grooved.

The connectors are chamfered at the edges and available with or without oil barrier (as blocked and unblocked types) depending on the application requirements. The bolted fitting featured herein was developed specifically for use in medium voltage cable accessories up to 42 kV. They may also be used in the 1 kV range.


Before using mechanical connectors in cable accessories, confirm that they are suitable for the given application and if necessary consult our experts.

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**





## PRODUCT SELECTION INFORMATION



Description	Cross Sectional Range (mm²)	Blocked	Dimensions (mm)							Contact Bolts Quantity	Head Size AF (mm)		
			L1	L2	D1	D2	D3	D4					
Mechanical Connectors													
BSMB-10/35	10 - 35	yes	45	20	19	8,5	-	-		2		10	
BSM-25/95	25 - 95	yes	65	30	24	12,8	-	-		2		13	
BSM-25/95-U	25 - 95	no	65	-	24	12,8	-	-		2		13	
BSMB-35/150	35 - 150	yes	80	35	28	15,8	-	-		2		17	
BSMU-35/150	35 - 150	no	80	-	28	15,8	-	-		2		17	
BSM-95/240	95 - 240	yes	125	60	33	20	-	-		4		19	
BSM-95/240-U	95 - 240	no	125	-	33	20	-	-		4		19	
BSMB-95/240-34	95 - 240	yes	125	60	34	22	-	-		4		19	
BSMB-120/300	120 - 300	yes	140	65	37	24	-	-		4		22	
BSMU-120/300	120 - 300	no	140	-	37	24	-	-		4		22	
BSMB-150/400	150 - 400	yes	170	80	42	25,5	-	-		6		13	
BSMU-150/400	150 - 400	no	170	-	42	25,5	-	-		6		13	
BSMB-500mk2	500	yes	160	70	46	30	-	-		6		13	
BSMB-630mk2	630	yes	160	70	50	33	-	-		6		13	
BSMB-800mk2	800	yes	180	85	56	36	-	-		8		13	
BSMB-1000	1000	yes	180	85	60	40	-	-		8		13	
Reduction Connectors	Side 1	Side 2								Side 1	Side 2	Side 1	Side 2
BSMB 25/95-95/240	25 - 95	95 - 240	yes	125	60	24	12,8	33	20	1	2	13	19
BSMB 95/240-185/400	95 - 240	185 - 400	yes	170	80	33	20	42	25,5	2	3	19	22
BSMB 185/400-500	185 - 400	500	yes	190	90	42	25,5	46	30	3	3	22	27
BSMB 185/400-630	185 - 400	630	yes	200	95	42	25,5	50	33	3	3	22	27
BSMB 500-630mk2	500	630	yes	160	70	46	30	50	33	3	3	13	13
BSMB 500-800	500	800	yes	180	85	46	30	56	36	3	4	13	13
BSMB 630-800	630	800	yes	180	85	50	33	56	36	3	4	13	13
BSMB 630-1000	630	1000	yes	180	85	50	33	60	40	3	4	13	13
BSMB 800-1000	800	1000	yes	180	85	56	36	60	40	3	4	13	13
Split Connectors										Contact	Central	Head Size AF Contact AF Central	
BSMV-120/300	120 - 300	yes	160	65	37	24	4	-		4	1	22	21
BSMV-185/400	185 - 400	yes	190	80	42	25,5	6	-		6	1	22	19
Mechanical Repair Sleeves													
BSM-25/95-U-L440	25 - 95	no	440	30	24	12,8	-	-		2		13	
BSM-95/240-U-L440	95 - 240	no	440	60	33	20	-	-		4		19	
BSMU-95/240-34-L440	95 - 240	no	440	60	34	22	-	-		4		19	
BSMU-120/300-L440	120 - 300	no	440	65	37	24	-	-		4		22	
BSM-185/400-U-L440	185 - 400	no	440	80	42	25,5	-	-		6		22	
BSMU-500-L440	500	no	440	90	46	30	-	-		6		27	




Mechanical Repair Connector



Mechanical Connector



Reduction Connector



Split Connector

### FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 89 6089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+ 7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015

[te.com/energy](http://te.com/energy)

© 2018 TE Connectivity. All Rights Reserved. EPP-2287-DDS-10/18-EN

TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.