

A2L REFRIGERANT SENSOR FROM TE CONNECTIVITY

UL 60335-2-40 COMPLIANT A2L REFRIGERANT SENSOR FOR R-454B AND R-32 LEAK DETECTION

TE Connectivity's (TE) A2L refrigerant sensor module is designed to meet or exceed all UL and CSA 60335-2-40 Annex LL requirements, supporting leak hazard mitigation without the need for field calibration. The module uses thermal conductivity sensing technology to detect R-454B and R-32 gases at 10% LFL* with $\pm 2.5\%$ accuracy and a 15s response time. With integrated temperature and humidity sensors for environmental compensation, the module can operate at temperatures ranging from -40°C to $+95^{\circ}\text{C}$ and up to 100% relative humidity. The sensor is resistant to poisoning by typical interference gases and uses automated self-calibration (ASC) to maintain performance for up to 15 years without recalibration.



PERFORMANCE

- Gas Type(s): R-454B, R-32
- Detection Range: 0%-100% LFL*
- Detection Threshold: 10% LFL*
- Detection Accuracy: $\pm 2.5\%$ LFL*
- Response Time (typ.): 15s, (max 30s)
- Warm-Up Time : 5s
- Operating Temp: -40°C to $+95^{\circ}\text{C}$
- Operating Humidity: 0%-100%RH
- Lifetime: up to 15 years

ELECTRICAL

- Supply Voltage: 5V - 17V DC
- Max Current: 100mA
- Power Consumption: 0.5W
- Communication: RS485 Modbus RTU

MECHANICAL

- Approx. Dimensions: 52 mm x 35 mm x 14 mm
- I/O: 4 Pin Sealed Signal Double Lock Connector
- Ingress Protection: IP54

STANDARDS & SPECIFICATIONS

- ETL Certified: Conforms to UL & CSA 60335-2-40 (Annex LL)
- Application Specification: [114-161909](#)

KEY FEATURES

- Thermal conductivity gas sensor with temperature and humidity compensation
- RS485 Modbus RTU communication protocol with Pulse Width Modulation (PWM) or Universal Asynchronous Receiver-Transmitter (UART) options
- Locking connector interface supporting customized harnessing (optional IP67 connection)
- Easy installation with compact enclosure design and multiple mounting bracket options
- Enclosed module meeting IP54 and salt spray corrosion testing standards
- Integrated anti-condensation heater
- ETL certified to meet UL and CSA 60335-2-40 Annex LL standards

APPLICATIONS



HVAC Equipment



Air-conditioner



Water Heater




Appliances

*LFL = lower flammability limit

A2L REFRIGERANT SENSOR MODULE

Gas	Bracket Style	Part Number
R454-B, R-32 ¹	1-Hole Mount w/ Alignment Pins	2539600-1

ENCLOSURE WITH BRACKET ¹



2539600-1 SHOWN

²Additional bracketing options with alternate mounting configurations are available upon request

MATING CONNECTOR ACCESSORIES

Part Description	Part Number
Sealed Signal Double Lock Plug Housing	2443729-4
Receptacle Terminal	2321921-1
Perimeter Seal	2321920-4
Rear Wire Seal	2321922-4

Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need. Visit te.com/support to chat with a Product Information Specialist.

TE Connectivity
Connected Living Solutions

te.com/a2l-refrigerant-sensor

TE, TE Connectivity, TE connectivity (logo) and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

© 2026 TE Connectivity. All Rights Reserved.

05-26