




Connectors > Power Connectors > Circular Power > Circular Power Connectors



Connector Product Type: **Lead Assembly**
Operating Voltage: **15000 VDC**
Wire Size: **16 AWG**
Connector System: **Wire-to-Wire**
Number of Positions: **1**

Features

Product Type Features

Connector Product Type	Lead Assembly
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Operating Voltage	15000 VDC
-------------------	-----------

Body Features

Positive Stop Ferrule	With
-----------------------	------

Contact Features

Contact Type	Socket
Contact Protection	Without

Termination Features

Termination Method to Wire & Cable	Pre-Terminated to Cable
------------------------------------	-------------------------

Mechanical Attachment

Mating Alignment	With
------------------	------



Dimensions

Wire Size	16 AWG
Assembly Length	508 mm[20 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
----------	----

Packaging Features

Packaging Quantity	20
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (2% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Also in the Series | [LGH SGL](#)




[Circular Power Connectors\(75\)](#)

Customers Also Bought




TE Part #823667-000
[301A022-3/42-0](#)



TE Part #34227
[BUDGET BUTT SPLICE 16-14](#)



TE Part #5-830178-1
[RECEPTACLE](#)



TE Part #860425-1
[LGH 1/2 SGL MLD END](#)



TE Part #862549-8
[LGH-1 LEAD SGL END POS STOP](#)



TE Part #1617142-1
[MSW-12 = MS T05 RELAY](#)



TE Part #3-1393117-2
[KUP-11A55-6=KU](#)



TE Part #221111-1
[JACK,PCB,VERTICAL,SERIES SMB](#)



TE Part #414946-1
[PLUG ASSY,STR,SMB](#)



TE Part #6-331693-2
[BNC BHD JACK PTFE](#)

Documents

[Product Drawings](#)

[LGH-1/2L SGL MOLDED END LEAD](#)

English

[CAD Files](#)

[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_1-863534-1_K.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-863534-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-863534-1_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1308940_Sec9_lghlead](#)

English