

BUCHANAN WIREMATE ITB RELEASABLE POKE-IN CONNECTORS

Inverted Thru-Board (ITB) connectors join the BUCHANAN WireMate connector family from TE Connectivity (TE), specially designed for use in linear and circular LED modules found in all sorts of commercial and industrial lighting systems. The headers help enable power delivery from the underside of the PCB and LED arrays, helping eliminate top-surface wire management issues. With their easy-to-use poke-in and wire release features, the connectors help shorten installation time and provide extra flexibility for reuse and wire replacement. The reduced profile of the connector takes only 2mm in height above the PCB top surface while horizontal wire insertion helps minimize space usage beneath the PCB. The connectors are modular in design, available for up to five wire connections and in different colors to help installers minimize mistakes when inserting wires. The connectors conform to the UL 1977 standard for component connectors for use in data, signal, control and power applications.

BENEFITS

- Reliable poke-in technology (no wire crimping) for fast and easy termination
- Inverted Thru-Board (ITB) application helps reduce profile for good lighting effect
- Wire release feature helps enable easy re-work and robust design of release mechanism helps prevent damage during wire assembly and rework
- Space saving low profile design
- Lower inventory and production costs with higher connection variations supported by a side by side stackable design on 4mm spacing

KEY FEATURES

- Inverted Thru-Board (ITB) wire to board connection with horizontal wire insertion
- Wire poke-in design with strong wire retention
- Wire release feature for wire replacement
- Applicable for Surface Mount Technology soldering process
- Applicable wire size: 18-22AWG
- Modular housing design for multi-color combinations

APPLICATIONS



Commercial Lighting



Office Lighting



Industrial Lighting

BUCHANAN WIREMATE ITB RELEASABLE POKE-IN CONNECTORS

ELECTRICAL

- Voltage rating: 320V Max.
- Current: 6A for 18AWG, 5A for 20AWG & 22AWG

MECHANICAL

- Pitch: 4.00mm & 6.5mm
- 2.0mm max height above the PCB surface
- Poke-in structure for good wire fix function
- Wire releasable


MATERIALS

- Housing: UL 94 V0 high temperature resistant thermoplastic
- Contact: Copper Alloy with Tin plating

STANDARDS & SPECIFICATIONS

- Product Specification: [108-137311](#)
- Application Specification: [114-137311](#)
- UL1977

PART NUMBERS

Positions	Pitch [mm]	PN	Description	Product Image
1	4.0	2834334-1	4.0 Pitch With Cap ITB_1P_WHITE	
2	4.0	2834334-2	4.0 Pitch With Cap ITB_2P_WHITE	
2	4.0	8-2834334-2	4.0 Pitch With Cap, ITB_2P_WHITE/BLACK	
3	4.0	2834334-3	4.0 Pitch With Cap, ITB_3P_WHITE	
3	4.0	3-2834334-3	4.0 Pitch With Cap, ITB_3P_WHITE/BLACK/RED	
1	6.5	1-2834331-1	6.5 Pitch With Cap ITB_1P_WHITE	
2	6.5	1-2834331-2	6.5 Pitch With Cap ITB_2P_WHITE	

BUCHANAN WireMate connectors also offer standard modular poke-in series (x-2834006-x), please go to [te.com](#) for details.

Note:

1. BUCHANAN WireMate Inverted Thru-Board (ITB) Releasable Poke-In Series offer other color combinations, please contact your TE sales person for inquiry.
2. A P/N set without a protective cap is available for the Inverted Thru-Board (ITB) releasable Poke-in Series, please contact your TE sales person for inquiry.

BUCHANAN WIREMATE ITB RELEASABLE POKE-IN CONNECTORS

Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.
Visit te.com/support to chat with a Product Information Specialist.

te.com/buchanan-wire-mate-connectors

BUCHANAN WireMate, TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2025 TE Connectivity. All Rights Reserved.

04/25
