

DEUTSCH TERMINAL TO OCEAN APPLICATOR CROSS REFERENCE GUIDE

FROM TE CONNECTIVITY

Deutsch Terminals/OCEAN Applicators (Applicator Family 1 for size 16 AWG)

Deutsch P/N (Pin)	TE P/N (Pin)	Deutsch P/N (Socket)	TE P/N (Socket)	Terminal Insulation Range	Applicator P/N Conversion P/N*	Wire Crimp Width	Wire Crimper P/N	Insulation Range O.D.	Insulation Crimp Width	Insulation Crimper P/N	Anvil P/N	Terminal Specification									
1060-14-0122	286505-1	1062-14-0122	286506-1	2.41 - 3.81 mm (.095 - .150 IN)	2266100 7-2266100-8	2.29 mm "F" (.090 IN)	2-1633713-6 (6°)	3.05 mm - 3.81 mm (.120 - .150 IN)	3.20mm "O" (.126 IN)	1803019-3	1803293-1	114-151000									
1060-14-0144	286505-2	1062-14-0144	286506-2																		
1060-14-0177	286505-3	1062-14-0177	286506-3																		
		AT62-14-0122	286506-7																		
1060-14-1077	286505-5	1062-14-1077	286506-5	2.41 - 3.81 mm (.095 - .150 IN)	2266101 7-2266101-8	2.29 mm "F" (.090 IN)	2-1633713-6 (6°)	2.67 mm - 3.02 mm (.105 - .119 IN)	2.79mm "O" (.110 IN)	1803019-4	1803293-2	114-151000									
1060-14-1088	286505-6	1062-14-1088	286506-6																		
1060-14-0122	286505-1	1062-14-0122	286506-1																		
1060-14-0144	286505-2	1062-14-0144	286506-2																		
1060-14-0177	286505-3	1062-14-0177	286506-3																		
		AT62-14-0122	286506-7																		
1060-14-1077	286505-5	1062-14-1077	286506-5																		
1060-14-1088	286505-6	1062-14-1088	286506-6																		
1060-16-0122	286503-1	1062-16-0122	286504-1																		
1060-16-0144	286503-2	1062-16-0144	286504-2																		
1060-16-0177	286503-3	1062-16-0177	286504-3																		
1060-16-0722	286503-7	1062-16-0722	286504-7																		
1060-16-0744	286503-8	1062-16-0744	286504-8																		
1060-16-0777	286503-9	1062-16-0777	286504-9																		
1060-16-0977	1-286503-1	1062-16-0977	1-286504-1																		
1060-16-0988	1-286503-2	1062-16-0988	1-286504-2																		
1060-16-0122	286503-1	1062-16-0122	286504-1	1.91 - 3.56 mm (.075 - .140 IN)	2266102 7-2266102-8	2.29 mm "F" (.090 IN)	2-1633713-6 (6°)	2.26 mm - 2.64 mm (.089 - .104 IN)	2.29mm "O" (.090 IN)	1803019-5	1803293-3	114-151000									
1060-16-0144	286503-2	1062-16-0144	286504-2																		
1060-16-0177	286503-3	1062-16-0177	286504-3																		
1060-16-0722	286503-7	1062-16-0722	286504-7																		
1060-16-0744	286503-8	1062-16-0744	286504-8																		
1060-16-0777	286503-9	1062-16-0777	286504-9																		
1060-16-0977	1-286503-1	1062-16-0977	1-286504-1																		
1060-16-0988	1-286503-2	1062-16-0988	1-286504-2																		
1060-16-0122	286503-1	1062-16-0122	286504-1										1.91 - 3.56 mm (.075 - .140 IN)	2266103 7-2266103-8	2.29 mm "F" (.090 IN)	2-1633713-6 (6°)	1.93 mm - 2.24 mm (.076 - .088 IN)	2.03mm "O" (.080 IN)	1803019-6	1803293-4	114-151000
1060-16-0144	286503-2	1062-16-0144	286504-2																		
1060-16-0177	286503-3	1062-16-0177	286504-3																		
1060-16-0722	286503-7	1062-16-0722	286504-7																		
1060-16-0744	286503-8	1062-16-0744	286504-8																		
1060-16-0777	286503-9	1062-16-0777	286504-9																		
1060-16-0977	1-286503-1	1062-16-0977	1-286504-1	1.91 - 3.56 mm (.075 - .140 IN)	"2266104 7-2266104-8"	2.29 mm "F" (.090 IN)	2-1633713-6 (6°)	1.60mm - 1.91mm (.063 - .075)	"1.73mm "O" (.068 IN)"	1803019-7	1803293-5	114-151000									
1060-16-0122	286503-1	1062-16-0122	286504-1																		
1060-16-0144	286503-2	1062-16-0144	286504-2																		
1060-16-0177	286503-3	1062-16-0177	286504-3																		
1060-16-0722	286503-7	1062-16-0722	286504-7																		
1060-16-0744	286503-8	1062-16-0744	286504-8																		
1060-16-0777	286503-9	1062-16-0777	286504-9																		
1060-16-0977	1-286503-1	1062-16-0977	1-286504-1																		
1060-16-0988	1-286503-2	1062-16-0988	1-286504-2																		

Deutsch Terminals/OCEAN Applicators (Applicator Family 2 for size 16 AWG)

1060-16-0622	286503-4	1062-16-0622	286504-4	1.40 - 2.10 mm (.055 - .083 IN) Matches Terminal Drawing	2266110 7-2266110-8	1.88 mm "F" (.074 IN)	4-1633713-1 (6°)	1.68mm - 2.39mm (.066 - .094 IN)	1.73mm "O" (.068 IN)	1803019-7	1803293-6	114-151000
1060-16-0644	286503-5	1062-16-0644	286504-5									
1060-16-0677	1-286503-3	1062-16-0677	1-286504-4									
1060-16-0688	286503-6	1062-16-0688	286504-6									
1060-16-0622	286503-4	1062-16-0622	286504-4	1.40 - 2.10 mm (.055 - .083 IN) Matches Terminal Drawing	2266111 7-2266111-8	1.88 mm "F" (.074 IN)	4-1633713-1 (6°)	1.27mm - 1.65mm (.050 - .065 IN)	1.32mm "O" (.052 IN)	1803019-8	1803293-7	114-151000
1060-16-0644	286503-5	1062-16-0644	286504-5									
1060-16-0677	1-286503-3	1062-16-0677	1-286504-4									
1060-16-0688	286503-6	1062-16-0688	286504-6									

Deutsch Terminals/OCEAN Applicators (Applicator Family 1 for size 20 AWG)

Deutsch P/N (Pin)	TE P/N (Pin)	Deutsch P/N (Socket)	TE P/N (Socket)	Terminal Insulation Range	Applicator P/N Conversion P/N*	Wire Crimp Width	Wire Crimper P/N	Insulation Range O.D.	Insulation Crimp Width	Insulation Crimper P/N	Anvil P/N	Terminal Specification
1060-20-0122	1572032-1	1062-20-0122	286680-1	1.91 - 3.18 mm (.075 - .125 IN)	2266116 7-2266116-8	1.75 mm "F" (.069 IN)	1803364-2	2.74mm - 3.18mm (.108 - .125)	2.79mm "O" (.110 IN)	1803019-4	1-1803293-2	114-151003
1060-20-0144	1572032-2	1062-20-0144	286680-2									
1060-20-0177		1062-20-0177										
		1062-20-0322	286680-5									
		1062-20-0344	286680-6									
		1062-20-0377										
1060-20-0122	1572032-1	1062-20-0122	286680-1	1.91 - 3.18 mm (.075 - .125 IN)	2266117 7-2266117-8	1.75 mm "F" (.069 IN)	1803364-2	2.31mm - 2.72mm (.091 - .107)	2.29mm "O" (.090 IN)	1803019-5	1-1803293-3	114-151003
1060-20-0144	1572032-2	1062-20-0144	286680-2									
1060-20-0177		1062-20-0177										
		1062-20-0322	286680-5									
		1062-20-0344	286680-6									
		1062-20-0377										
1060-20-0122	1572032-1	1062-20-0122	286680-1	1.91 - 3.18 mm (.075 - .125 IN)	2266118 7-2266118-8	1.75 mm "F" (.069 IN)	1803364-2	1.91mm - 2.29mm (.075 - .090)	2.03mm "O" (.080 IN)	1803019-6	1-1803293-4	114-151003
1060-20-0144	1572032-2	1062-20-0144	286680-2									
1060-20-0177		1062-20-0177										
		1062-20-0322	286680-5									
		1062-20-0344	286680-6									
		1062-20-0377										
1060-20-0222	1572032-3	1062-20-0222	286680-3	1.30 - 2.16 mm (.051 - .085 IN)	2266119 7-2266119-8	1.75 mm "F" (.069 IN)	1803364-2	1.60mm - 2.16mm (.063 - .085)	1.73mm "O" (.068 IN)	1803019-7	1-1803293-5	114-151003
1060-20-0244	1572032-4	1062-20-0244	286680-4									
1060-20-0277		1062-20-0277										
1060-20-0222	1572032-3	1062-20-0222	286680-3	1.30 - 2.16 mm (.051 - .085 IN)	2266120 7-2266120-8	1.75 mm "F" (.069 IN)	1803364-2	1.27mm - 1.57mm (.050 - .062)	1.32mm "O" (.052 IN)	6-1803019-3	1-1803293-6	114-151003
1060-20-0244	1572032-4	1062-20-0244	286680-4									
1060-20-0277		1062-20-0277										

Deutsch Terminals/OCEAN Applicators (Applicator Family 2 for size 20 AWG)

1060-20-0622	2113369-1	1062-20-0622	2113370-1	1.91 - 3.18 mm (.075 - .125 IN)	2266121 7-2266121-8	1.73 mm "F" (.068 IN)	4-1333281-8	2.74 - 3.18 mm (.108 - .125 IN)	2.79mm "O" (.110 IN)	1803019-4	1-1803293-7	114-151003
1060-20-0644	2113369-2	1062-20-0644	2113370-2									
1060-20-0677	2113369-3	1062-20-0677	2113370-3									
1060-20-0622	2113369-1	1062-20-0622	2113370-1	1.91 - 3.18 mm (.075 - .125 IN)	2266122 7-2266122-8	1.73 mm "F" (.068 IN)	4-1333281-8	2.31 - 2.72 mm (.091 - .107 IN)	2.29mm "O" (.090 IN)	1803019-5	1-1803293-8	114-151003
1060-20-0644	2113369-2	1062-20-0644	2113370-2									
1060-20-0677	2113369-3	1062-20-0677	2113370-3									
1060-20-0622	2113369-1	1062-20-0622	2113370-1	1.91 - 3.18 mm (.075 - .125 IN)	2266123 7-2266123-8	1.73 mm "F" (.068 IN)	4-1333281-8	1.91 - 2.29 mm (.075 - .090 IN)	2.03mm "O" (.080 IN)	1803019-6	1-1803293-9	114-151003
1060-20-0644	2113369-2	1062-20-0644	2113370-2									
1060-20-0677	2113369-3	1062-20-0677	2113370-3									

Deutsch Terminals/OCEAN Applicators (Applicator Family 1 for size 12 AWG)

1060-20-0622	2113369-1	1062-20-0622	2113370-1	1.91 - 3.18 mm (.075 - .125 IN)	2266121 7-2266121-8	1.73 mm "F" (.068 IN)	4-1333281-8	2.74 - 3.18 mm (.108 - .125 IN)	2.79 mm "O" (.110 IN)	1803019-4	1-1803293-7	114-151003
1060-20-0644	2113369-2	1062-20-0644	2113370-2									
1060-20-0677	2113369-3	1062-20-0677	2113370-3									
1060-20-0622	2113369-1	1062-20-0622	2113370-1	1.91 - 3.18 mm (.075 - .125 IN)	2266122 7-2266122-8	1.73 mm "F" (.068 IN)	4-1333281-8	2.31 - 2.72 mm (.091 - .107 IN)	2.29 mm "O" (.090 IN)	1803019-5	1-1803293-8	114-151003
1060-20-0644	2113369-2	1062-20-0644	2113370-2									
1060-20-0677	2113369-3	1062-20-0677	2113370-3									
1060-20-0622	2113369-1	1062-20-0622	2113370-1	1.91 - 3.18 mm (.075 - .125 IN)	2266123 7-2266123-8	1.73 mm "F" (.068 IN)	4-1333281-8	1.91 - 2.29 mm (.075 - .090 IN)	2.03 mm "O" (.080 IN)	1803019-6	1-1803293-9	114-151003
1060-20-0644	2113369-2	1062-20-0644	2113370-2									
1060-20-0677	2113369-3	1062-20-0677	2113370-3									

Deutsch Terminals/OCEAN Applicators (Applicator Family 2 for size 12 AWG)


1060-12-0222	286989-1	1062-12-0222	286988-1	3.56 - 5.18 mm (.140 - .204 IN)	2266127 7-2266127-8	3.28 mm "F" (.129 IN)	4-1633713-7 (6°)	4.65mm - 5.18mm (.183 - .204 IN)	4.83mm "O" (.190 IN)	2-1803019-9	2-1803293-3	114-151006
1060-12-0244	286989-2	1062-12-0244	286988-2									
1060-12-0222	286989-1	1062-12-0222	286988-1	3.56 - 5.18 mm (.140 - .204 IN)	2266128 7-2266128-8	3.28 mm "F" (.129 IN)	4-1633713-7 (6°)	3.96mm - 4.62mm (.156 - .182 IN)	4.06mm "O" (.160 IN)	3-1803019-0	2-1803293-4	114-151006
1060-12-0244	286989-2	1062-12-0244	286988-2									
1060-12-0222	286989-1	1062-12-0222	286988-1	3.56 - 5.18 mm (.140 - .204 IN)	2266129 7-2266129-8	3.28 mm "F" (.129 IN)	4-1633713-7 (6°)	3.56mm - 3.94mm (.140 - .155 IN)	3.30mm "O" (.130 IN)	6-1803019-2	2-1803293-7	114-151006
1060-12-0244	286989-2	1062-12-0244	286988-2									

*CONVERSION PART NUMBER OF FORMAT 7-#-8 CAN BE PURCHASED TO CONVERT THE SAME FAMILY / SIZE OF TERMINALS INTO ANOTHER INSULATION CRIMP WIDTH OUTCOME, E.G. PURCHASING APPLICATOR 2266124 IS SUITED TO AN APPLIED CABLE DIAMETER OF 3.83 - 4.47MM [.151 - .176] WITH INSULATION CRIMP WIDTH (TOOLING WIDTH) OUTCOME OF 3.96MM [.156"]; PURCHASING CONVERSION PART NUMBER 7-2266125-8 WILL ENABLE APPLICATOR 2266124 TO BE CONVERTED TO APPLY A CABLE DIAMETER OF 3.27 - 3.81MM [.129 - .150] WITH INSULATION CRIMP WIDTH (TOOLING WIDTH) OUTCOME OF 3.40MM [.134"]




Let's Connect

Learn more about our comprehensive line of tooling solutions at tooling.te.com.
To find the right TE tooling for your needs, call us at **717-810-2082**
or email toolingSales@te.com.



TE Connectivity Technical Support Center

USA:	1.800.522.6752	UK:	+44.0800.267666
Canada:	1.800.522.6752	France:	+33.1.34.20.8686
Mexico:	+52.55.11.06.0800	Netherlands:	+31.73.624.6999
Latin/S. America	+55.11.3404.6261	China:	+86.400.820.6015
Germany:	+49.6151.607.1999		



Waste Not. Want Not.

Whether it's time or scrap, in manufacturing everyone knows that waste costs money. With our on-site certification and consultation services, we can help you:

- Reduce downtime
- Reduce scrap
- Maintain crimp quality



Time is Money.

In manufacturing downtime can be expensive. That's why TE is constantly working to improve product availability and delivery rates. With a strong global footprint, short lead times and a strong distribution channel, TE has the equipment and the accessories to keep production online.

To check distributor stock and availability for your tooling needs go to: www.te.com/commerce/sck/cdi.do

te.com

OCEAN, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners. The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.

1-1773720-8 07/18 Original

Contact us today to learn more

E-mail (Americas): fieldservicesnorthamerica@te.com

Phone (Americas): 800-722-1111 or 717-986-3434

E-mail (EMEA): TEFE1@te.com

Phone (EMEA): +49-6151-607-1518