




Automotive Parts > Automotive Terminals > AMP MCP, RECEPTACLE AND TAB



Terminal Type: **Receptacle**
Wire Size: **.22 – .35 mm²**
Mating Tab Width: **2.8 mm [.11 in]**
Interface Plating: **Silver (Ag)**
Primary Locking Feature: **Locking Lance**

[All AMP MCP, RECEPTACLE AND TAB \(105\)](#)

Features

Product Type Features

Receptacle Style	180°
Primary Locking Feature	Locking Lance
Sealable	Yes

Body Features

Terminal Seal Type	Single Wire Seal (SWS)
--------------------	------------------------

Contact Features

Typical Current Rating	11 A
Crimp Type	F-Crimp
Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]



Interface Plating	Silver (Ag)
Mating Tab Thickness	.6 mm, .8 mm[.024 in][.031 in]

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	1.1 – 1.4 mm[.043 – .055 in]
Wire Size	.22 – .35 mm²
Wire Size Search	.22 mm², .35 mm²
Tab Length	19.9 mm[.78 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	140 °C[284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Conforms to Automation Guideline	Yes, DIN 72036 Automation of Wiring Harness Production, Version June 2024, Yes, KOMAX Guideline for automatic component insertion for electrical connections, Version 5.0 (March 2018)

Industry Standards

Compatible With Agency/Standards Products	DIN 72036
---	-----------

Packaging Features

Packaging Method	Reel
Packaging Quantity	3500

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151484-2
OCEAN-2.0-APPLICATOR-S-062F155O-RSA

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

TE Part # 2151484-1
OCEAN-2.0-APPLICATOR-S-062F155O-RSM

TE Part # 7-2151484-7
OCEAN_2.0_SPARE_PART_KIT-062F155O

TE Part # 7-2836449-7
OC-062F155O-752-CRIMPTOOLINGKIT

TE Part # 963294-1
SINGLE WIRE SEAL INSULATION DI

Also in the Series | AMP MCP 2.8



Automotive Connector Caps & Covers (1)



Automotive Connector Locks & Position Assurance(5)




Automotive Housings(193)



Automotive Signal & Power Connector Housings(111)



Automotive Signal & Power Headers(1)



Automotive Terminals(52)

Customers Also Bought



TE Part #CH03566001
QSZH-125-NR3-30MM



TE Part #7121976001
RBK-VWS-125-NR3-X-65MM




TE Part #1335390003
ES-CAP-NO.3-B8-X-40MM



TE Part #1718758-3
MCON 1.2 LL TAB SWS AG



TE Part #2141884-2
TAB A 1.6x0.6 CONTACT CF SWS Sn




TE Part #1-2177909-1
MCON 0.5 CB, CONTACT



TE Part #CAT-M4596-T273
HPF 1.2, RECEPTACLE



TE Part #2297816-1
SINGLE WIRE SEAL,HPF 1.2,RUBBER



TE Part #2297817-1
SINGLE WIRE SEAL,HPF 1.2,RUBBER

Documents



Product Drawings

AMP MCP 2.8K, CONTACT, SWS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1564984-3_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1564984-3_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1564984-3_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Application Specification

German

Application Specification

English