

1583092-1

✓ ACTIVE

AMP

TE Internal #: 1583092-1

Premium Crimp Tooling, Removable/Interchangeable, MIL Spec /
TE Product Specification (114-), Battery / Hydraulic / Manual, Hand
Crimping Tools[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Yes – Certificate Included

Power Technology Type: Battery, Hydraulic, Manual

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per

Solder Process Capability	homogenous material. Also BFR/CFR/PVC Free
---------------------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 193673-4
SKT ASSY.,CRIMP, 6MM, 6AWG



TE Part # 328144
TERMINAL,AMPOWER 6 3/8



TE Part # 328158
TERMINAL,AMPOWER 6 1/2



TE Part # 1490745-1
HYP10 LIGHT DUTY 12T HEAD



TE Part # 1490746-1
HYP10 LIGHT DUTY 14T HEAD



TE Part # 328142
TERMINAL,AMPOWER 6 1/4



TE Part # 1490749-1
HYP10 8-4/0AWG MANUAL TOOL



TE Part # 328143
TERMINAL,AMPOWER 6 5/16



TE Part # 328141
TERMINAL,AMPOWER 6 10




TE Part # 193837-4
PIN ASSY.,CRIMP, 6MM, 6AWG



TE Part # 1490747-1
HYP10 HEAVY DUTY 12T HEAD

Customers Also Bought

TE Part #486085-000
CWT-9-W122-5TE Part #53041
TERMINAL,T-N R 8 8TE Part #66024-2
TAB,PIDG TERMI-BK 16-14TE Part #320576
TERMINAL,PIDG R 12-10 5/16TE Part #324046
TERMINAL,T-N R 6 10TE Part #325401
TERMINAL,AMPOWER 2/0 .265TE Part #328142
TERMINAL,AMPOWER 6 1/4TE Part #2388970-1
SDE F DEUTSCH (16) 1.00-2.00mm²
ASSYTE Part #5207871-1
SCREW RETAINER KITTE Part #608028-2
PIDG KIT WO/TOOL

Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

Bottoming Dies

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English