Meter Relays 077 Series Analogue Meter Relays

20 0 6C 80 100 P :RCEN T 100

Series 077 meter relays combine a highly accurate indicator with High and Low set point relay. The relays can operate alarm and control devices when the monitored signal value moves outside the chosen set point limits shown by adjustable red index pointers.

A single compact case houses the unit which requires only the input signal and power supply thus saving space and installation time.

Meter Relays	Product Code
One relay, two setpoints Upscale de-energized, down scale energized. Typical applications: Liquid level control, load shedding and power factor correction.	077-300
One relay, one set point Upscale energized, downscale de-energized. Typical application: High alarm.	077-301
Two relays, two set points Mid band de-energized, outside band energized. Typical applications: High and Low alarm, High alarm plus shut down.	077-302
Two relays, two setpoints Both upscale energized, downscale de-energized. Typical application: High alarm plus shutdown.	077-303
Two relays, two setpoints High and low midband energized, outside band de-energized. No time delay. Typical application: High alarm plus shutdown.	077-304
Two relays, two set points Both upscale de-energized,downscale energized. Typical application: Frequency monitoring.	077-305
One relay, one set point Upscale de-energized, downscale energized. Typical application: Low alarm.	077-307
Two relays, two set points Midband de-energized, outside band energized. Operates from from 2, 3 or 4 wire resistance temperature detector (RTD). Typical application: Temperature indication / control.	077-30R
Two relays, two set points Midband de-energized, outside band energized. Operates from thermocouple input. Cold junction compensation and thermocouple break protection are standard features. Typical application: Typical application / control	077-30T
Typical application: Temperature indication / control.	077-301

Features

- Monitors and controls any variable which can be converted to an A.C. or D.C. signal.
- Rugged, shock and vibration resistant design
- Indicator, relays and power unit in one housing
- Stable electronic switching circuit does not use lamps, photocells, inductors or capacitors
- >>> Taut band, fluid damped indicator
- Isolated input signal
- ▶ LED relay state indicators
- Built-in 0 10 second adjustable time delays
- UL Approved File No. E75911SP

Applications

- Voltage monitoring/ control current monitoring
- >> Overload alarm
- Battery monitoring/ charging
- >> Temperature indication
- >> Temperature control
- Load shedding
- Power factor correction
- Frequency monitoring
- Level control







Meter Relays 077 Series Analogue Meter Relays

Specification

Input signal ratings:

Frequency monitoring: 45/65Hz or 55/65Hz

100/125 V, 200/250V

380/440V or 480V system

D.C. Voltage: 10mV to 500V - $10\text{k}\Omega/\text{V}$ D.C. Current: $10\mu\text{A}$ to 500mA - 20mV drop

4/20mA

A.C. Voltage: 6V to $600V - 1000 \Omega/V$ A.C. Current: $100\mu A$ to 1A - 1V drop

5A CT operation - 0.5VA

10 Ω Copper 100 Ω Platinum

0-200°C, 0-150°C or 20 - 140°C

Overloads: 1.2 x continuous, up to 200V or 100mA - 10 x for 10 secs.

Indicator Accuracy:Max error 1.5%Damping time:1 second4" Scale:100° deflectionSet point accuracy:Max error 1.5%

Repeatability: 0.5%
Differential: 1% of span

Operating time: 250m sec to 10 sec adjustable

Set-point Adjustments: Single - 100% of scale

Double - 98% of scale

Minimum span: 2% between setpoints

Colour: Red

Output Relay: Mounted internally

Operation: SPDT contacts on each setpoint

Optional latching on either or both relays (077-301, 077-302

or 077-307 only)

Contact Rating: 5A, 250V, 1000W non-

inductive

Ambient TemperatureRange:

-10°C to +60°C (+14°F to 140°F)

Standard calibration: 20°C (68°F)

Panel Material: Ferrous or non-ferr

Panel Material: Ferrous or non-ferrous

Dielectric test: 2600V r.m.s. for 1 minute

Auxiliary power requirement:

A.C.: Dual rating - 120/240, 50/60Hz
D.C.: 12V, 24V or 125V DC

Burden: 3W maximum

Options

- BR Non reflecting window
- CT Calibrated at customer specified temperature
- EB Both relays latch, external switch to reset
- EH High relay latch, external switch to reset
- EL Low relay latch, external switch to reset
- FK Finger knob setpoint adjusters
- LB Both relays latch, remove auxiliary supply to reset
- LH High relays latch, remove auxiliary supply to reset

- LL Low relays latch, remove auxiliary supply to reset
- PD Electrical heavily damped movements
- PG Panel mounting gasket
- SL Red line on instrument dial
- SM Customer logo on instrument dial (Note: one off setup charge may apply)
- SZ Coloured band on instrument dial
- TP TPC-Time proportional control (proportional plus derivative control)

Connections

Relay switch modes with input signals in zone indicated by meter pointer



