



All MCON 1.2 Locking Lance Receptacle and Tab Terminals (14)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1801610-1
BULK HEAD, MCON, 10W, CLIPPED



TE Part # 1801606-2
TAB HOUSING, MCON, 10 W, SEALED



TE Part # CAT-N14-RC4812
48V Ready 1.2mm Sealed Connectors



TE Part # 1-2141324-4
6POS, MCON 1.2 LL TAB SEALED
COD A



TE Part # 2151480-1
OCEAN_2.0_APPLICATOR-S-
070F130SP-RSM




TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No
Crimp




TE Part # 7-2151480-7
OCEAN_2.0_SPARE_PART_KIT-
070F130SP




TE Part # 5-1579018-6
INSERTION TOOL



TE Part # 967067-1
MQS SGL WIRE SEAL



TE Part # 2-1564559-4
4POS, MCON 1.2 LL TAB SEALED
COD B



TE Part # 1-2141520-4
5POS, MCON 1.2 LL TAB SEALED
COD A



TE Part # 1-1703494-4
3POS, MCON 1.2 LL TAB SEALED
COD A



TE Part # 1801606-1
TAB HOUSING, MCON, 10 W, SEALED




TE Part # 1801606-5
TAB HOUSING, MCON, 10 W, SEALED



TE Part # 2372541-2
SDE F 1.2 MM SWS 15--18 DIE SET



TE Part # 2372541-1
SDE F 1.2 MM SWS 15--18 ASSY



TE Part # 7-2266807-7
OC-070F130SP-752-
CRIMP TOOLING KIT



TE Part # 7-1452671-2
MCON 1.2 LL REC SWS AU



TE Part # 963142-2
SWS,MQS,CVTY DIA,4.0,GRY



TE Part # 1-1703498-4
2POS, MCON 1.2 LL TAB SEALED
COD A

Customers Also Bought





TE Part #CAT-D48-ST273
DEUTSCH Connector Solid Contacts



TE Part #DT04-2P
REC, 2P, GRY, N




TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

Product Drawings

MCON 1.2 LL TAB SWS AU

English

MCON 1.2 LL TAB SWS AU

English

CAD Files

Customer View Model

ENG_CVM_CVM_1718762-2_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1718762-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1718762-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

English

