




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Cap**

Mating Alignment: **With**

Mating Alignment Type: **Polarization**

Mating Retention: **With**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
Number of Rows	3

Electrical Characteristics

Insulation Resistance	1000 MΩ
Operating Voltage	300 VAC

Body Features

Primary Product Color	Red
-----------------------	-----



Contact Features

Contact Layout	Matrix
Contact Base Material	Copper Alloy
Contact Retention Within Housing	Without
Contact Type	Tab
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Material	Nylon 6/6

Dimensions

Connector Height	17.6 mm[.69 in]
Connector Length	29 mm[1.14 in]
Row-to-Row Spacing	4.6 mm[.181 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	500
--------------------	-----



Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 175149-1
UNIVERSAL POWER CONN TAB



TE Part # 175149-2
AMP UNIVE. POWER CONN TAB
CONT



TE Part # 175154-2
U/P TAB CONT L/P



TE Part # 176276-9
AMP UNIVERSAL POWER PLUG 9P






TE Part # 175149-3
AMP UNIVERSAL POWER CONN.TAB
C




TE Part # 176276-2
AMP UNIVERSAL POWER PLUG 9P



TE Part # 175154-1
UNIV POWER TAB CONT L/P



TE Part # 175153-1
UNIV POWER TAB CONT L/P



TE Part # 175153-2
U/P TAB CONT L/P



TE Part # 176276-1
AMP UNIVERSAL POWER PLUG 9P



TE Part # 176276-4
AMP UNIVERSAL POWER PLUG 9P



TE Part # 175150-2
AMP UNIVE. POWER CONN TAB
CONT




TE Part # 175150-1
UNIVERSAL POWER CONN TAB


Also in the Series | AMP Universal Power



Connector Contacts(59)



PCB Headers & Receptacles(118)




Power Contacts(58)



Rectangular Connector Housings(367)



Rectangular Power Connectors(485)



Standard Rectangular Connectors(367)



Wire-to-Board Connector Assemblies
& Housings(47)

Also in the Series | Power Double Lock



Connector Contacts(59)




Connector Hardware(25)



Connector Seals & Cavity Plugs(8)



Insertion & Extraction Tools(2)




PCB Headers & Receptacles(118)



Power Contacts(58)



Rectangular Power Connectors(485)



Wire-to-Board Headers & Receptacles (118)

Customers Also Bought



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D48-ST273
DEUTSCH Connector Solid Contacts




TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING

Documents

Product Drawings

AMP UNIVERSAL POWER CAP 9P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_176287-2_H.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_176287-2_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_176287-2_H.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_176287-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_176287-2_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_176287-2_B.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1773458-5_POWER_DBL_LOCK_\(PDL\)_CONNECTORS](#)

English

Product Specifications

[Crimping of Universal Power Contact](#)

English

[Product Specification](#)

Japanese

[AMP Universal Power Connector](#)

Japanese

Instruction Sheets

[AMP UNIVERSAL POWER CONNECTOR SERIES](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English