schaffner
MORE POWER TO YOU

is now part of

TE connectivity



SELECTOR CHART

How to find the right filter?

Table of Contents

IEC Inlet Filters 3

Common Mode Chokes 4

Single Phase EMI Filters 5

Three Phase EMI Fliters 6

DC EMI Fliters 7

All series are listed in ascending Performance from **Good** → **Better** → **Best**

* - medical versions available

E - family name ending with E, (with Earth line choke)

IEC Inlet Filters

Unfiltered Inlets

SR style 15A (C20)
C style with switch 15A (C14)
P style with switch + Fuse 3-6A (C14)

Filtered - Power Inlet

FN9222/FN9222E * 1-20A (C14,C16,C20)
FN9226 * 1-10A (C14,C16)
EBF style 1-10A (C13)
FN9233/ FN9233E * 1-15A (C14,C16)
FN9244/FN9244E * 1-15A (C14,C16)
SRB style 15A/20A (C14,C20)
EEJ / EJH * 1-20A (C14,C20)
IH style * 1-15A (C18)
EJT style 1-20A (C14,C20)
FN9274 * 1-15A (C18)

Filtered - Power Entry Module

With fuse

GG/HG style 1-10A (C14)
FN9260/FN261 * 1-10A (C14)
FN9262 * 1-10A (C14)

With switch

FN9264 * 1-10A (C14)
FN9266 * 1-10A (C14)

With Fuse/ Switch/ Voltage selector

FN280 * 1-10A (C14)
FN370 * 2-6A (C14)
FN380 * 2-6A (C14)
FN390 * 1-10A (C14)
FN9280 * 1-10A (C14)
P style * 3-6A (C14)
FN9290 * 1-10A (C14)
HP style * 3-12A (C14)

Specials

FN9246
M Series *
IF13

Standard Termination Type

Quick Connect



Wire Lead

Mating parts – C13, C19 connectors, Power Cords

All series are listed in ascending Ampacity from **Low** → **High**

Common Mode Chokes

Two Line

- **RC Chokes** 0.25-0.7A
- **RN Chokes** 0.3-10A
- **RB Chokes** 16-50A
- **RT Chokes** 6-85A
- **RD Chokes** 6-64A
- **RV Chokes (parallel)** 32-100A
- **RV Chokes (in series)** 16-50A

Three Line

- **RT Chokes** 6-85A
- **RD Chokes** 6-64A

All series are listed in ascending Ampacity from **Low** ↓ **High**

Four Line

- **RV Chokes** 16-50A
- **RD Chokes** 6-64A

Special Chokes

- **ED Series** Dual Choke (Common and differential)
- **EV/EH Series** High leakage inductance
- **RR** Ring core only

Specifications:

- Voltage: Up to 600 VAC, up to 1000 VDC
- Current: 0.2 A – 85 A

Key Benefits:

- Extensive selection of discrete EMC/EMI chokes
- Various inductance and current ratings
- Ferrite and nanocrystalline core types for performance choice
- Designed easily and economically
- Build your own EMI Filter on PCBA with innovative magnetic solution

All series are listed in ascending Performance from **Good** → **Better** → **Best**

* - medical versions available

Single Phase EMI Filters

Standard Performance
Single Stage Filter

FN332 1-10A
FN2450 1-10A
H style 3-15A *
B style 1-30A
HT style 6-15A *
FN2010 1-60A *
K style 1-60A (earth line choke)
FN2020 1-60A *
SK style 3-40A (earth line choke)
FN2030 1-30A *
FN350 8-55A
FN2410 / FN2412 8-100A / 8-42A (Din rail mount)

High Performance
Double Stage Filter

FN343 1-10A (earth line choke)
FN2415 6-20A
MV style 3-20A *
HT/HQ style 15A/3-6A *
R style 1-20A (earth line choke)
FN2060 1-30A *
FN2070 1-36A *
FC style / S style 6-50A / 3-60A
VW Style 3-20A
EP/VP style 3-20A
FN2080 1-16A *
Q style 3-20A
T style 3-20A
FN2090 1-30A *

Very High Performance
Triple Stage Filter

FN700Z 6-20A (2CM + 1DM choke)
FN352Z 6-30A (1CM + 2DM Choke)

Lighting performance

FB / FBL / FBH style 1-20A
MRI style (DC filter) 3A

Our single-phase filters are available with various termination options , such as

Quick Connect 

Wire Lead

Stud

Terminal Block

Each families listed will have one or more termination options

Specials

Low Profile – High and Very high performance – Robotics application

FN2500 10-32A (quick connect)	**FN2640** 10-20A (IEC connector)
FN2520 10-32A (quick connect)	**FN2660** 10-20A (IEC Connector)

Three Phase EMI Filters

Standard Performance Single Stage Filter	**High Performance** Double Stage Filter	**Very High Performance** Triple Stage Filter

3 wire (or) Delta config.	**FN3030 / FN3040** 1-30A , 520V	**FN3287** 10-160A, 530V	**FN3271** 150-1000A, 520V
	FN3025/FN3026 10-50A , 520V	**FN3288 / FN3288HV** 10-160A, (520V, 760V)	**FN3359 / FN3359HV** 150-2000A (520V,760V)
	FN3311/FN3310 - HV 250-2300A, 520V , 690V		
	FN351H 8-280A , 520V		
	FN3258 / FN3268 * 7-180A , 520V		
	F3270 10-100A, 520V		
	FN3100 35-300A, 520V		
	FN3120H 25-230A, 520V		
4 wire (or) Star config.	**FN355** 3-20A	**FN354** 4-25A	
	FN3256H 8-160A	**FN3280H** 8-600A	

* - FN3258 – compact design
FN3268 – RCD compatible

Specials

FN3840 – Book style for regenerative drive application

Standard Termination Type

Stud

Terminal Block

Bus Bar

Three phase filters – Schaffner product families preferred

DC EMI Filters

PV Application

EV Application

FN200
25 to 2300 A - 1200 VDC - High Performance EMC Filter for PV

FN2211 and FN2210
250 to 2300 A - 1000 VDC - EMC Filters for PV

FN2220, FN2230 and FN2240
150 to 600 A - 1000 VDC - Filter for EV charging applications



EVX series
150 A - 1600 A,
500 V, 1000 V, 1500 V

FN2211HV and FN2210HV
250 to 2300 A - 1500 VDC - EMC Filter for PV



EVX series
150 A - 1600 A,
500 V, 1000 V, 1500 V

About TE Connectivity

Body Copy. m faccab ipsam aut et essim qui tenim ex expelec uptur, sitas rerum is ea eum sita dolorios deliquo cuptat. Upta dolorum ini dis ne nossim iminis dero optiaerem fuga. Haribusda quosaped maionsed maximil lestis eumquae nis susaerum qui dolor sundipsam reptatibus.Hil eture nimost, omnimilicta de nime eos iunt et voles enimperi simi, suntibu santuri tataessiti quaspeditius audit liquiam faccusanis ex et ex ea saperfe rferfer iatiate velest maio ventiisquati denienda vent essi to qui ra velectia que prempos ratur aliquun temodiam quo illa cum nitas estibus doluptatet ipsunto evellessequo mincips aperitasi as aut etus et, sam ipitet que etur alicien tiatque peratur? Equam reicabo rereri odi unt.

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2025 TE Connectivity. All Rights Reserved.

05-25

schaffner MORE POWER TO YOU

is now part of TE connectivity