


HF - Speed Sensor with Amplifier Typ DSH 1840.0x SxHV

DSH 1840.0x SxHV


Operating Instructions 374E- 64268



General		
Function	The HF speed sensors DSH 1840.01 SHV (Part no. 374 DSH 1840.01 S1HV (Part no. 374Z-05305) and DSH 184 374Z-05494) are suitable for use with a pole wheel to ge frequency signals. They exhibit dynamic behaviour, where down to 0.1 Hz is guaranteed. The sensing element is a poole wheel influences the damping in the oscillator. This modulation is converted to a square wave output sig trigger characteristics and a short circuit output stage.	0.05 SHV (Part no. nerate speed proportional eby pulse generation HF-Oscillator. A metallic
Certification	The DSH sensors are approved by Germanischer Lloyd (GL), Certificate no. 17332-00 HH	
Technical Data		
Supply voltage	1030 VDC, max. superimposed AC-voltage of 25 mVpp protected against false polarity	
Current consumption	max. 12mA at 12 Volt (without load)	
Signal output	Square wave signals from push-pull stage, DC-coupled to the supply (negative pole = reference potential), max. load 25 mA, Output voltage HI: > supply voltage -2.5 Volt at I = 15 mA Output voltage LO: < 1.5 Volt at I = 15 mA short-circuit proof and protected against false polarity	
Frequency range	0.1 Hz20 kHz	
Electromagnetic compatibility (EMC)	With cable shield connected to the GND pole. Electrostatic discharge into housing, cable shield and wires: Up to 4 kV peak according to IEC 61000-4-2, severity level 2 Radiated electromagnetic field: Up to 30 V/m, 50% AM, 1 KHz in the range of 1 MHz to 1000 MHz according to IEC 61000-4-3, severity level 3 Electrical fast transcients/burts, coupled to sensor cable with a capacitive coupling clamp: up to 4 kV peak according to IEC 61000-4-4, severity level 4	
Insulation	Housing, cable shield and electronics galvanically isolated. (500V/50Hz/1Min.)	
Operating Temperature	-40℃+125℃. (Version H)	
Housing	Aluminium alloy, black anodizied. Dimensions according to dimensional drawing.	
Weight	95 g with 2 m cable, 120 g with 3 m cable.	
Protection class	IP67 (head), IP67 (cable outlet)	
Vibration immunity	5 g in the range 52000 Hz	
Shock immunity	50 g during 20 ms, half-sine wave	
Pole wheel	Pole wheel (ST37) Module 4 : 0,24,0 mm Pole wheel (aluminium) with blades: Blade Blade Distance thickness width between blades 4,0 mm 15 mm 6,5 mm 2,1 mm 15 mm 7,5 mm	Pole wheel - sensor gap 0,22,0 mm 0,21,5 mm

Cable	Teflon cable , PartNo. 824L-35053, 4-wire, 4 x 0.24 mm² (AWG 24), strand shielded (metal net, insulated from housing), white, outer-Ø max. 4.5 mm, bending radius min. 60 mm.
	The brown wire not used in this sensor is cut off.
	Shield to be connected to the instrument side 0 V.
Versions	DSH 1840.01 SHV: Cable 2m long
	DSH 1840.01 S1HV: Cable 3m long
	DSH 1840.05 SHV: Cable 2m long, different sealing concept than DSH 1840.01
	SHV and hence shorter installation length

Connecting diagram:



DSH 1840.0x SxHV_e.doc 07/01/10