

# Hall Effect Zero Speed Sensor

## F58A25

**GREEN LINE**  
INDUSTRIAL SPEED SENSORS

### Product ID

Type #	Product #	Drawing #
F58A25	385Z-05564	113.592 Rev.1

### General


Function	The F58A25 series Hall effect speed sensors are suitable, in conjunction with a ferrous pole wheel, for generating square wave signals proportional to rotary speeds. They exhibit a static function, whereby pulse generation down to 0 Hz is guaranteed. The sensor function is independent of rotational mounting angle.
----------	---

### Technical data

Supply voltage	8...25 VDC
Current consumption	Max. 12 mA (without load)
Signal output	Square wave signal from NPN output transistor with internal 2.7 kOhm pull-up resistor, DC-coupled to supply (negative pole = reference Voltage). Sink current: max. 25 mA Output voltage: $U_{high} \sim$ supply voltage $U_{low} < 0.5 \text{ V}$ at $I = 25 \text{ mA}$
Frequency range	0 Hz...15 kHz
Housing	5/8"-18 UNF-2A, tightening torque: max. 35 Nm
Connection	Connector: M12x1 thread, 4 pins, black
Protection	Sensor head: IP68 Connector: IP67
Insulation	Housing and electronics galvanically isolated (Test: 500 V, 50 Hz for 1 minute)
Pole wheel	Prerequisite: Toothed wheel of a ferrous material (e.g. Steel 1.0036). Optimal performance with Involute gear Tooth width > 10 mm Side offset < 0.2 mm Eccentricity < 0.2 mm
Air gap between sensor and pole wheel	Module 1.0 (DP 25.4): 0.3...0.5 mm Module 2.0 (DP 12.7): 0.3...1.5 mm
Electromagnetic compatibility (EMC)	Please contact Jaquet for further details.
Vibration & shock immunity	Jaquet Greenline sensors are approved for rough environments. Please contact Jaquet for further details.
Operating temperature	-40°C...125°C


## Further Information

Safety	All mechanical installations must be carried out by an expert. General safety requirements have to be met.
Installation	<p>The sensor has to be aligned to the pole wheel according to the sensor drawing independent of its rotational orientation. Deviations in positioning may affect the performance and decrease the noise immunity of the sensor. During installation, the smallest possible pole wheel to sensor gap should be set. The gap should however be set to prevent the face of the sensor ever touching the pole wheel. Within the air gap specified the amplitude of the output signal is not influenced by the air gap.</p> <p>A sensor should be mounted with the middle of the face side over the middle of the pole wheel. Dependent upon the wheel width, a certain degree of axial movement is permissible. However, the middle of the sensor must be at minimum in a distance of 3 mm from the edge of the pole wheel under all operating conditions.</p> <p>A solid and vibration free mounting of the sensor is important. Eventual sensor vibration relative to the pole wheel can induce additional output pulses.</p> <p>The sensors are insensitive to oil, grease etc. and can be installed in arduous conditions.</p>
Maintenance	Product cannot be repaired.
Transport	Product must be handled with care to prevent damage of the front face.
Storage	Product must be stored in dry conditions. The storage temperature corresponds to the operation temperature.
Disposal	Product must be disposed of properly, it must not be disposed as domestic waste.



J2.r!!!C2:.....	aquet	—W—
3852-05323	IF58A	59.7
3852-05564	IJ= R.c25	83.7
3852-05565	IF58A40	02 121.1

schematic diagram:



contact configuration:  
1 +V  
2 signal (..IL)  
3 GND  
4 not connected

mates with straight plug M12x1, 4 pins

FOR TECHNICAL SPECIFICATIONS SEE OPERATING INSTRUCTIONS

dimensions in mm						
part no.	material remarks			application		
-	-	-1-	-	nominal size range		
-	-	-1-	-	allowed tolerance		
-	-	-1-	-	replacement for		
-	-	-1-	-	first angle projection	drawn 25.09.2006	ebi
1	-	06.11.06/ebi	aktualisiert im Rahmen der GreenUne Erweiterung	<b>-E1-\$-</b>	approved 31.09.07	
rev.	ecn.	date/signature	change description	scale 1:1	drawing no.	rev.
<b>JAQUET</b> TECHNOLOGY GROUP Thannerstrasse 15 CH-4009 Basel www.jaquet.com				formal A4	113.592	1
part name speed sensor GreenUne F58A				file name	113592-revtdft	