



Connectors > Contacts > Connector Contacts



Wire Contact Termination Area Plating Material: **Silver**

Contact Base Material: **Beryllium Copper**

Sealable: **No**

Product Terminates To: **Wire**

Contact Current Rating (Max): **150 A**

Features

Product Type Features

Sealable	No
----------	----

Contact Features

Wire Contact Termination Area Plating Material	Silver
Contact Base Material	Beryllium Copper
Contact Current Rating (Max)	150 A

Termination Features

Product Terminates To	Wire
-----------------------	------

Usage Conditions

Operating Temperature Range	-196 – 200 °C[-321 – 392 °F]
-----------------------------	------------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 192004-8  
BAND STRIP LA1A(.006)SIL



TE Part # 2-192004-6  
LA1 A, .008, TIN PL



TE Part # 1-192004-4  
BAND STRIP LA1B(.006)SIL


Customers Also Bought




TE Part #31880  
PIDG R 22-16 COMM 22-18 MIL 4



TE Part #33464  
TERMINAL,SOLIS R 6 10




TE Part #58074-1  
MTA 50/100/156 MANUAL TOOL FRAME



TE Part #58246-1  
MTA 100 CRIMP HEAD REPAIR DISCRETE





TE Part #103682-4  
05 MTE PANEL MOUNT SR




TE Part #130552  
TERM, RING, SOLIS, 6, M5



TE Part #324061  
TERMINAL, SOLIS R 8 8



TE Part #CAT-104MTA-NYLCC  
Nylon PCB Connector Covers: 2.54 mm, MTA 100



TE Part #5207719-1  
KIT SCREWLOCK FEMALE

Documents

Product Drawings

BAND STRIP LA1A (.004)SIL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_192004-4\_K\_c-192004-4-k.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_192004-4\_K\_c-192004-4-k.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_192004-4\_K\_c-192004-4-k.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER\_CONNECTORS\_CATALOG\_SEC02\_CABLE\_MOUNTED

English