

RTD RESISTANCE TEMPERATURE TABLE

APPLICATION NOTE

Platinum, 100 Ohm at 0°C, .00385 TCR

°C	0	-1	-2	-3	-4	-5	-6	-7	-8	-9
-50	80.31	79.91	79.51	79.11	78.72	78.32	77.92	77.52	77.12	76.73
-40	84.27	83.87	83.48	83.08	82.69	82.29	81.89	81.5	81.1	80.7
-30	88.22	87.83	87.43	87.04	86.64	86.25	85.85	85.46	85.06	84.67
-20	92.16	91.77	91.37	90.98	90.59	90.19	89.8	89.4	89.01	88.62
-10	96.09	95.69	95.3	94.91	94.52	94.12	93.73	93.34	92.95	92.55
0	100	99.61	99.22	98.83	98.44	98.04	97.65	97.26	96.87	96.48
°C	0	1	2	3	4	5	6	7	8	9
0	100	100.39	100.78	101.17	101.56	101.95	102.34	102.73	103.12	103.51
10	103.9	104.29	104.68	105.07	105.46	105.85	106.24	106.63	107.02	107.4
20	107.79	108.18	108.57	108.96	109.35	109.73	110.12	110.51	110.9	111.29
30	111.67	112.06	112.45	112.83	113.22	113.61	114	114.38	114.77	115.15
40	115.54	115.93	116.31	116.7	117.08	117.47	117.86	118.24	118.63	119.01
50	119.4	119.78	120.17	120.55	120.94	121.32	121.71	122.09	122.47	122.86
60	123.24	123.63	124.01	124.39	124.78	125.16	125.54	125.93	126.31	126.69
70	127.08	127.46	127.84	128.22	128.61	128.99	129.37	129.75	130.13	130.52
80	130.9	131.28	131.66	132.04	132.42	132.8	133.18	133.57	133.95	134.33
90	134.71	135.09	135.47	135.85	136.23	136.61	136.99	137.37	137.75	138.13
100	138.51	138.88	139.26	139.64	140.02	140.4	140.78	141.16	141.54	141.91
110	142.29	142.67	143.05	143.43	143.8	144.18	144.56	144.94	145.31	145.69
120	146.07	146.44	146.82	147.2	147.57	147.95	148.33	148.7	149.08	149.46
130	149.83	150.21	150.58	150.96	151.33	151.71	152.08	152.46	152.83	153.21
140	153.58	153.96	154.33	154.71	155.08	155.46	155.83	156.2	156.58	156.95
150	157.33	157.7	158.07	158.45	158.82	159.19	159.56	159.94	160.31	160.68
160	161.05	161.43	161.8	162.17	162.54	162.91	163.29	163.66	164.03	164.4
170	164.77	165.14	165.51	165.89	166.26	166.63	167	167.37	167.74	168.11
180	168.48	168.85	169.22	169.59	169.96	170.33	170.7	171.07	171.43	171.8
190	172.17	172.54	172.91	173.28	173.65	174.02	174.38	174.75	175.12	175.49
200	175.86	176.22	176.59	176.96	177.33	177.69	178.06	178.43	178.79	179.16
210	179.53	179.89	180.26	180.63	180.99	181.36	181.72	182.09	182.46	182.82
220	183.19	183.55	183.92	184.28	184.65	185.01	185.38	185.74	186.11	186.47
230	186.84	187.2	187.56	187.93	188.29	188.66	189.02	189.38	189.75	190.11
240	190.47	190.84	191.2	191.56	191.92	192.29	192.65	193.01	193.37	193.74

RTD RESISTANCE TEMPERATURE TABLE

APPLICATION NOTE

Platinum, 100 Ohm at 0°C, .003925 TCR

°C	0	-1	-2	-3	-4	-5	-6	-7	-8	-9
-50	79.92	79.52	79.11	78.71	78.3	77.89	77.49	77.08	76.68	76.27
-40	83.96	83.56	83.16	82.75	82.35	81.94	81.54	81.13	80.73	80.33
-30	87.99	87.59	87.19	86.78	86.38	85.98	85.58	85.17	84.77	84.37
-20	92.01	91.61	91.2	90.8	90.4	90	89.6	89.2	88.79	88.39
-10	96.01	95.61	95.21	94.81	94.41	94.01	93.61	93.21	92.81	92.41
0	100	99.6	99.2	98.8	98.41	98.01	97.61	97.21	96.81	96.41
°C	0	1	2	3	4	5	6	7	8	9
0	100	100.4	100.8	101.19	101.59	101.99	102.39	102.79	103.18	103.58
10	103.98	104.38	104.77	105.17	105.57	105.96	106.36	106.76	107.15	107.55
20	107.95	108.34	108.74	109.13	109.53	109.93	110.32	110.72	111.11	111.51
30	111.9	112.3	112.69	113.09	113.48	113.88	114.27	114.66	115.06	115.45
40	115.85	116.24	116.63	117.03	117.42	117.81	118.21	118.6	118.99	119.39
50	119.78	120.17	120.56	120.96	121.35	121.74	122.13	122.52	122.92	123.31
60	123.7	124.09	124.48	124.87	125.26	125.66	126.05	126.44	126.83	127.22
70	127.61	128	128.39	128.78	129.17	129.56	129.95	130.34	130.73	131.12
80	131.51	131.89	132.28	132.67	133.06	133.45	133.84	134.23	134.61	135
90	135.39	135.78	136.17	136.55	136.94	137.33	137.72	138.1	138.49	138.88
100	139.27	139.65	140.04	140.42	140.81	141.2	141.58	141.97	142.36	142.74
110	143.13	143.51	143.9	144.28	144.67	145.05	145.44	145.82	146.21	146.59
120	146.98	147.36	147.75	148.13	148.51	148.9	149.28	149.67	150.05	150.43
130	150.82	151.2	151.58	151.97	152.35	152.73	153.11	153.5	153.88	154.26
140	154.64	155.03	155.41	155.79	156.17	156.55	156.93	157.32	157.7	158.08
150	158.46	158.84	159.22	159.6	159.98	160.36	160.74	161.12	161.5	161.88
160	162.26	162.64	163.02	163.4	163.78	164.16	164.54	164.92	165.3	165.68
170	166.05	166.43	166.81	167.19	167.57	167.95	168.32	168.7	169.08	169.46
180	169.83	170.21	170.59	170.97	171.34	171.72	172.1	172.47	172.85	173.23
190	173.6	173.98	174.36	174.73	175.11	175.48	175.86	176.23	176.61	176.98
200	177.36	177.74	178.11	178.48	178.86	179.23	179.61	179.98	180.36	180.73
210	181.11	181.48	181.85	182.23	182.6	182.97	183.35	183.72	184.09	184.47
220	184.84	185.21	185.58	185.96	186.33	186.7	187.07	187.45	187.82	188.19
230	188.56	188.93	189.3	189.67	190.05	190.42	190.79	191.16	191.53	191.9
240	192.27	192.64	193.01	193.38	193.75	194.12	194.49	194.86	195.23	195.6

RTD RESISTANCE TEMPERATURE TABLE

APPLICATION NOTE

Platinum, 100 Ohm at 0°C, .003916 TCR

°C	0	-1	-2	-3	-4	-5	-6	-7	-8	-9
-50	80	79.6	79.19	78.79	78.39	77.98	77.58	77.17	76.77	76.37
-40	84.03	83.62	83.22	82.82	82.42	82.02	81.61	81.21	80.81	80.4
-30	88.04	87.64	87.24	86.84	86.44	86.03	85.63	85.23	84.83	84.43
-20	92.04	91.64	91.24	90.84	90.44	90.04	89.64	89.24	88.84	88.44
-10	96.03	95.63	95.23	94.83	94.43	94.03	93.63	93.24	92.84	92.44
0	100	99.6	99.21	98.81	98.41	98.01	97.62	97.22	96.82	96.42
°C	0	1	2	3	4	5	6	7	8	9
0	100	100.4	100.79	101.19	101.59	101.98	102.38	102.78	103.17	103.57
10	103.96	104.36	104.75	105.15	105.55	105.94	106.34	106.73	107.13	107.52
20	107.91	108.31	108.7	109.1	109.49	109.89	110.28	110.67	111.07	111.46
30	111.85	112.25	112.64	113.03	113.43	113.82	114.21	114.61	115	115.39
40	115.78	116.18	116.57	116.96	117.35	117.74	118.13	118.53	118.92	119.31
50	119.7	120.09	120.48	120.87	121.26	121.65	122.04	122.43	122.82	123.21
60	123.6	123.99	124.38	124.77	125.16	125.55	125.94	126.33	126.72	127.11
70	127.5	127.89	128.28	128.66	129.05	129.44	129.83	130.22	130.6	130.99
80	131.38	131.77	132.15	132.54	132.93	133.32	133.7	134.09	134.48	134.86
90	135.25	135.64	136.02	136.41	136.79	137.18	137.57	137.95	138.34	138.72
100	139.11	139.49	139.88	140.26	140.65	141.03	141.42	141.8	142.19	142.57
110	142.95	143.34	143.72	144.11	144.49	144.87	145.26	145.64	146.02	146.41
120	146.79	147.17	147.56	147.94	148.32	148.7	149.09	149.47	149.85	150.23
130	150.61	150.99	151.38	151.76	152.14	152.52	152.9	153.28	153.66	154.04
140	154.42	154.81	155.19	155.57	155.95	156.33	156.71	157.09	157.47	157.85
150	158.22	158.6	158.98	159.36	159.74	160.12	160.5	160.88	161.26	161.63
160	162.01	162.39	162.77	163.15	163.53	163.9	164.28	164.66	165.04	165.41
170	165.79	166.17	166.54	166.92	167.3	167.67	168.05	168.43	168.8	169.18
180	169.55	169.93	170.31	170.68	171.06	171.43	171.81	172.18	172.56	172.93
190	173.31	173.68	174.06	174.43	174.81	175.18	175.55	175.93	176.3	176.68
200	177.05	177.42	177.8	178.17	178.54	178.92	179.29	179.66	180.03	180.41
210	180.78	181.15	181.52	181.9	182.27	182.64	183.01	183.38	183.76	184.13
220	184.5	184.87	185.24	185.61	185.98	186.35	186.72	187.09	187.46	187.84
230	188.21	188.58	188.95	189.31	189.68	190.05	190.42	190.79	191.16	191.53
240	191.9	192.27	192.64	193.01	193.38	193.74	194.11	194.48	194.85	195.22

RTD RESISTANCE TEMPERATURE TABLE

APPLICATION NOTE

Platinum, 1,000 Ohm at 0°C, .00385 TCR

°C	0	-1	-2	-3	-4	-5	-6	-7	-8	-9
-50	803.06	799.09	795.12	791.14	787.17	783.19	779.21	775.23	771.25	767.26
-40	842.71	838.75	834.79	830.83	826.87	822.9	818.94	814.97	811	807.03
-30	882.22	878.27	874.32	870.38	866.43	862.48	858.53	854.57	850.62	846.66
-20	921.6	917.67	913.73	909.8	905.86	901.92	897.98	894.04	890.1	886.16
-10	960.86	956.94	953.02	949.09	945.17	941.24	937.32	933.39	929.46	925.53
0	1,000.00	996.09	992.18	988.27	984.36	980.44	976.53	972.61	968.7	964.78
°C	0	1	2	3	4	5	6	7	8	9
0	1,000.00	1,003.91	1,007.81	1,011.72	1,015.62	1,019.53	1,023.43	1,027.33	1,031.23	1,035.13
10	1,039.03	1,042.92	1,046.82	1,050.71	1,054.60	1,058.49	1,062.38	1,066.27	1,070.16	1,074.05
20	1,077.94	1,081.82	1,085.70	1,089.59	1,093.47	1,097.35	1,101.23	1,105.10	1,108.98	1,112.86
30	1,116.73	1,120.60	1,124.47	1,128.35	1,132.21	1,136.08	1,139.95	1,143.82	1,147.68	1,151.55
40	1,155.41	1,159.27	1,163.13	1,166.99	1,170.85	1,174.70	1,178.56	1,182.41	1,186.27	1,190.12
50	1,193.97	1,197.82	1,201.67	1,205.52	1,209.36	1,213.21	1,217.05	1,220.90	1,224.74	1,228.58
60	1,232.42	1,236.26	1,240.09	1,243.93	1,247.77	1,251.60	1,255.43	1,259.26	1,263.09	1,266.92
70	1,270.75	1,274.58	1,278.40	1,282.23	1,286.05	1,289.87	1,293.70	1,297.52	1,301.33	1,305.15
80	1,308.97	1,312.78	1,316.60	1,320.41	1,324.22	1,328.03	1,331.84	1,335.65	1,339.46	1,343.26
90	1,347.07	1,350.87	1,354.68	1,358.48	1,362.28	1,366.08	1,369.87	1,373.67	1,377.47	1,381.26
100	1,385.06	1,388.85	1,392.64	1,396.43	1,400.22	1,404.00	1,407.79	1,411.58	1,415.36	1,419.14
110	1,422.93	1,426.71	1,430.49	1,434.26	1,438.04	1,441.82	1,445.59	1,449.37	1,453.14	1,456.91
120	1,460.68	1,464.45	1,468.22	1,471.98	1,475.75	1,479.51	1,483.28	1,487.04	1,490.80	1,494.56
130	1,498.32	1,502.08	1,505.83	1,509.59	1,513.34	1,517.10	1,520.85	1,524.60	1,528.35	1,532.10
140	1,535.84	1,539.59	1,543.33	1,547.08	1,550.82	1,554.56	1,558.30	1,562.04	1,565.78	1,569.52
150	1,573.25	1,576.99	1,580.72	1,584.45	1,588.18	1,591.91	1,595.64	1,599.37	1,603.09	1,606.82
160	1,610.54	1,614.27	1,617.99	1,621.71	1,625.43	1,629.15	1,632.86	1,636.58	1,640.30	1,644.01
170	1,647.72	1,651.43	1,655.14	1,658.85	1,662.56	1,666.27	1,669.97	1,673.68	1,677.38	1,681.08
180	1,684.78	1,688.48	1,692.18	1,695.88	1,699.58	1,703.27	1,706.96	1,710.66	1,714.35	1,718.04
190	1,721.73	1,725.42	1,729.10	1,732.79	1,736.48	1,740.16	1,743.84	1,747.52	1,751.20	1,754.88
200	1,758.56	1,762.24	1,765.91	1,769.59	1,773.26	1,776.93	1,780.60	1,784.27	1,787.94	1,791.61
210	1,795.28	1,798.94	1,802.60	1,806.27	1,809.93	1,813.59	1,817.25	1,820.91	1,824.56	1,828.22
220	1,831.88	1,835.53	1,839.18	1,842.83	1,846.48	1,850.13	1,853.78	1,857.43	1,861.07	1,864.72
230	1,868.36	1,872.00	1,875.64	1,879.28	1,882.92	1,886.56	1,890.19	1,893.83	1,897.46	1,901.10
240	1,904.73	1,908.36	1,911.99	1,915.62	1,919.24	1,922.87	1,926.49	1,930.12	1,933.74	1,937.36

RTD RESISTANCE TEMPERATURE TABLE

APPLICATION NOTE

Copper, 10 Ohm at 25°C, .00427 TCR

°C	0	-1	-2	-3	-4	-5	-6	-7	-8	-9
-50	7.1	7.06	7.03	6.99	6.95	6.91	6.87	6.83	6.79	6.75
-40	7.49	7.45	7.41	7.37	7.34	7.3	7.26	7.22	7.18	7.14
-30	7.88	7.84	7.8	7.76	7.72	7.68	7.64	7.61	7.57	7.53
-20	8.26	8.22	8.19	8.15	8.11	8.07	8.03	7.99	7.95	7.92
-10	8.65	8.61	8.57	8.53	8.49	8.46	8.42	8.38	8.34	8.3
0	9.04	9	8.96	8.92	8.88	8.84	8.8	8.76	8.73	8.69
°C	0	1	2	3	4	5	6	7	8	9
0	9.04	9.07	9.11	9.15	9.19	9.23	9.27	9.31	9.34	9.38
10	9.42	9.46	9.5	9.54	9.58	9.61	9.65	9.69	9.73	9.77
20	9.81	9.85	9.88	9.92	9.96	10	10.04	10.08	10.12	10.15
30	10.19	10.23	10.27	10.31	10.35	10.39	10.43	10.46	10.5	10.54
40	10.58	10.62	10.66	10.7	10.73	10.77	10.81	10.85	10.89	10.93
50	10.97	11	11.04	11.08	11.12	11.16	11.2	11.24	11.27	11.31
60	11.35	11.39	11.43	11.47	11.51	11.55	11.58	11.62	11.66	11.7
70	11.74	11.78	11.82	11.85	11.89	11.93	11.97	12.01	12.05	12.09
80	12.12	12.16	12.2	12.24	12.28	12.32	12.36	12.39	12.43	12.47
90	12.51	12.55	12.59	12.63	12.67	12.7	12.74	12.78	12.82	12.86
100	12.9	12.94	12.97	13.01	13.05	13.09	13.13	13.17	13.21	13.24
110	13.28	13.32	13.36	13.4	13.44	13.48	13.51	13.55	13.59	13.63
120	13.67	13.71	13.75	13.79	13.82	13.86	13.9	13.94	13.98	14.02
130	14.06	14.09	14.13	14.17	14.21	14.25	14.29	14.33	14.36	14.4
140	14.44	14.48	14.52	14.56	14.6	14.63	14.67	14.71	14.75	14.79
150	14.83	14.87	14.91	14.94	14.98	15.02	15.06	15.1	15.14	15.18
160	15.22	15.26	15.3	15.33	15.37	15.41	15.45	15.49	15.53	15.57
170	15.61	15.65	15.68	15.72	15.76	15.8	15.84	15.88	15.92	15.96
180	16	16.04	16.07	16.11	16.15	16.19	16.23	16.27	16.31	16.35
190	16.39	16.42	16.46	16.5	16.54	16.58	16.62	16.66	16.7	16.74
200	16.78	16.81	16.85	16.89	16.93	16.97	17.01	17.05	17.09	17.13
210	17.17	17.2	17.24	17.28	17.32	17.36	17.4	17.44	17.48	17.52
220	17.56	17.59	17.63	17.67	17.71	17.75	17.79	17.83	17.87	17.91
230	17.95	17.98	18.02	18.06	18.1	18.14	18.18	18.22	18.26	18.3
240	18.34	18.37	18.41	18.45	18.49	18.53	18.57	18.61	18.65	18.69

RTD RESISTANCE TEMPERATURE TABLE

APPLICATION NOTE

Nickel, 120 Ohm at 0°C, .00672 TCR

°C	0	-1	-2	-3	-4	-5	-6	-7	-8	-9
-50	87.21	86.6	86	85.4	84.8	84.21	83.61	83.02	82.43	81.84
-40	93.37	92.74	92.12	91.5	90.88	90.26	89.65	89.04	88.42	87.82
-30	99.73	99.08	98.44	97.8	97.16	96.52	95.89	95.25	94.62	93.99
-20	106.29	105.62	104.96	104.3	103.64	102.98	102.33	101.67	101.02	100.37
-10	113.04	112.36	111.68	110.99	110.32	109.64	108.96	108.29	107.62	106.95
0	120	119.3	118.59	117.89	117.19	116.5	115.8	115.11	114.42	113.73
°C	0	1	2	3	4	5	6	7	8	9
0	120	120.71	121.42	122.13	122.84	123.55	124.27	124.99	125.71	126.43
10	127.16	127.88	128.61	129.34	130.07	130.81	131.54	132.28	133.02	133.77
20	134.51	135.26	136.01	136.76	137.51	138.26	139.02	139.78	140.54	141.3
30	142.06	142.83	143.6	144.37	145.14	145.92	146.69	147.47	148.25	149.03
40	149.82	150.6	151.39	152.18	152.98	153.77	154.57	155.36	156.17	156.97
50	157.77	158.58	159.39	160.2	161.01	161.82	162.64	163.46	164.28	165.1
60	165.93	166.75	167.58	168.41	169.25	170.08	170.92	171.76	172.6	173.44
70	174.28	175.13	175.98	176.83	177.68	178.54	179.4	180.26	181.12	181.98
80	182.85	183.71	184.58	185.45	186.33	187.2	188.08	188.96	189.84	190.72
90	191.61	192.5	193.39	194.28	195.17	196.07	196.97	197.87	198.77	199.67
100	200.58	201.49	202.4	203.31	204.22	205.14	206.06	206.98	207.9	208.82
110	209.75	210.68	211.61	212.54	213.48	214.41	215.35	216.29	217.24	218.18
120	219.13	220.08	221.03	221.98	222.94	223.89	224.85	225.81	226.78	227.74
130	228.71	229.68	230.65	231.62	232.6	233.57	234.55	235.53	236.52	237.5
140	238.49	239.48	240.47	241.46	242.46	243.46	244.46	245.46	246.46	247.46
150	248.47	249.48	250.49	251.5	252.52	253.54	254.56	255.58	256.6	257.62
160	258.65	259.68	260.71	261.74	262.78	263.81	264.85	265.89	266.93	267.97
170	269.02	270.07	271.12	272.17	273.22	274.27	275.33	276.39	277.45	278.51
180	279.58	280.64	281.71	282.78	283.85	284.92	285.99	287.07	288.15	289.23
190	290.31	291.39	292.48	293.56	294.65	295.74	296.83	297.92	299.02	300.11
200	301.21	302.31	303.41	304.51	305.61	306.72	307.83	308.93	310.04	311.15
210	312.27	313.38	314.5	315.61	316.73	317.85	318.97	320.09	321.22	322.34
220	323.47	324.59	325.72	326.85	327.98	329.12	330.25	331.38	332.52	333.65
230	334.79	335.93	337.07	338.21	339.35	340.5	341.64	342.78	343.93	345.08
240	346.22	347.37	348.52	349.67	350.82	351.97	353.12	354.28	355.43	356.58

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, MEAS, TE Connectivity, and the TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

Measurement Specialties, Inc.,
a TE Connectivity Company
1711 139th Lane NW
Andover, MN 55304
Tel +1 763 689 4870
Fax +1 763 689 5033
customercare.ando@te.com