

RP73PF1J11RBTDF

✓ ACTIVE

Holsworthy | Holsworthy RP73

TE Internal #: 2-1625867-5

11 ohm, Thin Film, Precision Resistor, .1 %, 0603, .166 W, ±25 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**
Element Type: **Thin Film**
Package Size Code: **0603**
Power Rating: **.166 W**
Resistance Value: **11 Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0603

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	100 V
Power Rating	.166 W
Resistance Value	11 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.45 mm[.018 in]
Product Length	1.55 mm[.061 in]
Product Width	.8 mm[.031 in]



Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RP73PF1J11RBTDF

11 ohm, Thin Film, Precision Resistor, .1 %, 0603, .166 W, ±25 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73



TE Part # 1-2176092-8

RP 2A 0.25W 1K0 0.1% 25PPM 1K RL

TE Part # 2176093-5

RP 2A 0.25W 10K 0.1% 25PPM 1K RL

TE Part # 2-2176308-7

RP 1E 0.1W 249K 0.1% 25PPM 5K RL

TE Part # 1625867-2

RP 1J 0.166W 10K 0.1% 25PPM 1K RL

TE Part # 2176308-5

RP 1E 0.1W 147K 0.1% 25PPM 5K RL

Also in the Series | [Holsworthy RP73](#)

[Surface Mount Resistors\(4227\)](#)

Customers Also Bought

TE Part #154765-E

SMCB 50 M AB VV 7-03 CL * 0007 137 E004

TE Part #1241050-3

2x3P MOD II BREAK AWAY HDR,SMD, BLISTER

TE Part #1571983-8

GDH06S04=DIP SWITCH

TE Part #1614881-3

CPF 0603 100R 0.1% 25PPM 1K RL

TE Part #2-1625867-9

RP 1J 0.166W 12R1 0.1% 25PPM 1K RL

TE Part #4-1625867-8

RP 1J 0.166W 19R1 0.1% 25PPM 1K RL

TE Part #3-1879457-3

TE 2500W 470R 5% Bracket

TE Part #1-2176071-4

3521 470K 1% 2W

RP73PF1J11RBTDF

11 ohm, Thin Film, Precision Resistor, .1 %, 0603, .166 W, ±25 ppm/°C, Solder, 2 Terminations, .45 mm [.018 in] Height, Holsworthy RP73



Documents

Product Drawings

RP 1J 0.166W 11R 0.1% 25PPM 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1625867-5_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1625867-5_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1625867-5_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RP73-0915

English