




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
Connector System: **Board-to-Board**
Number of Positions: **393**
Centerline (Pitch): **2.79 mm, 3.04 mm, 61.97 mm [.11 in, .12 in, 2.44 in]**
PCB Mount Orientation: **Vertical**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Pairs	96
Number of Loaded Positions	393
Stackable	No
Pairs per Column	8
Number of Positions	393
PCB Mount Orientation	Vertical
Board-to-Board Configuration	Parallel
Number of Power Positions	0
Number of Signal Positions	8

Electrical Characteristics

Impedance	100 Ω
-----------	-------



Operating Voltage	0 VDC
-------------------	-------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Finish	Matte
Mating Tab Width	.69 mm[.027 in]
PCB Contact Termination Area Plating Material Thickness	.5 – 2.54 µm[19.68 – 100 µin]
Contact Layout	Staggered
Contact Base Material	Copper Alloy
Mating Tab Thickness	.41 mm[.015 in]
Contact Mating Area Plating Material	Gold Flash
Contact Type	Pin
Contact Current Rating (Max)	1.5 A
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.076 µm[3 µin]

Termination Features

Rectangular Termination Post & Tail Width	.43 mm[.016 in]
Rectangular Termination Post & Tail Thickness	.15 mm[.005 in]
Termination Post & Tail Length	1.45 mm[.057 in]
Termination Method to PCB	Through Hole - Press-Fit

Mechanical Attachment

Mating Retention	With
PCB Mount Alignment Type	Post Polarization
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	With

Housing Features

Mating Entry Location	Top
Centerline (Pitch)	2.79 mm, 3.04 mm, 61.97 mm [.11 in][.12 in] [2.44 in]
Housing Material	Matte

Dimensions



Connector Height	22.8 mm[.897 in]
Stack Height	23 mm[.905 in]
PCB Thickness (Recommended)	1.57 mm[.8 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box, Tray
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-2110551-1
[STRADA MESA,RC,ST,096,084,00,SN,N,NA](#)

Customers Also Bought



TE Part #5-104076-2
[60 SYS50 HDR DRST SHRD W/SL SN](#)



TE Part #3-1415020-1
[PT570N20](#)



TE Part #1-1825006-9
[GDS10S04=DIP SW,SLIDE,SMT](#)



TE Part #5146893-2
[1FHR,84,30A/S,S,C,S08,09,10](#)



TE Part #2176314-4
[MELF SMA_A 180R 0.1% 15PPM 0102 0.3W](#)



TE Part #1-928836-2
[MOD2 PIN WITH A-PIN L/P](#)



TE Part #1-1437581-1
[ASE22RL=AUTOSLIDE DP](#)



TE Part #5-103911-3
[60 SYSTEM 50 RCPT ASSY DRRA](#)



TE Part #7-2176246-6
[CRGS2512 5% 1M8](#)



TE Part #4-2176391-7
[RQ 1206 37K4 0.1% 10PPM 5K RL](#)

Documents

Product Drawings
[STRADA MESA,HD,ST,096,084,00,SN,N,23](#)
English



CAD Files

Customer View Model

[ENG_CVM_CVM_7-2110550-3_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_7-2110550-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-2110550-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English