

EDSP06SGRNNTU04

✓ ACTIVE

ALCOSWITCH | ALCOSWITCH DIP EDSP


TE Internal #: 2319764-8

DIP Switch, Gold Flash Contact Plating, Black, High Temperature Nylon, 6 Switch, -20 – 85 °C [-4 – 185 °F], Piano (Side Actuated), ALCOSWITCH DIP EDSP

[View on TE.com >](#)



Switches > DIP & SIP Switches



Switch Contact Plating Material: Gold Flash

Case Color: Black

Case Material: High Temperature Nylon

Sealed Device: No

Number of Switches: 6

Features

Product Type Features

Sealed Device	No
DIP & SIP Switch Type	DIP
Actuator Style	Piano (Side Actuated)

Configuration Features

Number of Positions	6
Number of Switches	6
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	.025 A
Operating Voltage	24 VDC

Body Features

Actuator Color	White
Product Orientation	Vertical
Case Color	Black



Case Material	High Temperature Nylon
---------------	------------------------

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold Flash
Switch Contact Plating Material	Gold Flash
Contact Base Material	Copper Alloy

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Length	15.14 mm[.596 in]
Product Height	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]
-----------------------------	--------------------------

Packaging Features

Packaging Method	Tube
Packaging Quantity	31

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-2319764-1
E STACK PIANO 2P G LONG T&R PD OFF



TE Part # 3-2319764-3
E STACK PIANO 6P G LONG T&R PD ON



TE Part # 2319764-2
E STACK PIANO 4P G LONG TUBE PD ON




TE Part # 2319764-4
E STACK PIANO 8P G LONG TUBE PD ON



TE Part # 3-2319764-1
E STACK PIANO 2P G LONG T&R PD ON

Also in the Series | ALCOSWITCH DIP EDSP



DIP & SIP Switches(20)

Customers Also Bought



TE Part #5070062034
RNF-100-1/4-X-STK




TE Part #4-1415899-9
RZ03-1A3-D012




TE Part #1622886-1
CRG0603 1% 22K




TE Part #2-2176058-5
RLP73K 3A R10 5% 2K RL




TE Part #2176331-7
CRGP 2512 33R 1%



TE Part #5-2176331-1
CRGP 2512 150K 1%



TE Part #2319764-3
E STACK PIANO 6P G LONG TUBE PD ON



TE Part #3-2319764-1
E STACK PIANO 2P G LONG T&R PD ON



TE Part #5747841-4
15 MSFL PLUG RA 318 (IN,FM,BL)



TE Part #4-1415538-0
RT314730WG

Documents

Product Drawings

E STACK PIANO 6P G SHORT TUBE PD ON

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2319764-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2319764-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2319764-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English

SWITCHES_CATALOG_SECTION_A_DIP_SWITCHES

English