



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Element Type: **Metal Film**
Power Rating: **3 W**
Resistance Class: **1kΩ – 1MΩ**
Resistance Value: **91K Ω**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	750 V
Power Rating	3 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	91K Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	15 x 5 mm
------------------------------	-----------



Usage Conditions

Temperature Coefficient	±300 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1879352-5
[RR02 5% 56R AMMO](#)



TE Part # 8-1879354-5
[RR03 5% 1K0 AMMO](#)



TE Part # 4-1879350-9
[RR01 5% 22R AMMO](#)



TE Part # 7-1879352-7
[RR02 5% 470R AMMO](#)



TE Part # 6-1879354-6
[RR03 5% 160R AMMO](#)

Also in the Series | [NEOHM RR](#)



[Through-Hole Resistors\(478\)](#)

Customers Also Bought



TE Part #1-338086-6
[6/6 INV.MOD.JACK](#)



TE Part #350778-1
[02P UMNL CAP HSG](#)



TE Part #530341-1
[BOX EST KEY PASSIVATED](#)




TE Part #2-640454-6
[26P MTA100 HDR ASSY SQ STR POL](#)




TE Part #3-641208-6
[06P MTA156 HDR ASSY FL ST LF](#)



TE Part #644752-2
[02P MTA156 HDR ASSY SQ STR F/L](#)



TE Part #1586037-4
[4P VERT HDR VAL-U-LOK V2](#)



TE Part #1-1623788-0
[SQM5 22R 5% \(WIRE\)](#)



Documents

Product Drawings

RR03 5% 91K AMMO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1879355-3_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1879355-3_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1879355-3_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Power Resistor - Type RR Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English