



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

Connector System: **Board-to-Board**

Number of Positions: **80**

Centerline (Pitch): **.8 mm [.031 in]**

PCB Mount Orientation: **Vertical**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Connector Contact Load Condition	Fully Loaded
Stackable	No
Number of Positions	80
PCB Mount Orientation	Vertical
Board-to-Board Configuration	Parallel

Electrical Characteristics

Impedance	100 Ω
-----------	-------



Insulation Resistance	2 MΩ
Dielectric Withstanding Voltage (Max)	675 VAC
Operating Voltage	125 VAC

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Mating Tab Width	.38 mm[.015 in]
PCB Contact Termination Area Plating Material Thickness	.25 μm[9.842 μin]
Contact Shape & Form	Single Beam, Square
Contact Base Material	Phosphor Bronze
Mating Tab Thickness	.2 mm[.008 in]
Contact Mating Area Plating Material	Gold Flash
Contact Type	Pin
Contact Current Rating (Max)	1.25 A, 9.5 A
PCB Contact Termination Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.25 μm[9.84 μin]

Termination Features

Rectangular Termination Post & Tail Width	.9 mm[.035 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Method to PCB	Surface Mount

Mechanical Attachment

Mating Retention	With
PCB Mount Alignment Type	Locating Posts
Connector Mounting Type	Board Mount
Mating Alignment	Without
PCB Mount Alignment	With
PCB Mount Retention	With

Housing Features

Centerline (Pitch)	.8 mm[.031 in]
Housing Material	LCP

Dimensions

Connector Height	13.39 mm[.526 in]
------------------	-------------------



Stack Height	14 mm[.551 in]
PCB Thickness (Recommended)	1.57 mm[.25 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Assembly Process Feature	None
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	125
Packaging Method	Pocket Tape

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2-1658012-2
MSB0.80RC-ASY080FL,-,10,-TY

TE Part # 2-1658043-2
MSB0.80RC-ASY080FL,-,F,-TY

TE Part # 6-1658043-2
MSB0.80RC-ASY080FL,GP,F,-TR

TE Part # 4-1658462-2
MSB0.80RC-ASY080FL,GP,30,-TR

TE Part # 6-1658462-2
MSB0.80RC-ASY080FL,GP,30,-TR

TE Part # 2-1658462-2
MSB0.80RC-ASY080FL,-,30,-TY

TE Part # 6-1658012-2
MSB0.80RC-ASY080FL,GP,10,-TR

TE Part # 1658043-2
MSB0.80RC-ASY080FL,-,F,-TY

TE Part # 4-1658012-2
MSB0.80RC-ASY080FL,GP,10,-TR

TE Part # 4-1658043-2
MSB0.80RC-ASY080FL,GP,F,-TR

TE Part # 1658012-2
MSB0.80RC-ASY080FL,-,10,-TY

TE Part # 1658462-2
MSB0.80RC-ASY080FL,-,30,-TY

Customers Also Bought


TE Part #5-104076-2
60 SYS50 HDR DRST SHRD W/SL SN

TE Part #3-1415020-1
PT570N20

TE Part #1-1825006-9
GDS10S04=DIP SW,SLIDE,SMT

TE Part #5146893-2
1FHR,84,30A/S,S,C,S08,09,10





TE Part #2176314-4
MELF SMA_A 180R 0.1% 15PPM 0102
0.3W




TE Part #1-1437581-1
ASE22RL=AUTOSLIDE DP



TE Part #1-928836-2
MOD2 PIN WITH A-PIN L/P



TE Part #5-103911-3
60 SYSTEM 50 RCPT ASSY DRRA



TE Part #4-2176391-7
RQ 1206 37K4 0.1% 10PPM 5K RL



TE Part #7-2176246-6
CRGS2512 5% 1M8

Documents

Product Drawings
MSB0.80PL14ASY080FL,GP,10,-TR
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_4-1658438-2_J.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_4-1658438-2_J.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_4-1658438-2_J.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
MICTOR SB Interconnection System
English

Product Specifications
Application Specification
English