

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (13% in 4690948374) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 6-87631-4 58 MODIV HSG DR MRKD .100 POL	 TE Part # 3-87631-8 42 MODIV HSG DR MRKD .100 POL	 TE Part # 1-87977-4 32 MODIV HSG DR MRKD .100POL	 TE Part # 1-87977-6 36 MODIV HSG DR MRKD .100 POL
 TE Part # 5-87977-4 72 MODIV HSG COMP DR .100 POL	 TE Part # 6-87456-5 64 MODIV HSG COMP DR .100CL	 TE Part # 4-87631-3 52 MODIV HSG COMP DR .100 POL	 TE Part # 1-102241-9 21 MODIV HSG COMP SR .100 POL
 TE Part # 6-87631-6 64 MODIV HSG DR MRKD .100 POL	 TE Part # 2-87977-4 60 MODIV HSG DR MRKD .100 POL	 TE Part # 87977-7 18 MODIV HSG DR MRKD .100 POL	 TE Part # 5-87977-7 56 MODIV HSG DR MRKD .100 POL
 TE Part # 6-87631-3 58 MODIV HSG COMP DR .100 POL	 TE Part # 4-87977-7 44 MODIV HSG COMP DR .100 POL	 TE Part # 1-102241-7 19 MODIV HSG COMP SR .100 POL	 TE Part # 5-87977-1 60 MODIV HSG COMP DR .100 POL



KIT

REPRESENTATION ONLY

TE Part # 7-2836135-7

[OCEAN_2.0_SPARE_PART_KIT-033F055O](#)



TE Part # 1-102241-1

[13 MODIV HSG COMP SR .100 POL](#)



TE Part # 1-87977-8

[40 MODIV HSG DR MRKD .100 POL](#)



TE Part # 1-87631-4

[18 MODIV HSG DR MKRD .100 POL](#)

Customers Also Bought




TE Part #CSE-SGAM-610-SGAM

[SMA to SMA 610mm RG316](#)



TE Part #CSE-SGAM-152-SGAM

[SMA to SMA 152mm RG316](#)



TE Part #87631-3

[08 MODIV HSG COMP DR .100 POL](#)



TE Part #87756-6

[MOD IV RECP PLTD SN](#)




TE Part #5-103735-3

[04 MTE HDR SRST LATCH .100CL](#)



TE Part #160292

[PLASTI-GRIP, RING, 12-10 M5](#)



TE Part #207008-6

[CABLE CLAMP KIT, BULK PKG](#)



TE Part #1-770969-0

[06P MINI UMNL R/A HDR ASSY SN](#)



TE Part #1586514-2

[03P CMNL HDR ASSY PC NATL LF](#)



TE Part #2-2176341-5

[CRGCQ 0805 1K0 1%](#)

Documents

Product Drawings

[MOD IV RECP PLTD 15 DPLX](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_102316-6_AF_c-102316-6-af.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_102316-6_AF_c-102316-6-af.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_102316-6_AF_c-102316-6-af.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP MODU IV & V Section of Catalog 1307819](#)

English

Product Specifications

[Application Specification](#)

English