

RNF-100-1/8-2-50MM

✓ ACTIVE

RAYCHEM | RAYCHEM RNF-100


TE Internal #: 5053006076

Heat Shrink Tubing, Red, 2:1, Single Wall, Shrinks To 1.6 mm [.063 in], Irradiated Modified Polyolefin, RAYCHEM RNF-100

[View on TE.com >](#)



Heat Shrink Tubing > RNF-100-2 Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**
Primary Product Color: **Red**
Wall Type: **Single Wall**
Expanded Inside Diameter (Min): **3.2 mm [.126 in]**
Recovered Inside Diameter (Max): **1.6 mm [.063 in]**

[All RNF-100-2 Heat Shrink Tubing \(72\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Red
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.5 mm[.02 in]
Product Length	50 mm[1.969 in]
Recovered Wall Thickness (Tolerance)	.2 mm[.008 in]
Expanded Inside Diameter (Min)	3.2 mm[.126 in]
Recovered Inside Diameter (Max)	1.6 mm[.063 in]



Tubing Size Range	1.6 – 3.2 mm[.062 – .125 in]
-------------------	------------------------------

Usage Conditions

Shrink Temperature (Min)	95 °C
Tubing Flammability Type	Flame-Retardant
Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
Recovery Temperature	121 °C

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-----------------------	--

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	China, Czech Republic

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

RNF-100-1/8-2-50MM

Heat Shrink Tubing, Red, 2:1, Single Wall, Shrinks To 1.6 mm [.063 in], Irradiated Modified Polyolefin, RAYCHEM RNF-100




limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM RNF-100



Heat Shrink Tubing(843)



Orange Heat Shrink Tubing(44)



Power Cable Tubing & Accessories(5)



Single Wall Tubing(842)


Customers Also Bought




TE Part #003127-000
55PC0212-20-9



TE Part #52430-3
TERMINAL,PIDG SPR SPD 12-10 6



TE Part #55845-1
#8 PRE-INSUL SEALED SPLICE



TE Part #3-644426-7
07P MTA100 CONN ASSY W/O#5





TE Part #1776695-1
Strain Relief, D5200, Dynamic



TE Part #1986185-1
Strain Relief, 6 Posn, D5200 Dynamic. 2



TE Part #1986186-1
Strain Relief, 20 Posn, D3000 Dynamic, 2



TE Part #2333393-7
QSFP 25GIG 30AWG 3 METER



TE Part #1-2373376-0
10P, 2MM, SHRD HDR, DRVT, SMD, 0.1 AU, TB



TE Part #1-2600030-0
4CCT BLACK RECEP W/LARGE SEAL

Documents

Product Drawings
RNF-100-1/8-2-50MM

English

Datasheets & Catalog Pages
Application Tooling for Raychem Heat Shrink Product

English

RNF-100 Pages from 9-1773447-9

English

Product Specifications
Application Specification

English

Agency Approvals
UL

English