




TRIO-MATE

TE Internal #: 6-487509-1
Connector Assembly, Wire-to-Board, 12 Position, 2.54 mm [.1 in]
Centerline, 1 Row, Vertical, Socket, Tray, Low, Vertical, TRIO-MATE,
FFC Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Connectors



FFC Connector Product Type: **Connector Assembly**
Connector System: **Wire-to-Board**
Number of Positions: **12**
Centerline (Pitch): **2.54 mm [.1 in]**
Number of Rows: **1**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Receptacle
FFC Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Insertion Force Type	Low

Configuration Features

Number of Positions	12
Number of Rows	1
PCB Mount Orientation	Vertical

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	5 µm[200 µin]
Contact Type	Socket
Contact Current Rating (Max)	1 A



Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	4.06 mm[.16 in]

Mechanical Attachment

Mating Alignment Type	Polarization
PCB Mount Retention Type	Z Bend
PCB Mount Retention	With
Mating Retention	Without
Mating Alignment	With
Panel Mount Feature	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]
FFC Cable Entry	Vertical

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	480
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted



	Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | **TRIO-MATE**

FFC Connectors(64)

Customers Also Bought

TE Part #816497-SF
RN114-0.3-02-47M

TE Part #CAT-PC9-F9260
FN9260 / FN9261 Power Entry
Modules with EMC Filter – General-
Purpose Solution with Fuse Options

TE Part #5-104362-1
02 MTE HDR SRST LATCH W/HLDWN

TE Part #5-104362-2
03 MTE HDR SRST LATCH W/HLDWN



TE Part #5-104363-5
[06 MTE HDR SRST LATCH .100CL](#)




TE Part #643228-1
[03P UMNL HDR ASSY R/A 94VO](#)



TE Part #643232-1
[05P UMNL HDR ASSY R/A 94VO](#)



TE Part #6-1879215-7
[CPF 0402 22K6 0.1% 25PPM 1K RL](#)



TE Part #3-2176452-2
[CPF 0201 1K13 0.1% 25ppm 1K RL](#)

Documents

Product Drawings

[TRIOMATE ASY V12P L=4.064,LDFR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_6-487509-1_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-487509-1_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-487509-1_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Trio-Mate Flat Flexible Discrete Circuit .100 Connectors](#)

English

[Application Specification](#)

Japanese

[Application Specification](#)

English