




Connectors > Connector Accessories > Connector Seals & Cavity Plugs > Medium Power Terminals Single Wire Seals 4.8mm-12mm



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Cavity Diameter: **6.4 mm [.252 in]**

Operating Temperature Range: **-40 – 130 °C [-40 – 266 °F]**

Primary Product Color: **Gray**

Primary Product Material: **Silicone**

[All Medium Power Terminals Single Wire Seals 4.8mm-12mm \(9\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)
----------------------------	------------------------

Body Features

Primary Product Color	Gray
Primary Product Material	Silicone

Dimensions

Cavity Diameter	6.4 mm[.252 in]
Compatible Insulation Diameter Range	1.2 – 2.1 mm[.047 – .082 in]

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
Operating Temperature (Max)	130 °C[266 °F]

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	50
Contains Lubricant	Yes

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Micro Power Quadlock](#)



Automotive Seals & Cavity Plugs(5)



Automotive Terminals(13)




Connector Seals & Cavity Plugs(5)




Insertion & Extraction Tools(1)


Customers Also Bought



TE Part #1-160759-2
250 PL MKI REC. 20-15AWG PTPB



TE Part #963142-2
SWS,MQS,CVTY DIA,4,0,GRY



TE Part #968119-2
MPO2,8 Sn rec LL EDS >0,5-1



TE Part #1326031-4
2.8MM BLD,SEAL,16AWG



TE Part #1379118-2
6POS MQS TAB



TE Part #1625971-5
HSA25 10R 5%



TE Part #1745083-1
3 POS. PLUG ASSY AMP SUPERSEAL 1.5 SRS



TE Part #1801175-3
2W RECEPTACLE HP CONNECTOR GREY



TE Part #1-1801175-5
2W RECEPTACLE HP CONNECTOR GREEN



TE Part #964133-2
FF 110 TAB 1-2.5 MM2 .110 F PTP CUSN4

Documents

Product Drawings

MPQ EINZELLEITDICHT

English

MPQ EINZELLEITDICHT

English

CAD Files

Customer View Model

ENG_CVM_CVM_967610-1_A.2d_dxf.zip



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_967610-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_967610-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English