




Automotive Parts > Automotive Connectors > Automotive Headers > Signal Header



PCB Mount Orientation: **Vertical**
Termination Method to PCB: **Through Hole - Solder**
Sealable: **No**
Centerline (Pitch): **2.54 mm [.1 in]**
Connector System: **Wire-to-Board**

[All Signal Header \(237\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Mixed & Hybrid Header	No
Header Type	Fully Shrouded
Connector Shape	Rectangular
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	18
Number of Sections	1
PCB Mount Orientation	Vertical
Number of Positions	18
Number of Rows	2



Body Features

Connector & Keying Code	A
Primary Product Color	Black

Contact Features

Mating Tab Width	.63 mm[.025 in]
Mating Tab Thickness	.63 mm[.025 in]
Contact Type	Tab
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
PCB Mount Retention	With
Mounting Holes	With
PCB Mount Retention Type	Boardlock
Mating Alignment	With
PCB Mount Alignment	With

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Connector Width	23.3 mm[.92 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Length	39.6 mm[1.56 in]
Profile Height from PCB	20.48 mm[.806 in]

Usage Conditions

Operating Temperature (Max)	125 °C[212 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Shielded	No
Circuit Application	Signal

Packaging Features



Packaging Quantity	420
--------------------	-----

Other

Interface Number	114-18063-023
------------------	---------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #DT15-08PA
HDR, 8P, GRY, ST, NI/CU, A



TE Part #5-146132-1
03 MODII HDR SR SFMNT B/A .100



TE Part #CAT-SIGH262
Signal Header




TE Part #CAT-M4599-H342
AMP MCP Unsealed Headers



TE Part #966870-3
16POS,TAB0.63X0.63,HDR ASSY,90
DEG,COD B



TE Part #1-1418362-3
62 POS MIXED HEADER CODA



TE Part #1642624-4
FSN-73.2Z-4

Documents

Product Drawings

18pos MQS .63 header 180deg

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_967618-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_967618-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_967618-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

MICRO QUADLOCK SYSTEM STIFTWANNEN ZUR INDIREKTEN LEITERPLATTENKONTAKTIERUNG

English

Product Specification

English

Product Specification

English