




Automotive Parts > Automotive Power Distribution Boxes > Module Components



Component Type: **Fuse Holder**

Fuse Type: **Medium Fuse**

Number of Fuses (Minimum): **4**

Number of Positions: **8**

Centerline (Pitch): **8.5 mm [.334 in]**

Features

Product Type Features

Component Type	Fuse Holder
Fuse Type	Medium Fuse
Primary Locking Feature	Locking Lance

Configuration Features

Number of Fuses (Minimum)	4
Number of Positions	8

Electrical Characteristics

Nominal Voltage Architecture	12 V
Operating Voltage	12 V

Body Features

Secondary Locking	No
-------------------	----

Housing Features

Centerline (Pitch)	8.5 mm[.334 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Vibration Class Level	3G
-----------------------	----



Other

Coupling With Other TE Modules	Yes
--------------------------------	-----

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 953653-2
HOLDER GUIDE FOR RELAY

Also in the Series | [Modular Hard Wired Fuse and Relay Box](#)



Automotive Housings(1)




Automotive Signal & Power Connector Housings(1)



Busbars & Terminals(2)



Hard Wired Box Accessories(12)




Module Components(16)




Other Automotive Connector Accessories(1)


Customers Also Bought



TE Part #1011-030-0205
CLIP, PA66, BLK, T-STUD, ST



TE Part #144432-1
JPT F REC 2.8 Contact SRC Sn



TE Part #2-953615-2
MODULAR RELAY HLDR 50-60A



TE Part #1-968851-1
AMP MCP 2.8, CONTACT




TE Part #1241375-1
AMP MCP 1.5K, CONTACT, (LP)



TE Part #1241978-2
JPT A REC 2.8 Contact SRC Sn



TE Part #1-1355200-1
MCP2,8BU-GEH ASSY2P



TE Part #1379681-1
24W TAB HSG ASSY BLACK



TE Part #2112289-1
PROTECTION CAP, GROUP A, ASSY



TE Part #2-2413900-2
2POS DIA 4MM PIN HSG ASSY-PCB, COD B

Documents



Product Drawings

AUTOFUSE HOLDER BLACK

English

CAD Files

Customer View Model

ENG_CVM_CVM_185847-2_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_185847-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_185847-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English