




Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Boots



Body Orientation: **Right Angle**  
Material Code: **4**  
Material Systems Code: **10**  
Adhesive Requirement: **Adhesive Precoat**  
Operating Temperature Range: **-55 – 135 °C [-67 – 275 °F]**

Features

Configuration Features

Adhesive Requirement	Adhesive Precoat
----------------------	------------------

Body Features

Primary Product Material	Polyolefin Flexible Modified
Material Code	4
Material Systems Code	10

Housing Features

Body Orientation	Right Angle
------------------	-------------

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Other

Adhesive Code	42
---------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	




Current ECHA Candidate List: JAN 2025  
(247)  
Candidate List Declared Against: JAN 2025  
(247)  
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 9-120035-5  
HarnWare/HarnVis Purchase Charge




TE Part # 9-120035-6  
HarnWare/HarnVis Renewal Charge


Customers Also Bought




TE Part #557721-000  
TMS-RJS-RIBBON-4RPSCE



TE Part #890113-000  
S1048-TAPE-1X100-FT



TE Part #CAT-P592-R472A  
PIDG Ring Tongue Terminals



TE Part #2378048-1  
ASSY, NANORF/MT BP FULL; SOSA 14.26MM

Documents

Product Drawings  
234A011-4/42-0  
English



Datasheets & Catalog Pages

1654025\_Sec4\_-4

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English