



Product Compliance

For compliance documentation, visit the product page on TE.com>

















EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 <p>TE Part # 1SNA291311R2300 FED2.L</p>	 <p>TE Part # 1SNA150047R0000 TH15-5.5-P4-1METER</p>	 <p>TE Part # 1SNA291110R2600 BJD5-10</p>	 <p>TE Part # 1SNA291107R2000 BJD5-7</p>
 <p>TE Part # 1SNA291103R2400 BJD5-3</p>	 <p>TE Part # 1SNA230000R1200 RC55</p>	 <p>TE Part # 1SNA291301R0200 FED1.L</p>	 <p>TE Part # 1SNA291106R2700 BJD5-6</p>
 <p>TE Part # 1SNA150046R0000 TH15-5.5-2METER</p>	 <p>TE Part # 1SNA291104R2500 BJD5-4</p>	 <p>TE Part # 1SNA291109R0200 BJD5-9</p>	 <p>TE Part # 1SNA199420R2100 BADRL</p>
 <p>TE Part # 1SNA291102R2300 BJD5-2</p>	 <p>TE Part # 1SNA291108R0100 BJD5-8</p>	 <p>TE Part # 1SNA291105R2600 BJD5-5</p>	 <p>TE Part # 1SNA164600R1200 PR2</p>

Customers Also Bought

 <p>TE Part #1SNA290201R1100 DR2.5/5.2L</p>	 <p>TE Part #1057290-1 3052 1201 10,N SERIES FM PLUG</p>	 <p>TE Part #1337808-3 50 OHM COAX SMA STR PLUG STR P</p>	 <p>TE Part #1622230-1 LR0204 1% 3K3</p>
--	--	--	---





TE Part #1622247-1
LR0204 1% 4K7



TE Part #2-1625892-5
3W SM M/OX 5% 1M0



TE Part #5-1625892-3
3W SM M/OX 5% 47K



TE Part #1838891-2
M12 Mtl FEMALE PNL CONN. Sldr Rear (Hex)



TE Part #1-1825142-5
AE101SD1AB04

TE Part #1SNA291301R0200
FED1.L

Documents

Datasheets & Catalog Pages

DR2.5/5.N.2L

English

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)