

H81K87BZA

✓ ACTIVE

Holsworthy | Holsworthy Holco


TE Internal #: 2-1879694-1

1.87K ohm, Thin Film, Precision Resistor, .1 %, .25 W, ±100 ppm/°C,  
Axial-Leaded, Copper Termination, 7.2 x 2.5 mm, Bandoliered,  
Holsworthy Holco

[View on TE.com >](#)



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Precision Resistor**  
Element Type: **Thin Film**  
Power Rating: **.25 W**  
Resistance Class: **1kΩ – 1MΩ**  
Resistance Value: **1.87K Ω**

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	350 V
Power Rating	.25 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	1.87K Ω
Passive Component Tolerance	.1 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	7.2 x 2.5 mm
------------------------------	--------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C[-67 – 311 °F]
Temperature Coefficient	±100 ppm/°C

Packaging Features

Packaging Method	Bandoliered
------------------	-------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts




TE Part # 1879629-8  
[H4P 127R 0.5% 5PPM](#)




TE Part # 1879623-8  
[H4 1K3 0.1% 5PPM](#)



TE Part # 9-1879664-1  
[H8 10K 0.1% 15PPM](#)



TE Part # 5-1879642-1  
[H8 5K0 0.1% 25PPM](#)



TE Part # 2-1879622-2  
[H4P 1M0 1% 50PPM](#)

Also in the Series | [Holsworthy Holco](#)



[Through-Hole Resistors\(6370\)](#)

Customers Also Bought



TE Part #20014203-12  
[PRESS XDCR M325M-000005-250PG](#)



TE Part #3954384002  
[CGPE-105-1/2-0-SP](#)



TE Part #1-1625893-3  
[5W SM M/OX 2% 22R](#)



TE Part #2-1879461-5  
[RL73H 2A R13 1% 1K RL](#)



TE Part #9-2176415-0  
[8W STD M/OX 5% 150K](#)



TE Part #9-2176415-1  
[8W STD M/OX 5% 160K](#)



TE Part #2-2176455-5  
[CPF 0402 7R5 0.1% 25ppm 1K RL](#)



TE Part #2-2329328-0  
[PB OFF/ON HC BLU M4 TERM. IP68](#)



Documents

Product Drawings

H8 1K87 0.1% 100PPM

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-1879694-1\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-1879694-1\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-1879694-1\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350\_PASSIVE\_COMPONENT

English

Axial Leaded Precision Resistors - Type HOLCO Series

English

8-1773459-4\_POWER\_FILTERING\_AND\_RESISTIVE\_SOLUTIONS\_FOR\_ELEVATORS\_AND\_ESCALATORS

English