

ASHD114-1PN-C16

✓ ACTIVE

DEUTSCH | DEUTSCH ASHD

TE Internal #: ASHD114-1PN-C16

1 Position Circular Connector, Wire-to-Wire, Black Zinc, Aluminum Alloy, N Code, Hard Dielectric/Silicone, 14 Shell Size, Receptacle, DEUTSCH ASHD

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Number of Positions: **1**

Shell Plating Material: **Black Zinc**

Shell Base Material: **Aluminum Alloy**

Polarization Code: **N**

Features

Product Type Features

Assembly Type	Electrical Connector
Connector Product Type	Connector Assembly
Connector System	Wire-to-Wire
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Factory Installed Backshell	No
Number of Positions	1
Contacts Preloaded	No

Body Features

Feedthrough Type	No
Entry Style	Rear Insertion
Shell Plating Material	Black Zinc
Shell Base Material	Aluminum Alloy
Circular Connector Insulation Material Type	Hard Dielectric/Silicone
Hermetically Sealed	No

Contact Features

--	--



Circular Connector Contact Type	Pin
---------------------------------	-----

Mechanical Attachment

Mating Retention Type	Bayonet Peg
Mating Alignment	With
Polarization Code	N
Mating Alignment Type	Keyed
Mating Retention	With

Housing Features

Circular Connector Shell Size	14
-------------------------------	----

Dimensions

Assembly Length	33.5 mm
-----------------	---------

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	7
Fluid Resistance	Immersion
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Operation/Application

Durability Rating	500 Cycles
-------------------	------------

Other

Field Serviceable	Yes
-------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.2% in Contact) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | DEUTSCH ASHD

Standard Circular Connectors(72)

Customers Also Bought

TE Part #ASL606-05SN-HE
PLUG ASSY. AS MICRO MK3.

TE Part #ASU603-03PN-HE
PLUG ASSY AS 3 WAY

TE Part #AS110-35SN
RECEPT.CABLE COUP.TYPE 1

TE Part #ASL106-05SN-HE
RECEPT.ASSY. IN-LINE.AS MICRO MK3

TE Part #ASU103-03SN-HE
RECEPT ASSY INLINE AS 3 WAY

TE Part #ASHD614-1SN-C16
PLUG.100A.16mm SKT.

TE Part #ASL106-05PB-HE
RECEPT.ASSY. IN-LINE.AS MICRO MK3

TE Part #AS110-35PN
RECEPT.CABLE COUP.TYPE 1

Documents

Datasheets & Catalog Pages



DEUTSCH Autosport Interconnection Solutions

English