



Wire & Cable > Hook Up Wire > SPEC 80 Hookup Wire: FlexLine Cable, Silver Coated Copper



Cable Type: **Spec 80**

Operating Voltage: **600 V**

Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**

Conductor Material: **Silver-Coated Copper**

Wire Size: **12 AWG**

[All SPEC 80 Hookup Wire: FlexLine Cable, Silver Coated Copper \(18\)](#)

Features

Product Type Features

Wall Type	Single Wall
Cable Style	Primary

Configuration Features

Number of Conductors	1
----------------------	---

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Conductor Stranding	High Strand Count Conductor
Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Silver-Coated Copper
Wire Color (Base)	White

Dimensions

Wire Size	12 AWG
-----------	--------

Usage Conditions

Cable Type	Spec 80
------------	---------



Operating Temperature Range

-65 – 150 °C[-85 – 302 °F]

Operation/Application

Wire Class	Equipment
------------	-----------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



 <p>TE Part #216368-001 <a href="#">22759/33-26-9</a></p>	 <p>TE Part #997172-000 <a href="#">462A023-25/225-0</a></p>	 <p>TE Part #032015-000 <a href="#">82A0111-22-9</a></p>	 <p>TE Part #819098-000 <a href="#">381A303-51-0</a></p>
 <p>TE Part #851659-000 <a href="#">TXR40AB90-1006AI</a></p>	 <p>TE Part #414354-000 <a href="#">55A6262-22-9/96-9CS2275</a></p>	 <p>TE Part #819103-000 <a href="#">462A421-51-0</a></p>	 <p>TE Part #E17344-000 <a href="#">CM-SCE-TP-1/2-4H-9</a></p>
 <p>TE Part #6160-246-1231 <a href="#">CONT PIN ASSY</a></p>	 <p>TE Part #254872-000 <a href="#">44B5841-4-MST4-9CS1401</a></p>		

Documents

Product Drawings  
[82A0112-12-9](#)

English

Datasheets & Catalog Pages  
[Raychem Wire and Cable Quick Reference Guide](#)

English

Product Specifications  
[Product Specification](#)

English