



All 48V Ready 1.5mm Sealed Connectors (19)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1241380-1  
AMP MCP 1.5K, CONTACT, SWS




TE Part # 964971-1  
EINZELLEITERDICHTNG


Customers Also Bought




TE Part #179631-1  
DIAGNOSTIC PLUG HSG 16P NARU.




TE Part #927366-1  
8P MIN D-FLACHF GEH




TE Part #CAT-T4827-T273  
TIMER, RECEPTACLE AND TAB




TE Part #1-967402-3  
2,5MM ST-GEH KPL 2P




TE Part #967542-1  
2.8MM SFC, TERMINAL, SWS, LL




TE Part #1241608-6  
MQS1,5 Ag rec CB unseal. 0,75-1,5



TE Part #1418994-1  
AMP MCP 2.8 HSG.WITH SEC.10POS



TE Part #1534099-1  
MQS COVER 2X10P



TE Part #1823467-8  
6POS,AMP MCP1.5K,REC HSG,CODH

Documents



Product Drawings

5POS,AMP MCP1.5K,REC. HSG

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_2137400-1\_A.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2137400-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2137400-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English