



Energy & Power > Analog Power Meters



Power Meter Function: DC Ammeter

Scale: 0/400 A

Scale Shape: Short Scale (90)

Case Size: 96 mm [ 3.78 in ]

Features

Product Type Features

Scale	0/400 A
Scale Shape	Short Scale (90)
Accuracy	±1.5 %

Configuration Features

Wiring Configuration	Single Phase
Panel Cutout Size	64 mm[2.52 in]

Electrical Characteristics

Power Meter Function	DC Ammeter
----------------------	------------

Body Features

Product Weight	.25 kg
----------------	--------

Mechanical Attachment

Product Mount Type	DIN Panel Mount
--------------------	-----------------

Dimensions

Case Size	96 mm[3.78 in]
Product Height	96 mm[3.78 in]
Product Depth	64 mm[2.52 in]
Product Width	96 mm[3.78 in]



Operation/Application

Operating Frequency Range	50 – 60 Hz
---------------------------	------------

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

CI-E244-01AGFASJ

DIN Panel Mount Analog Power Meter, DC Ammeter, 0/1 mA, 0/400 A, Short Scale (90), 96 mm [3.78 in] Case, 64 mm [2.52 in] Panel Cutout, Crompton 007






TE Part # D62307-000  
[CI-E244-01V-G-NL-NL](#)



TE Part # A27988-000  
[CI-E244-01VGNDND](#)

Also in the Series | [Crompton 007](#)



[Analog Power Meters\(210\)](#)

Customers Also Bought



TE Part #D67827-000  
[CI-E243-01A-G-MT-MT](#)



TE Part #10218849-00  
[PRESS XDCR M323M-00000E-010BG](#)



TE Part #1393260-1  
[SR6B4005 - V23050-A1005-A542](#)



TE Part #7-1614352-6  
[RN 0603 73R2 0.1% 10PPM 1K RL](#)



TE Part #4-1614893-5  
[CPF 0805 38K3 0.1% 25PPM 1K RL](#)



TE Part #1622770-1  
[LR2 1% 62K](#)




TE Part #1825136-2  
[A101KAB04](#)



TE Part #1-2176376-8  
[RQ 0805 18K7 0.1% 10PPM 1K RL](#)



TE Part #2-2308350-1  
[CRIMP BARREL11](#)



TE Part #2-1833011-8  
[RZF1-1A6-L005](#)



Documents

Product Drawings

CI-E244-01AGFASJ

English

Datasheets & Catalog Pages

DIN PANEL METERS TE CROMPTON INSTRUMENTS

English