



Product Compliance

For compliance documentation, visit the product page on TE.com>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Not reviewed for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 2132723-1


IMP100O,R,RA6P12C,UG,39




Customers Also Bought




TE Part #50865  
SOCKET,MIN-SPR AU SER-4




TE Part #861647-6  
RECPT FLANGED H.V. 7 CONTACTS




TE Part #1376073-2  
DYNAMIC D-2000 TAB ASSY 50P




TE Part #8-1622796-9  
YR1 0.1% 191K




TE Part #9-1734774-3  
PCI EXP 2.3L 64 POS BLK 30u"




TE Part #1735482-3  
0.8FH,R17H.5,080,08/Sn,TR,SC




TE Part #1735482-4  
0.8FH,R17H.5,100,08/Sn,TR,SC



TE Part #8-1879160-5  
RN 0805 8R66 0.1% 10PPM 1K RL



TE Part #1-1879208-4  
CPF 0402 36R 0.1% 25PPM 1K RL



TE Part #4-2176230-7  
3522 5K6 5% 3W

Documents

Product Drawings

IMP100O,HMP,V6P12C,UG,OEW39,5.5

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English